



MATERIALS AND FINISHES



BODY BRASS
PLATED GOLD

CENTER CONTACT BERYLLIUM COPPER
PLATED GOLD

INSULATOR TEFLON



RECOMMENDED PANEL CUTOUT
MAX PANEL THICKNESS: 2.2mm (.087)



LABEL FORMAT FOR
73391-0042

PART NUMBER: 73391-0040
ORDER NUMBER: 73391-0042
MOLEX
DATE: YYWW

PS-89675-3460	ELECTRICAL/MECHANICAL
MIL-STD-348A, FIG. 310.2	INTERFACE
SPECIFICATION	DESCRIPTION

73391-0042	ONE PIECE PER BAG
73391-0041	SMALL TRAY (20 PIECES)
73391-0040	STANDARD TRAY
PART NO.	PACKAGING

CHG: UPDATE LABEL FOR -0042	EC NO: URF2012-0380	2012/01/04	QUALITY SYMBOLS ▽=0 ▽=0
	DRWN: BOMALLEY	2012/01/04	
	CHKD: AZR	2012/01/04	
REV	APPR: JWIENER	2012/01/04	DESCRIPTION

GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM/IN		SCALE	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
	mm	INCH	DRAWN BY DATE		SMA JACK RECEPTACLE 4 HOLE FLANGE 50 OHMS SMA-JR EWR-N/A  MOLEX INCORPORATED		
4 PLACES	± ---	± ---	IRIS 1997/05/27				
3 PLACES	± ---	± ---	CHECKED BY DATE				
2 PLACES	± ---	± ---	SAM 1997/05/27				
1 PLACE	± ---	± ---	APPROVED BY DATE				
ANGULAR ± 2 °			JWIENER 2011/04/20				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			MATERIAL NO.		DOCUMENT NO.		SHEET NO.
			SEE TABLE		SD-73391-004		1 OF 1
			SIZE 		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		