




Sezione A-A
(Section)



Note: (Notes)

- 1 Noryl (UL 94-V0) Colore Nero (Black colour).
2 Tolleranza non Cumulativa.
(Non-Cumulative Tolerance).
3 OBSOLETE



22	280642	53,34	58,2	3	1
15	280641	35,56	40,4	3	
12	280640	27,94	32,8		
9	280639	20,32	25,1	3	
8	280638	17,78	22,6		
4	280637	7,62	12,5		
N° Pos.	Part Number	Dim. "A"	Dim. "B"		Mat.

FINITURA / COLORE (FINISH / COLOUR)		MATERIALE (MATERIAL)		NUMERO (PART NUMBER)	
CUSTOMER DWG. FOR REFERENCE ONLY		DISEGNO PER CLIENTE SOLO PER RIFERIMENTO			
THIS DRAWING IS UNPUBLISHED		RELEASE FOR PUBLICATION			
TOLLERANZE: SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES UNLESS OTHERWISE SPECIFIED)		DIAM. ISOLANTE (INS. DIA. RANGE)		RANGO FILO (WIRE RANGE)	
± 0,3				SCALA (SCALE) 5:1	
ANGOLI (ANGLES) ± 2°		TE Connectivity			
DIS. (DR.) Bassano 29.9.86		DESCRIZIONE (DESCRIPTION) AMP MODU II Pin Housing, Double Row, Crimped Snap-In.			
CONT. (CHK)		LOC. SIZE (DWG NO.)		REV. FOGLIO (SHEET)	
APP. (APP)		NUMERO (DWG NO.)		DI (OF)	
J1 REVISED PER ECO-11-005294		RK 08APR11		J1 1 OF 1	
REVISIONI (REVISION RECORD)		DIS. DATA (DR) (DATE)		IAC (Master Dwg.)	