

Liquidtight Flexible Cord & Cable Fittings

T&B Catalog Number:



CC-NPT-1-G

78621014682

Active

Description:

1 in. non-metallic gray nylon cable gland with NPT threads, cord range-.709-.984; thread length-.709.

Features

Sturdy cable sealing mechanism which results in superior strain relief.

Compact size ensures quick and easy installation in cramped spaces

Non-metallic construction provides excellent corrosion, chemical and impact resistance.

General

Material	Nylon
----------	-------

Color	Gray
-------	------

Dimension Information

Hub Size (inches)	1
Thread Length (inches)	0.709
Cord Range (inches)	.709-.984
Thread Length (mm)	18

Specifications

3dmodel	Available on Website
Temperature Rating	-30 C (-86F) to +80 (176F) - continuous

Accessories & Components

Locknut Catalog Nbr	LN503
---------------------	-------

Packaging

T&B Inner Pack	20
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	10.63 lbs. per 100

Application Support

T&B Sales Drawings	wsd-000004
T&B Instruction Sheets	ta02021-tb2
Product Overview	Available on Website
Portable Cord Selection Table	Available on Website

Notes

Working temperatures- -30°C (-86F) to +80°C (176F)

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 13938

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com