











*System Article type	Technical Data	Order no. Colour	*System Article type	Technical Data	Order no. Colour
(4)  BUELA 300 K	 30 A solder contact max. 2.5 mm ²	931 667-100 ● 931 667-101 ● 931 667-102 ● 931 667-103 ● 931 667-104 ●	(4)  VQ 20	 16 A screw connection max. 1.5 mm ²	930 058-100 ● 930 058-101 ● 930 058-102 ● 930 058-103 ● 930 058-104 ●
(4)  BSB 20 K	 30 A screw connection max. 2.5 mm ²	930 729-100 ● 930 729-101 ● 930 729-102 ● 930 729-103 ● 930 729-104 ●	(4)  VQ 30	 30 A solder contact max. 2.5 mm ²	930 061-100 ● 930 061-101 ● 930 061-102 ● 930 061-103 ● 930 061-104 ●
(4)  BSB 300	 16 A solder contact max. 1.5 mm ²	931 294-100 ● 931 294-101 ●	(4)  VSB 20	 30 A screw connection max. 2.5 mm ²	930 435-100 ● 930 435-101 ● 930 435-102 ● 930 435-103 ● 930 435-104 ●
(4)  VON 20	 16 A screw connection max. 1.5 mm ²	930 046-100 ● 930 046-101 ● 930 046-102 ● 930 046-103 ● 930 046-104 ●	(↔)  SLS 10 B	 30 A 60 V DC	931 824-100 ● 931 824-101 ●
(4)  VON 30	 30 A solder contact max. 2.5 mm ²	930 047-100 ● 930 047-101 ● 930 047-102 ● 930 047-103 ● 930 047-104 ●	(↔)  SLS 20 B	 16 A 300 V screw connection up to 1.5 mm ²	931 825-100 ● 931 825-101 ●

* System: (64) = 0.64 mm system / (2) = 2 mm system / (4) = 4 mm system / ● = 4 mm safety system / (↔) = 4 mm sliding sleeve system