



Features

- ✓ Available from Stock in Convenient 5-Packs
- ✓ PFA or Glass Braid Insulation
- ✓ 20, 24, 30 and 36 AWG Wires
- ✓ Made from Special Limits of Error Wire
- ✓ 36 and 72 inch Lengths Standard
- ✓ NIST Calibration Available


Model No.	AWG Gage	Dia.	Insulation
5TC-GG-(*)-20-(**)	20	0.032"	Glass Braid
5TC-GG-(*)-24-(**)	24	0.020"	Glass Braid
5TC-GG-(*)-30-(**)	30	0.010"	Glass Braid
5TC-TT-(*)-20-(**)	20	0.032"	PFA
5TC-TT-(*)-24-(**)	24	0.020"	PFA
5TC-TT-(*)-30-(**)	30	0.010"	PFA
5TC-TT-(*)-36-(**)	36	0.005"	PFA

*Specify calibration: J, K, T or E

**Specify length: 36 or 72 inches

Calibrations			
J =	K =	T =	E =
Iron-Constantan	CHROMEGA®-ALOMEGA®	Copper-Constantan	CHROMEGA®-Constantan

PFA insulation



Glass Braid insulation

