


USB "A" to USB "B" Cable

172-1028-E



USB "A" to USB "B" Cable



Dimensions: mm (in.)

SPECIFICATIONS

(5) Ferrite Core:	ø12x25xø5.6mm
(4) PVC Molding:	black
(3) Connt. 2:	USB "B" type male 30U
(2) Connt. 1:	USB "A" type male 30U
(1) Cable:	28AWG/1P+24AWG/2C+AEB Rev: 2.0 Jacket color: black OD: 4.5 ± 0.1 mm
RoHS Compliant	

ELECTRICAL SPECIFICATIONS

Contact resistance:	2Ω max.
Insulation resistance:	5M Ω min.
Hi-pot:	300VDC/10ms
100% open short mis-wire test	

Date Last Revised: 6-29-12

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 301382

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

172-1028-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[172-1028-E](#)