

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS – in [mm]				
		A ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
P4-10R	#10	1.40 [35,6]	.55 [14,0]	.50 [12,7]	1.12 [28,5]	.20 [5,1]
P4-14R	1/4"	1.40 [35,6]	.55 [14,0]	.50 [12,7]	1.12 [28,5]	.27 [6,9]
P4-56R	5/16"	1.46 [37,1]	.68 [17,3]	.50 [12,7]	1.12 [28,5]	.33 [8,4]
P4-38R	3/8"	1.46 [37,1]	.68 [17,3]	.50 [12,7]	1.12 [28,5]	.39 [9,9]
P4-12R	1/2"	1.55 [39,4]	.86 [21,8]	.53 [13,5]	1.12 [28,5]	.52 [13,2]


NOTES:

1. UL LISTED AND CSA CERTIFIED FOR:
 - A. #4 AWG STRANDED COPPER WIRE
 - B. 302°F (150°C) MAX TEMP RATING
 - C. 2000 VOLTS MAX
2. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
3. MATERIAL:
 - A. STAMPING - .05" [1,27] THK COPPER, TIN PLATED
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. WIRE STRIP LENGTH: $1/2" \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ [12,7mm $\begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}$]

UL & CSA TOOLS (DIES)

CT-1701 (P4)
CT-2600 (CD-2600-P4)



TITLE				
# 4 BARREL NON-INSULATED RING TONGUE				
CUSTOMER DRAWING				
ITEM REVISION NAME		N41213BB/09		
DATASET FILE NAME		N41213BB/09		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				
.X ± .XX ±		.XXX ± ANGLES ±		
		THIRD ANGLE PROJECTION		
DRAWN BY		MATERIAL:		
DATE		SEE NOTES		
CHK		DRAWING NUMBER:		
SCALE		A41213		
DAW		SIZE		
		SHT 1 OF 1		
		A		