

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — BY —

LOC

	DIST
--	------

REVISIONS

AF

50

	F
--	---

LTR

DESCRIPTION

DATE _____

	DWN
--	-----

	APVD
--	------


11

REVISÉD PER ECR-13-004343

30JUL13

KH

KR



- 1 MATES WITH $.020 \pm .001$ X $.110$ OR $.125$ TABS
- 2 WIRE STRIP LENGTH $.281$
- 3 INSULATION SIZE $.230$ MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 $.015$ MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

HOUSING: NYLON, COLOR—RED TRANSLUCENT
RECEPTACLE: BRASS
TIN

2-520306-2

MATERIAL & FINISH

PART NUMBER	
1	2
3	4
5	6
7	8
9	10
11	12
13	14
15	16
17	18
19	20
21	22
23	24
25	26
27	28
29	30
31	32
33	34
35	36
37	38
39	40
41	42
43	44
45	46
47	48
49	50
51	52
53	54
55	56
57	58
59	60
61	62
63	64
65	66
67	68
69	70
71	72
73	74
75	76
77	78
79	80
81	82
83	84
85	86
87	88
89	90
91	92
93	94
95	96
97	98
99	100

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	11/9/88
B. FORTNEY	

P. FORTNEY	
CHK	11/9/88

MS FEHER	
ARVD	11 / 11 / 88

K RANDOLPH

PRODUCT SPEC

108-2043
APPLICATION OF 2003

1.1.4. 0107

	114-2123
WEIGHT	

WEIGHT	—
--------	---



TE Connectivity

RECEPTACLE ASSY,ULTRA-FAST,
.110/.125 SERIES, 22-18 AWG

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A 7 000730 © 530306

A5	00779	G=520306	=
----	-------	----------	---

SCALE	5:1	SHEET	1 OF 1	REV	
-------	-----	-------	--------	-----	--

1470-19 (3/11)