

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300061402](#)
Status: **Active**
Overview: [Brad Mini-Change Connectors](#)
Description: Mini-Change A-Size Single-Ended Cordset, 5 Poles, Female (90°) to Pigtail, 20 AWG, PVC Cable, 1.0m (3.28') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837

General

Product Family Industrial Cordsets
Series [130006](#)
Connector End A Mini-Change
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [Brad Mini-Change Connectors](#)
Product Name Mini-Change
Protocol DeviceNet
Region America
Type Single Ended
UPC 78678843396

Physical

Cable Diameter 7.14mm (.281")
Cable Length 1.0m (3.28')
Color - Cable Jacket Yellow
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold
Orientation 90° to Pigtail
Poles 5
Temperature Range - Operating -20°C to +90°C
Wire Size AWG 20
Wire/Cable Type E152210

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 300V

Material Info

Engineering Number 105001A07M010

Reference - Drawing Numbers

Sales Drawing SD-130006-033



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130006](#) Series