




**ALL NEW  
PRODUCTS!**


## Heyco® Compression Cable Clamps

| WIRE CAPACITY          |             | Pin<br>Count | PART<br>NO. | DESCRIPTION | PART DIMENSIONS |      |            |      |             |      |
|------------------------|-------------|--------------|-------------|-------------|-----------------|------|------------|------|-------------|------|
| Volume                 |             |              |             |             | A<br>Length     |      | B<br>Width |      | C<br>Height |      |
| in.                    | mm.         |              |             |             | in.             | mm.  | in.        | mm.  | in.         | mm.  |
| Double Arrowhead Mount |             |              |             |             |                 |      |            |      |             |      |
| 2.11 x .45             | 53,5 x 11,5 | 40           | 12121       | CCTF-40A    | 2.64            | 67,0 | .39        | 10,0 | .63         | 16,0 |
| Adhesive Back Mount    |             |              |             |             |                 |      |            |      |             |      |
| 1.26 x .45             | 32,0 x 11,5 | 30           | 12124       | CCTFA-30    | 1.77            | 45,0 | .73        | 18,6 | .62         | 15,8 |
| 2.57 x .41             | 65,2 x 10,5 | 50           | 12126       | CCTFA-50    | 3.08            | 78,3 | .74        | 18,8 |             |      |

Standard color natural.



- Hinged style allows for easy addition or removal of cables.
- Secures cable into place with easy installation.
- Will not strain cable.



## Heyco® Cable Stays

### Adhesive Back Mount

**ALL NEW  
PRODUCTS!**

| Base Length |      | PART DIMENSIONS Base Width |      | Tongue Length |      | PART NO. | DESCRIPTION |
|-------------|------|----------------------------|------|---------------|------|----------|-------------|
| in.         | mm.  | in.                        | mm.  | in.           | mm.  |          |             |
| .59         | 15,1 | .30                        | 7,7  | .52           | 13,1 | 12143    | CS-5930A    |
| .73         | 18,5 | .39                        | 10,0 | .76           | 19,2 | 12144    | CS-7339A    |



- Provide a secure, yet simple fastening for cables.
- Adhesive back mount results in a very secure attachment.

Material: Nylon 6/6  
Flammability Rating: 94V-2  
Temperature Range: 32°F (0°C) to 185°F (85°C)

Material: Electrolytic Tin-Plated Steel with 3M Adhesive Tape  
Temperature Range: Application Temperature: 70°F (21°C) to 100°F (38°C)  
Operating Temperature: -40°F (-40°C) to 176°F (80°C)

Cable Stays: Electrolytic Tin-Plated Steel with 3M Adhesive Tape  
Application Temperature: 70°F (21°C) to 100°F (38°C)  
Operating Temperature: -40°F (-40°C) to 176°F (80°C)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Heyco:

[3822](#) [3821](#) [3823](#) [3335](#) [3341](#) [3338](#) [3337](#) [3339](#) [3336](#) [3824](#) [3337-P](#) [3335-P](#) [3821-P](#) [3336-P](#) [3338-P](#) [3822-P](#)  
[3341-P](#) [3339-P](#) [3336AB](#) [3336A](#) [3823-P](#) [3824-P](#)