








LOC		DIST		P		F		ZONE		LTR		DESCRIPTION		DATE	APPD
CM		53								G		REV PER EC 0L30-0035-97		3-7-97	JH R5

AMP LOGO AND CAVITY NUMBER LOCATED ON EITHER SURFACE.



RECOMMENDED CUT OUT FOR 1.52 MAX THICK PANEL



3-DIMENSIONAL MODEL NTS

2.13	.084	6.73	.265	-	-
1.57	.062	5.08	.200	21.72	.855
1.52	.060	5.05	.199	20.57	.810
0.38	.015	3.68	.145	12.83	.505
0.25	.010	3.18	.125	8.76	.345
0.13	.005	2.67	.105	8.64	.340
MM	IN	MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES]	DR 11-4-93 K. WHITAKER
TOLERANCES ON :	CHK 11-4-93 R. SWING
2 PLC DEC ± 0.13	APPD 11-4-93 C. CASH
3 PLC DEC ± -	APPD 11-4-93 C. CASH
ANGLES ± 1°0'	PRODUCT SPEC -
MATERIAL NYLON, UL 94V-2 NATURAL	APPLICATION SPEC -
FINISH -	WEIGHT -

DR 11-4-93 K. WHITAKER	CHK 11-4-93 R. SWING	APPD 11-4-93 C. CASH	APPD 11-4-93 C. CASH
PRODUCT SPEC -	APPLICATION SPEC -	WEIGHT -	

AMP Incorporated Harrisburg, PA 17105-3608		770343-1	
NAME		PART NO	
RECEPTACLE, PANEL MOUNT, 2 CIRCUIT, .062 PIN AND SOCKET			
SIZE D	CAGE CODE 00779	DRAWING NO C-770343	
SCALE 5:1		SHEET 1 OF 1	

CUSTOMER DRAWING