

Merchandising/Packaging	2	Router Bits	82
Drilling	4	Jigsaw Blades	98
Drilling Systems	6	XPC Wood Cutting Blades	100
Drill Bit Selection	7	Wood Cutting Blades T-Shank	103
Masonry Drill Bits	11	Wood Cutting Blades U-Shank	105
EXTREME DeWALT® Masonry Drill Bits	12	Metal Cutting Blades T-Shank	106
Multi-Material Drill Bits	12	EXTREME DeWALT® Bi-Metal Cutting Blades T-Shank	107
SDS-Plus EXTREME DeWALT® 2 Drill Bits	13	Metal Cutting Blades U-Shank	107
EXTREME DeWALT® XLR Full Head Carbide Drill Bits	16	Wood & Metal Cutting Blades T-Shank	108
EXTREME DeWALT® Full Head Carbide Drill Bit Sets	17	EXTREME DeWALT® Special Material Blades T-Shank	108
SDS-Plus 4-Cutter Drill Bits	17	Wood & Metal Cutting Blade Kits T-Shank	109
SDS-Max Hammer Drill Bits	18	Reciprocating Saw Blades	110
Chisels	19	Wood Cutting Blades Bi-Metal	112
SDS Chisels	20	Wood Cutting Blades HCS	113
Pavement Breaker Drills	22	Metal Cutting Blades Bi-Metal	114
Light Duty SDS-Plus Core Drills	22	General Purpose Blades Bi-Metal	115
Heavy Duty SDS-Max Core Drills	22	Demolition Blades	116
Light & Heavy Duty Core Adapters	23	Specialist Blades	117
Single Piece Cores	23	Reciprocating Blade Sets	119
Through Drilling Bits	23	ALLIGATOR® Saw Blades	119
Drive Adapters & Adapter - SDS-Plus	23	Bandsaw Blades	120
Metal Drilling	24	Planer Blades & Jointer Accessories	121
Stationary Hard Material Drill Bits	25	Coated Abrasives	122
HSS-CO EXTREME DeWALT® Cobalt Metal Drill Bits	26	Full Sheet	124
EXTREME DeWALT® 2 Metal Drill Bits	28	Half Sheet	125
HSS-G DIN 338 Jobber Metal Drill Bits	30	Third Sheet	126
HSS-G DIN 340 Long Series Metal Drill Bits	33	Quarter Sheet	128
Step Drills	34	Detail	128
Impact Driver Drill Bits	34	Rolls & Belts	129
Wood Drilling	35	Grinding Belts	131
Brad Point Wood Drill Bits	36	Nylon Loop Discs	132
Frame Drill Bits	36	Extreme Fibre Discs	133
TCT Hinge Boring Bits	36	DeWALT® Flap Discs	134
Wood Auger Drill Bits	37	Honing Belts	134
Self Feed Drill Bits	37	Pads & Bonnets	135
Flatwood Drill Bits	38	'Quick Fit' Platens	135
EXTREME DeWALT® Flat Wood Drill Bits	39	Angle Grinder Polishing Bonnets	135
EXTREME DeWALT® 406mm Flat Wood Drill Bits	39	Bonded Abrasives	136
Holesaws	40	Metal Cutting and Grinding Discs	137
Bi-Metal Deep Cut Holesaws	41	Chop Saw Wheel	137
Holesaw Mandrels and Accessories	42	High Speed Metal Cutting Discs	138
Bi-Metal Holesaw Sets	42	Stainless Steel & Thin Metal Cutting Discs	138
Quick Change Mandrels and Accessories	43	Aluminium Cutting Discs	138
Carbide Grit Holesaws	43	High Speed Stone Cutting Discs	139
Holesaw Mandrels and Accessories	44	Stone Cutting and Grinding Discs	139
Carbide Grit Holesaw Sets	44	Grinding Wheels & Honing Wheels	139
Drilling Accessories	44	Wire Brushes	140
Mixer Tools	44	Diamond Discs	141
Chucks & Keys	45	Laser Blades	144
Screwdriving	46	Dry Diamond Discs	147
Screwdriving Accessories	48	Wet Diamond Tile Saw	148
DeWALT 'Flip & Drive' Units	53	Diamond Drills	149
Pilot Bits	53	Dry Diamond Core Drills & Dosensenker	150
Countersink & Pilot	53	Wet Diamond Core Bits	151
Drilling Sets	54	Adapters, Extension Rods & Pilot Bits	152
Screwdriving Sets	56	Diamond Tile Drill Bits	153
Tough Case Storage	57	Nailer Accessories	154
Circular Saw Blades	60	Nails	155
EXTREME DeWALT® Stationary Circular Saw Blades	62	Staples	156
Portable Circular Saw Blades	70		
EXTREME DeWALT® Portable Circular Saw Blades	74		
Cordless Circular Saw Blades	78		
Insert Rings	78		
Circular Saw Blade Guide	80		

IN STORE MERCHANDISING AND DISPLAY SYSTEM



- FLEXIBLE, MODULAR SYSTEM
- CLEAR PRODUCT DIFFERENTIATION AND COMMUNICATION
- STRONG DeWALT BRANDING

PROFESSIONAL PACKAGING

- STRONG ROBUST PACKAGING FITS INDUSTRIAL USER'S REQUIREMENTS
- ON PACK COMMUNICATION WITH ICONS - CLEAR AND SIMPLE
- CLEAR DIFFERENTIATION BETWEEN STANDARD AND "EXTREME DeWALT" PRODUCT
- PRODUCT STORAGE

ABRASIVES



JIGSAW BLADES



HAMMER BITS




METAL BITS



CIRCULAR SAW BLADES



SCREWDRIVER BITS



TOUGH CASES



HOLESAWS



POINT-OF-SALE STRIPS



ENVIRONMENTAL

DeWALT recognises and respects the balance between industry and a healthy and sustainable environment. Our role in this balance is to manufacture our products in a way that preserves the quality of our environment for ourselves and our children, while providing employees with clean and safe working conditions.

We are committed to striving for excellence in environment, health and safety management through process improvements, advanced manufacturing techniques and pollution control practices. We expect our managers and employees to maintain our facilities at the highest standards, minimise waste generation, re-use and recycle materials and products where possible and comply with all applicable laws and regulations.

DeWALT is constantly striving to maintain the highest quality of its products by implementing rigorous product development and manufacturing controls such as Six Sigma and ISO certification.

All measurements are in mm unless otherwise stated.
DeWALT reserves the right to revise product specifications at any time without notice.
Prices are correct as of going to print. However, DeWALT reserves the right to change these, be it a price increase or decrease.

Symbols

 All products shown are in compliance with the appropriate European regulations.

DeWALT DRILLING SYSTEMS

DeWALT is a market-leading manufacturer of high performance power tools and accessories that provide a fully integrated drilling system for masonry, metal and wood. Its dedicated accessories factory in Germany was established in 1959 and now employs over 200 people, producing more than 50 million drill bits every year.

MANUFACTURING

To ensure maximum performance and customer satisfaction, DeWALT drill bits undergo the most rigorous manufacturing and testing procedures (including computer controlled milling) and the most advanced production and quality management processes. DeWALT not only produces its own bits, it even designs the machines that make them.

PRODUCT DEVELOPMENT

By talking continuously to its customers, DeWALT has gained a comprehensive knowledge of user needs and applications. Its world-class development facility utilises the latest Catia CAD system and automated test equipment to develop and test all drill bits prior to and during manufacture.

QUALITY CONTROL

DeWALT is a long-standing member of PRUF GEMEINSCHAFT MAUERBOHRER (PGM), an internationally recognised organisation that verifies the suitability of drill bits for use in anchor fixing. All drill bits are certified to the latest ISO 9001: 2000 quality standards and high technology testing machinery is used for the control of variables.

COMING IN 2009

FULL HEAD CARBIDE

In 2009, DeWALT launches its most advanced SDS+ drill bit to date. Designed to perform in the hardest applications with today's new generation of harder hitting, more powerful hammers, the new DeWALT XLR Full Head Carbide drill bits offer the ultimate in drill bit durability and life. Available in diameters from 5mm to 12mm and lengths of 100mm up to 460mm the new DeWALT XLR Full Head Carbide SDS+ drill bit range covers all major fixing applications.

Manufactured in our own factory using top quality materials the DeWALT XLR Full Head Carbide SDS+ drill bit range combines a solid carbide drill bit tip for Extreme life and durability with a unique 4 flute spiral, ensuring constant drilling speed and efficient debris removal. The flute and tip are bonded using a new innovative handling system which bonds to the materials as one to offer the greatest durability and longest life available from DeWALT to date.

XTRA LIFE & RELIABILITY

1 Manufactured in our own plant in Germany using only the best European Steel and advanced manufacturing techniques

2 4 FLUTE SPIRAL
4 separate channels on the flute give the optimum debris removal without compromising on drill bit durability, even in use with the hardest hitting hammers



3 4 CUTTER GEOMETRY
For cleaner, more concentric holes for the ultimate in fixing retention

4 SOLID CARBIDE HEAD
Longest life & Extreme durability in the toughest applications



INNOVATIVE BONDING SYSTEM

The tip and the flute are bonded as one to offer the highest standards available in SDS+ drill bit durability



MASONRY AND CONCRETE DRILLING

MASONRY BITS



For rotary/percussion drilling in masonry, brick/block work, natural stone, tiles, light concrete. Usage as for masonry bits.

EXTREME DeWALT® MASONRY BITS



For rotary/percussion drilling in masonry, brick/block work, natural stone. For anchors, plastic plugs, fixings and pipework clearance.

SDS-PLUS EXTREME DeWALT® 2 HAMMER BITS



High performance long-life SDS-Plus hammer bit. Suitable for masonry, stone and concrete.

SDS-PLUS EXTREME DeWALT® XLR FULL HEAD CARBIDE



The ultimate in SDS Plus life and durability, designed for users with the hardest applications in masonry, stone and granite.

SDS-PLUS 4-CUTTER BITS



For fixing holes and through holes 16mm - 30mm.

SDS-MAX HAMMER BITS



For SDS-Max drive hammer drills. Suitable for masonry, stone and concrete.

CHISELS



For electro-pneumatic chiselling machines. Applications include demolition, channelling, surface preparation in masonry, stone, concrete, brick/block work.

CORE DRILLS (TCT)



For clean, round rotary drilling in light concrete, brick/block work. Available for SDS+ & SDS Max systems

SDS-PLUS

The range of SDS+ Extreme Masonry drill bits possesses some important New design features which deliver the very best in DURABILITY and RELIABILITY as well as consistent performance in terms of bit life and drilling speed.

4 Flute Spiral enabling faster debris removal and outstanding durability

New optimized carbide tip geometry for increased durability and longer life



SDS-MAX

DeWALT's comprehensive range includes the EXTREME DeWALT® SDS-MAX hammer bits, which deliver a class leading combination of drilling speed and durability through features such as a four flute spiral with maximised entry to all flutes and a low friction head design.

4-Flute Spiral with Maximized Flute Entry
Maximizes drilling speed and debris removal

Maximized Central Core
Increased energy transmission

Fully Supported Head
Greater durability

Multi-Cutter Head
Reduced vibration

Low Friction Head Design
Increased drilling speed



Open Head Design
Rapid debris removal

SUITABLE FOR MASONRY CONCRETE, BRICK OR BLOCK WORK



Concrete




Brick




Block

DRILLING SYSTEMS

SDS-PLUS SYSTEM




SDS-MAX SYSTEM



19MM HEX SYSTEM



28MM HEX SYSTEM




SHANK FITMENTS

For use with

- DeWALT: DC212N, DC212KA, DC213KA, DC213KB, DC22KA, DC222KB, DC223KA, DC224KA, DC224KB, DC234KL, DC232KL, D25112K, D25113K, D25114K, D25213K, D25313K, D25314K, D25315K, D25404K, D25405K, D25330K, DC228/229KL
- Atlas Copco: PFH 200E, PHE20R, PHE20RL-N, PHLE20, RL-N2, PHE20RL-MF2, PHE24R, PHE24RX, PHE26R, PHE26RA, PHERX2, PHE26, PFH24
- Bosch: GBH 2-18, GBH 2-22RE, GBH 2-26RE, GBH 2-26DRE, GBH 2-26DFR, GAH 500DSR, GBH 24V,


- GBH 24VRE, GBH 24VFR, GBH 3-28E, GBH 3-28FE, GSH 3E, GBH 4DFE, GBH 4DSC
- Hiiti: TE2, TE2-S, TE2-M, TE2-A, TE6-S, TE6-C, TE6-A, TE7-A, TE7-C, TE7-S, TE16, TE16-C, TE16-M, TE35C, TE104
- Hitachi: DH24DV, DH24PB3, DH24PC3, DH25PB, DH30PC, H25PV
- Kango: 285, 200, 426, 430D
- Makita: HK0500, HR2010, HR2020, HR2410, HR2420, HR2430, HR2431, HR2432, HR2440, HR2440F, HR2445, HR2450, HR2450T, HR2450F, HR2450FT, HR2455, HR2510, HR3000C, HR1830, BHR200WAE, BHR200SAJ, BHR200SJE



- Metabo: UBH2/20RLE, PB E501/2S-R-L, PBE701/2 SR+L Signal, BHE6010 S-E+L, BHE6012 S-R+L, BHE6020 S-R+L, BHE6026 S-R+L Signal, UHE 22 Multi, UHE 28 Multi, BHE6024, BHE 20 SR, BHE6009 S, BHE6011, S-R+L, BHE 6015 S-R+L, BHE 24 SR, BHE 6021 S-R+L, BHE6024 S-R+L, BHE6028 S-R+L, KHE 32

- DeWALT: D25500K, D25600K, D25830K, D25700K, D25701K, D25840K, D25730K, D25900K, D25899K, D25901K
- Atlas Copco: PH5S, PHE 7 S, PHE50S
- Bosch: GBH 5-38 DE, GBH 5-40 DE, GBH 7-46 DE, GBH 11 DE, GSH 5E, GSH 11 E, GSH 500
- Hiiti: TE56, TE56-ATC, TE76P, TE76P-ATC, TE505


- TE706-AVR, TE706
- Hitachi: DH40MR, DH45MR, DH50MB, H45MR, H60MA, H60MB
- Makita: HM0860C, HM1202C, HR4000C, HR4001C, HR4010C, HR4011C, HR4500C, HR5001C
- Metabo: BHE 6045 S



19mm Hexagon shank

- DeWALT: D25940K, D25941K
- Atlas Copco: PB14D


- Kango: 637, 638
- Makita: HM1200B




28mm Hexagon shank

- DeWALT: D25980K, D25980K
- Bosch: GSH27

- Makita: HM1304B
- Hitachi: H70SD



DRILL BIT SELECTION



DeWALT offers you a wide range of drill bits for diverse applications.

To achieve maximum cost efficiency, productivity, bit/tool life and hole accuracy with your DeWALT drill bit, careful selection and the use of correct speeds and feeds are essential.

The following tables outline specific guidelines on bit selection, and optimum feed/speed rates to achieve satisfaction with your DeWALT drill bit.

STEP 1

Select the correct bit, material group, surface speed and coolant for your application from table 1.

STEP 2

From table 2 select the correct feed rate for the material group and bit diameter.

STEP 3

Use table 3 to convert surface speed to RPM.

STEP 4

Carry-out the application using the correct bit, RPM, feed rate & coolant.

DRILL BIT SELECTION

Table 1/Material Groups

Material Group	Material Description	Recommended Bit Selection	Point Angle	Cutting Speed	Coolant
Cold Worked Steel					
4	Non Alloyed steel up to 600N/mm²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	30-40	Emulsion
4	Non Alloyed steel up to 600-800N/mm²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	25-35	Emulsion
4	Steel sheet up to 800N/mm²	EXTREME DeWALT® 2 Metal	Split point	-	Emulsion
4	Non Alloyed Tool Sheet upto 800N/mm²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	20-30	Emulsion
4	Alloyed Tool sheet 700-800N/mm²	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	10-15	Emulsion
3	Alloyed Tool Sheet 800-1000N/mm²	HSS-R/HSS-G/ HSS-CO EXTREME DeWALT® Cobalt	118°/130°	8-12	Oil
2	Alloyed Tool Sheet 1000-1200N/mm²	HSS-CO EXTREME DeWALT® Cobalt	130°	6-10	Oil
1	Spring Steel	HSS-CO EXTREME DeWALT® Cobalt	130°	5-10	Oil
3	Stainless Steel (Austenitic) 500-800N/mm²	HSS-CO EXTREME DeWALT® Cobalt	130°	5-10	Oil
2	Heat Resistant Steel up to 800N/mm²	HSS-CO EXTREME DeWALT® Cobalt	130°	5-15	Oil
5	Cast Iron up to 250N/mm²	HSS-G/HSS-CO EXTREME DeWALT® Cobalt	118°/130°	15-25	Emulsion/Air
Non Ferrous Metal					
5	Copper Non Alloyed	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	30-40	Emulsion
5	Copper Alloyed	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	25-35	Emulsion
6	Aluminium Alloyed & Non alloyed	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	40-100	Emulsion
6	Cast Aluminium	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	40-65	Emulsion
3	Titanium & Titanium Alloys	HSS-CO EXTREME DeWALT® Cobalt	130°	3-60	Oil
5	Brass (long chippings)	HSS-R/HSS-G/EXTREME DeWALT® 2 Metal	118°/Split point	30-40	Emulsion
6	Brass (short chippings)	EXTREME DeWALT® 2 Metal	Split point	40-60	Emulsion
4	Bronze	HSS-G/HSS-CO EXTREME DeWALT® Cobalt/ EXTREME DeWALT® 2 Metal	118°/Split point	25-35	Emulsion
5	Aluminium, Copper, Brass sheet	EXTREME DeWALT® 2 Metal	Split point	-	Emulsion
6	Magnesium & Mrg. Alloys	EXTREME DeWALT® 2 Metal	Split point	60-100	Emulsion
Plastic/Synthetic Material					
6	Thermoplastic- PVC, Plexiglass, Polymide	HSS-R/HSS-G/ EXTREME DeWALT® 2 Metal	118°/Split point	20-40	Air
4	Duroplastic, Bakelite, Hard rubber	HSS-R/HSS-G/ EXTREME DeWALT® 2 Metal	118°/Split point	15-20	Air
Stone/Masonry					
	Red brick, Gasbeton, Ziegal	All Conc/Masonry bits	130°/EXTREME DeWALT® Tip -		Air
	Hard Brick, Klinker, Sandlime block	All Conc/Masonry bits	130°/EXTREME DeWALT® Tip -		Air
	Light Concrete	All Conc/Masonry drill bits	130°/EXTREME DeWALT® Tip -		Air
	Hard/Reinforced Concrete	SDS-Plus EXTREME DeWALT® 2/SDS-Plus	130°/EXTREME DeWALT® Tip -		Air
	Natural Stone (Granite/Marble)	EXTREME DeWALT® Masonry/ SDS-Plus EXTREME DeWALT® 2	EXTREME DeWALT® Tip	*	Air
	Slate	EXTREME DeWALT® Masonry	EXTREME DeWALT® Tip	*	Air
	Wall Tiles (Soft Ceramic)	EXTREME DeWALT® Masonry	EXTREME DeWALT® Tip	*	Air
	Floor Tiles (Hard Ceramic)	EXTREME DeWALT® Masonry/ SDS-Plus EXTREME DeWALT® 2	EXTREME DeWALT® Tip	*	Air

* Low RPM without percussion or hammer action when drilling tiles

Table 2 / Recommended Feed Rates

Feedrate (mm/REV) by bit diameter & Material Group																
Material Group	Ø 1	Ø 2	Ø 2.5	Ø 3	Ø 4	Ø 5	Ø 6	Ø 8	Ø 10	Ø 12	Ø 16	Ø 20	Ø 25	Ø 30	Ø 40	Ø 50
1	0.004	0.02	0.02	0.03	0.04	0.05	0.05	0.06	0.08	0.1	0.12	0.12	0.16	0.2	0.2	0.25
2	0.006	0.02	0.03	0.04	0.05	0.05	0.06	0.08	0.1	0.12	0.16	0.16	0.2	0.25	0.25	0.3
3	0.008	0.03	0.04	0.05	0.06	0.06	0.08	0.1	0.12	0.13	0.2	0.2	0.25	0.3	0.3	0.4
4	0.01	0.04	0.05	0.06	0.08	0.1	0.1	0.12	0.16	0.2	0.25	0.25	0.3	0.4	0.4	0.5
5	0.01	0.05	0.06	0.08	0.1	0.1	0.12	0.16	0.2	0.25	0.3	0.3	0.4	0.5	0.5	0.6
6	0.012	0.06	0.08	0.1	0.12	0.12	0.16	0.2	0.25	0.25	0.4	0.4	0.5	0.6	0.6	0.8

DRILL BIT SELECTION

Table 3/Recommended Surface Speed and RPM

Surface speed m/min

Ø mm	4	6	8	10	12	15	18	20	25	30	35	40	50
1	1273	1909	2545	3182	3818	4773	5727	6364	7955	9545	11136	12727	15909
1.5	848	1273	1607	2121	2545	3182	3818	4242	5303	6364	7424	8485	10606
2	636	955	1273	1591	1909	2386	2864	3182	3977	4773	5568	6364	7955
2.5	509	764	1018	1273	1527	1909	2291	2545	3182	3818	4455	5091	6364
3	424	636	848	1061	1273	1591	1909	2121	2652	3182	3712	4242	5303
3.5	364	545	727	909	1091	1364	1636	1818	2273	2727	3182	3636	4545
4	318	477	636	795	955	1193	1432	1591	1989	2386	2784	3182	3977
4.5	283	424	566	707	848	1061	1273	1414	1768	2121	2475	2828	3535
5	255	382	509	636	764	955	1145	1273	1591	1909	2227	2545	3182
5.5	231	347	463	579	694	868	1041	1157	1446	1736	2025	2314	2893
6	212	318	424	530	636	795	955	1061	1326	1591	1856	2121	2652
6.5	196	294	392	490	587	734	881	979	1224	1469	1713	1958	2448
7	182	273	364	455	545	682	818	909	1136	1364	1591	1818	2273
7.5	170	255	339	424	509	636	764	848	1061	1273	1485	1697	2121
8	159	239	318	398	477	597	716	795	994	1193	1392	1591	1989
8.5	150	225	299	374	449	561	674	749	936	1123	1310	1497	1872
9	141	212	283	354	424	530	636	707	884	1061	1237	1414	1768
9.5	134	201	268	335	402	502	603	670	837	1005	1172	1340	1675
10	127	191	255	318	382	477	573	636	795	955	1114	1273	1591
11	116	174	231	289	347	434	521	579	723	868	1012	1157	1446
12	106	159	212	265	318	398	477	530	663	795	928	1061	1326
13	98	147	196	245	294	367	441	490	612	734	857	979	1224
14	91	136	182	227	273	341	409	455	568	682	795	909	1136
15	85	127	170	212	255	318	382	424	530	636	742	848	1061
16	80	119	159	199	239	298	358	398	497	597	696	795	994
17	75	112	150	187	225	281	337	374	468	561	655	749	936
18	71	106	141	177	212	265	318	354	442	530	619	707	884
19	67	100	134	167	201	251	301	335	419	502	586	670	837
20	64	95	127	159	191	239	286	318	398	477	557	636	795
21	61	91	121	152	182	227	273	303	379	455	530	606	758
22	58	87	116	145	174	217	260	289	362	434	506	579	723
23	55	83	111	138	166	208	249	277	346	415	484	553	692
24	53	80	106	133	159	199	239	265	331	398	464	530	663
25	51	76	102	127	153	191	229	255	318	382	445	509	636
26	49	73	98	122	147	184	220	245	306	367	428	490	612
27	47	71	94	118	141	177	212	236	295	354	412	471	589
28	45	68	91	114	136	170	205	227	284	341	398	455	568
29	44	66	88	110	132	165	197	219	274	329	384	439	549
30	42	64	85	106	127	159	191	212	265	318	371	424	530
31	41	62	82	103	123	154	185	205	257	308	359	411	513
32	40	60	80	99	119	149	179	199	249	298	348	398	497
33	39	58	77	96	116	145	174	193	241	289	337	386	482
34	37	56	75	94	112	140	168	187	234	281	328	374	468
35	36	55	73	91	109	136	164	182	227	273	318	364	455
36	35	53	71	88	106	133	159	177	221	265	309	354	442
37	34	52	69	86	103	129	155	172	215	258	301	344	430
38	33	50	67	84	100	126	151	167	209	251	293	335	419
39	33	49	65	82	98	122	147	163	204	245	286	326	408
40	32	48	64	80	95	119	143	159	199	239	278	318	398
41	31	47	62	78	93	116	140	155	194	233	272	310	388
42	30	45	61	76	91	114	136	152	189	227	265	303	379
43	30	44	59	74	89	111	133	148	185	222	259	296	370
44	29	43	58	72	87	108	130	145	181	217	253	289	362
45	28	42	57	71	85	106	127	141	177	212	247	283	354
46	28	42	55	69	83	104	125	138	173	208	242	277	346
47	27	41	54	68	81	102	122	135	169	203	237	271	338
48	27	40	53	66	80	99	119	133	166	199	232	265	331
49	26	39	52	65	78	97	117	130	162	195	227	260	325
50	25	38	51	64	76	95	115	127	159	191	223	255	318

USEFUL DRILL BIT SIZES

Metric Coarse DIN 13

Size	Thread Pitch	Tap Drill Dia
1.0	0.25	0.75
1.1	0.25	0.85
1.2	0.25	0.95
1.4	0.30	1.10
1.6	0.35	1.25
1.8	0.35	1.45
2.0	0.40	1.60
2.2	0.45	1.75
2.5	0.45	2.05
3.0	0.50	2.50
3.5	0.60	2.90
4.0	0.70	3.30
4.5	0.75	3.70
5.0	0.80	4.20
6.0	1.00	5.00
7.0	1.00	6.00
8.0	1.25	6.80
9.0	1.25	7.80
10.0	1.50	8.50
11.0	1.50	9.50
12.0	1.75	10.20
14.0	2.00	12.00
16.0	2.00	14.00
18.0	2.50	15.50
20.0	2.50	17.50
22.0	2.50	19.50
24.0	3.00	21.00
27.0	3.00	24.00
30.0	3.50	26.50
33.0	3.50	29.50
36.0	4.00	32.00
39.0	4.00	35.00
42.0	4.40	37.50
45.0	4.40	40.50
48.0	5.00	43.00
52.0	5.00	47.00
56.0	5.50	50.50
60.0	5.50	54.50
64.0	6.00	58.00
68.0	6.00	62.00

Metric Fine DIN 13

Size	Tap Drill Dia
2.0 x 0.25	1.75
2.2 x 0.25	1.95
2.3 x 0.25	2.05
2.5 x 0.35	2.15
2.6 x 0.35	2.20
3.0 x 0.35	2.65
3.5 x 0.35	3.15
4.0 x 0.35	3.65
4.0 x 0.50	3.50
5.0 x 0.50	4.50
6.0 x 0.50	5.50
6.0 x 0.75	5.20
7.0 x 0.75	6.20
8.0 x 0.50	7.50
8.0 x 0.75	7.20
8.0 x 1.00	7.00
9.0 x 0.75	8.20
9.0 x 1.00	8.00

Metric Fine DIN 13

Size	Tap Drill Dia
10 x 0.50	9.50
10 x 0.75	9.20
10 x 1.00	9.00
10 x 1.25	8.80
11 x 1.00	10.00
12 x 0.75	11.20
12 x 1.00	11.00
12 x 1.25	10.80
12 x 1.50	10.50
13 x 1.00	12.00
14 x 1.00	13.00
14 x 1.80	12.80
14 x 1.50	12.50
15 x 1.00	14.00
15 x 1.50	13.50
16 x 1.00	15.00
16 x 1.50	14.50
18 x 1.00	17.00
18 x 1.50	16.50
18 x 2.00	16.00
20 x 1.00	19.00
20 x 1.50	18.50
20 x 2.00	18.00
22 x 1.00	21.00
22 x 1.50	20.50
22 x 2.00	20.00
24 x 1.00	23.00
24 x 1.50	22.50
24 x 2.00	22.00
25 x 1.00	24.00
25 x 1.50	23.50
26 x 1.50	24.50
28 x 2.00	26.00
30 x 1.00	29.00
30 x 1.50	28.50
30 x 2.00	28.00
32 x 1.50	30.50
33 x 1.50	31.50
33 x 2.00	31.00
34 x 1.50	32.30
35 x 1.50	33.40
36 x 1.50	34.40
36 x 2.00	34.00
36 x 3.00	33.00
38 x 1.50	36.50
39 x 1.50	37.50
39 x 2.00	37.00
39 x 3.00	36.00
40 x 1.50	38.50
40 x 2.00	38.00
40 x 3.00	37.00
42 x 1.50	40.40
42 x 2.00	40.00
42 x 3.00	39.00
45 x 1.50	43.40
45 x 2.00	43.00
45 x 3.00	42.00
48 x 1.50	46.50
48 x 2.00	46.00


Metric Fine DIN 13

Size	Tap Drill Dia
48 x 3.00	45.00
50 x 1.50	48.50
50 x 2.00	48.00
50 x 3.00	47.00
52 x 1.50	50.50
52 x 2.00	50.00
52 x 3.00	49.00

Whitworth G Threads DIN ISO 228/1

Size	Thread Pitch	Tap Drill Dia
G 1/8"	28	8.80
G 1/4"	19	11.80
G 3/8"	19	15.25
G 1/2"	14	19.00
G 5/8"	14	21.00
G 3/4"	14	24.50
G 7/8"	14	28.25
G 1"	11	30.75
G 1 1/8"	11	35.30
G 1 1/4"	11	39.25
G 1 3/8"	11	41.70
G 1 1/2"	11	45.25
G 1 3/4"	11	51.00
G 2"	11	57.00
G 2 1/4"	11	63.10
G 2 1/2"	11	72.60
G 2 3/4"	11	78.90
G 3"	11	85.30
G 3 1/4"	11	91.50
G 3 1/2"	11	97.70
G 3 3/4"	11	104.00
G 4"	11	110.40

MASONRY DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6500QZ	3	60	28	1	1	5011402382309	1.04
DT6504QZ	4	75	38	1	1	5011402372379	1.06
DT6501QZ	4.5	85	44	1	1	5011402372393	1.00
DT6505QZ	5	85	44	1	1	5011402372416	1.16
DT6502QZ	5.5	85	44	1	1	5011402372454	1.19
DT6552QZ	5.5	150	82	1	1	5011402372478	1.60
DT6506QZ	6	100	54	1	1	5011402372492	1.34
DT6556QZ	6	150	82	1	1	5011402372515	1.98
DT6606QZ	6	200	135	1	1	5011402372539	2.24
DT6503QZ	6.5	100	54	1	1	5011402372553	1.36
DT6603QZ	6.5	200	135	1	1	5011402372591	2.35
DT6507QZ	7	100	54	1	1	5011402372614	1.41
DT6557QZ	7	150	82	1	1	5011402372638	2.14
DT6508QZ	8	120	67	1	1	5011402372676	1.50
DT6558QZ	8	150	82	1	1	5011402372690	2.14
DT6608QZ	8	200	135	1	1	5011402372713	2.54
DT6708QZ	8	400	230	1	1	5011402372737	5.08
DT6509QZ	9	120	67	1	1	5011402372751	2.20
DT6609QZ	9	200	135	1	1	5011402372799	2.69
DT6510QZ	10	120	67	1	1	5011402372836	2.20
DT6560QZ	10	150	82	1	1	5011402372850	2.14
DT6610QZ	10	200	135	1	1	5011402372874	2.70
DT6710QZ	10	400	230	1	1	5011402372898	5.67
DT6732QZ	10	600	400	1	1	5011402382361	6.88
DT6561QZ	11	150	82	1	1	5011402372911	2.54
DT6562QZ	12	150	82	1	1	5011402372935	2.92
DT6612QZ	12	200	135	1	1	5011402372959	3.75
DT6712QZ	12	400	230	1	1	5011402372973	6.72
DT6733QZ	12	600	400	1	1	5011402382378	7.16
DT6563QZ	13	150	82	1	1	5011402372997	3.07
DT6713QZ	13	400	230	1	1	5011402373031	7.59
DT6564QZ	14	150	82	1	1	5011402373055	3.07
DT6714QZ	14	400	230	1	1	5011402373093	8.23
DT6734QZ	14	600	400	1	1	5011402382385	7.86
DT6565QZ	15	150	82	1	1	5011402373116	5.26
DT6566QZ	16	150	82	1	1	5011402373130	5.79
DT6716QZ	16	400	230	1	1	5011402373154	8.63
DT6735QZ	16	600	400	1	1	5011402382392	10.75
DT6718QZ	18	400	230	1	1	5011402373192	11.15
DT6736QZ	18	600	400	1	1	5011402382408	12.63
DT6720QZ	20	400	230	1	1	5011402373239	11.82
DT6737QZ	20	600	400	1	1	5011402382415	13.93

MASONRY DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6952QZ	5 piece set in plastic cassette	4, 5, 6, 8, 10	5	1	5011402373413	7.85

**FOR USE WITH
ROTARY OR
PERCUSSION
DRILLS (CORDED
& CORDLESS)**



APPLICATIONS

- Typically used for drilling anchor, plastic plug, fixing or pipework clearance holes.
- Suitable for masonry, brick/blockwork, stone.


FEATURES

- Rotary/percussion masonry drill bit 130° Douglas form carbide tip.
- Shank diameter of drill bits 10-13 mm is reduced to 9.5 mm.
- Shank diameter of drill bits larger than 13 mm is reduced to 12.7 mm.





FOR USE WITH
ROTARY OR
PERCUSSION
DRILLS (CORDED
& CORDLESS)




APPLICATIONS

- Typically used for drilling anchor, plastic plug, fixing or pipework clearance holes.
- Suitable for masonry, brick, stone, tiles and light concrete.

FEATURES

- Lasts up to 2x longer and delivers up to 50% more holes per charge than a standard masonry bit.
- Unique Carbide Grade - optimum grade maximises durability.




APPLICATIONS

- Suitable for wood, plastics, mild steel and non ferrous metals and masonry.
- For use in rotary or percussion drilling modes.

FEATURES

- Unique 120° tip grind for maximum sharpness.
- Fully supported carbide head gives faster drilling and extended life.
- Non slip shank ensures better retention in chuck.


EXTREME DeWALT® MASONRY DRILL BITS SINGLE PACKS

							
Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6695QZ	3	110	70	1	1	5035048061879	2.25
DT6699QZ	3.5	110	70	1	1	5035048014028	NOT UK
DT6696QZ	4	110	70	1	1	5035048061886	2.30
DT6671QZ	4	75	50	1	1	5035048060568	2.15
DT6672QZ	5	85	50	1	1	5035048060575	2.17
DT6673QZ	5	150	100	1	1	5035048060582	3.42
DT6674QZ	5.5	85	50	1	1	5035048060599	2.30
DT6675QZ	6	100	60	1	1	5035048060605	2.37
DT6676QZ	6	150	100	1	1	5035048060612	3.17
DT6677QZ	6	200	150	1	1	5035048060629	3.94
DT6678QZ	6.5	100	60	1	1	5035048060636	2.41
DT6679QZ	6.5	150	100	1	1	5035048060643	3.42
DT6680QZ	7	100	60	1	1	5035048060650	2.80
DT6681QZ	7	150	100	1	1	5035048060667	3.42
DT6682QZ	8	120	80	1	1	5035048060674	2.80
DT6683QZ	8	200	150	1	1	5035048060681	4.07
DT6684QZ	9	120	80	1	1	5035048060698	4.20
DT6685QZ	10	120	80	1	1	5035048060704	3.60
DT6686QZ	10	200	150	1	1	5035048060711	4.29
DT6687QZ	12	150	100	1	1	5035048060728	5.01
DT6688QZ	12	200	150	1	1	5035048060735	6.00
DT6689QZ	13	150	100	1	1	5035048060742	6.50
DT6690QZ	14	150	100	1	1	5035048060759	7.64
DT6691QZ	14	200	150	1	1	5035048060766	8.72
DT6692QZ	16	150	100	1	1	5035048060773	9.25
DT6693QZ	16	200	150	1	1	5035048060780	9.31

EXTREME DeWALT® MASONRY DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6956QZ	5 piece set in plastic cassette.	4,5,6,8,10	5	1	5035048060797	11.82
DT7928QZ	Ph2x4, Pz2x4, Ph2x50mm, Pz2x50mm, Slotted 5.5x50mm, Magnetic holder, Magnetic drive guide.	4, 5, 5.5, 6, 7, 8	19	1	5035048060803	49.48
DT7928BQZ	Blister Pack				5035048072219	49.48

MULTI MATERIAL DRILL BITS


								
Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)	
DT6515QZ	3	113	83	1	1	5035048066010	2.14	
DT6516QZ	3.5	113	83	1	1	5035048066027	2.36	
DT6517QZ	4	103	73	1	1	5035048066034	2.68	
DT6518QZ	5	113	83	1	1	5035048066041	2.81	
DT6527QZ	5.5	113	83	1	1	5035048077504	2.69	
DT6528QZ	5.5	200	170	1	1	5035048077511	3.27	
DT6519QZ	6	123	93	1	1	5035048066058	3.05	
DT6529QZ	6	200	170	1	1	5035048077528	3.70	
DT6520QZ	6.5	123	93	1	1	5035048066065	3.32	
DT6530QZ	6.5	200	170	1	1	5035048077535	4.04	
DT6521QZ	7	123	93	1	1	5035048066072	3.91	
DT6522QZ	8	134	104	1	1	5035048066089	4.03	
DT6531QZ	8	200	170	1	1	5035048077542	4.92	
DT6523QZ	9	134	104	1	1	5035048066096	4.28	
DT6524QZ	10	134	104	1	1	5035048066102	4.39	
DT6533QZ	10	200	170	1	1	5035048077559	4.61	
DT6525QZ	12	153	123	1	1	5035048066119	5.89	
DT6526QZ	13	160	130	1	1	5035048066126	8.68	

SDS-PLUS EXTREME DeWALT® 2 DRILL BITS SINGLE PACKS



WORKING LENGTH mm

DIAMETER mm




LENGTH mm

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT9625QZ	3	135	75	1	1	5035048014011	NOT UK
DT9500QZ	3.5	110	50	1	1	5035048054758	5.40
DT9502QZ	4	110	50	1	1	5035048054772	3.28
DT9503QZ	4	160	100	1	1	5035048054789	5.07
DT9504QZ	5	110	50	1	1	5035048054796	2.91
DT9505QZ	5	160	100	1	1	5035048054802	3.45
DT9506QZ	5	210	150	1	1	5035048054819	5.15
DT9507QZ	5	310	250	1	1	5035048054826	8.83
DT9620QZ	5	460	400	1	1	5035048061855	18.34
DT9508QZ	5.5	110	50	1	1	5035048054833	3.01
DT9509QZ	5.5	160	100	1	1	5035048054840	3.30
DT9510QZ	5.5	210	150	1	1	5035048054857	4.84
DT9511QZ	5.5	260	200	1	1	5035048054864	6.58
DT9512QZ	5.5	310	250	1	1	5035048054871	8.95
DT9513QZ	5.5	460	400	1	1	5035048054888	20.22
DT9514QZ	6	110	50	1	1	5035048054895	3.02
DT9515QZ	6	160	100	1	1	5035048054901	3.45
DT9516QZ	6	210	150	1	1	5035048054918	4.86
DT9517QZ	6	260	200	1	1	5035048054925	7.41
DT9621QZ	6	310	250	1	1	5035048061862	8.65
DT9518QZ	6	460	400	1	1	5035048054932	19.40
DT9519QZ	6.5	110	50	1	1	5035048054949	3.18
DT9520QZ	6.5	160	100	1	1	5035048054956	3.59
DT9521QZ	6.5	210	150	1	1	5035048054963	3.82
DT9522QZ	6.5	260	200	1	1	5035048054970	8.41
DT9523QZ	6.5	310	250	1	1	5035048054987	9.53
DT9524QZ	7	110	50	1	1	5035048054994	3.49
DT9525QZ	7	160	100	1	1	5035048055007	3.75
DT9526QZ	7	210	150	1	1	5035048055014	5.65
DT9527QZ	7	260	200	1	1	5035048055021	6.19
DT9528QZ	8	110	50	1	1	5035048055038	3.50
DT9529QZ	8	160	100	1	1	5035048055045	3.89
DT9530QZ	8	210	150	1	1	5035048055052	4.53
DT9531QZ	8	260	200	1	1	5035048055069	7.41
DT9532QZ	8	310	250	1	1	5035048055076	8.94
DT9533QZ	8	410	350	1	1	5035048055083	14.15
DT9534QZ	8	460	400	1	1	5035048055090	13.00
DT9535QZ	8	600	540	1	1	5035048055106	18.94
DT9536QZ	9	160	100	1	1	5035048055113	5.03
DT9537QZ	9	210	150	1	1	5035048055120	6.66
DT9539QZ	10	110	50	1	1	5035048055144	3.62
DT9540QZ	10	160	100	1	1	5035048055151	4.25
DT9541QZ	10	210	150	1	1	5035048055168	5.09
DT9542QZ	10	260	200	1	1	5035048055175	6.87
DT9543QZ	10	310	250	1	1	5035048055182	5.79
DT9544QZ	10	350	300	1	1	5035048055199	8.00
DT9545QZ	10	460	400	1	1	5035048055205	12.31
DT9546QZ	10	600	550	1	1	5035048055212	17.11
DT9547QZ	10	1000	950	1	1	5035048055229	42.65
DT9548QZ	11	160	100	1	1	5035048055236	5.29
DT9549QZ	11	210	150	1	1	5035048055243	5.70
DT9550QZ	11	260	200	1	1	5035048055250	5.85
DT9551QZ	11	310	250	1	1	5035048055267	6.19
DT9552QZ	12	160	100	1	1	5035048055274	5.24
DT9553QZ	12	200	150	1	1	5035048055281	5.70
DT9554QZ	12	260	200	1	1	5035048055298	6.08
DT9555QZ	12	300	250	1	1	5035048055304	7.00
DT9556QZ	12	350	300	1	1	5035048055311	8.92
DT9557QZ	12	450	400	1	1	5035048055328	11.12
DT9558QZ	12	600	550	1	1	5035048055335	19.17



FOR USE WITH
SDS-PLUS
HAMMER DRILLS



APPLICATIONS

- Suitable for fast drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work.


FEATURES

- The innovative EXTREME DeWALT® 2 SDS+ drill bit is amongst the very best in terms of its durability drilling life and speed.
- The Superior carbide grade ensures a tip with outstanding durability which gives consistent drilling life.
- The NEW 4 FLUTE SPIRAL incorporates a maximized central core for increased durability and energy transmission.
- The 140° tip design ensures better bit penetration and longer life.
- Hardened Steel body for extra strength and reduced breakage.





FOR USE WITH
SDS-PLUS
HAMMER DRILLS



APPLICATIONS

- Suitable for fast drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work.


FEATURES

- The innovative EXTREME DeWALT® 2 SDS+ drill bit is amongst the very best in terms of its durability drilling life and speed.
- The Superior carbide grade ensures a tip with outstanding durability which gives consistent drilling life.
- The NEW 4 FLUTE SPIRAL incorporates a maximized central core for increased durability and energy transmission.
- The 140° tip design ensures better bit penetration and longer life.
- Hardened Steel body for extra strength and reduced breakage.



DRILLING


SDS-PLUS EXTREME DeWALT® 2 DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT95590Z	12	1000	950	1	1	5035048055342	44.96
DT95600Z	13	160	100	1	1	5035048055359	6.03
DT95610Z	13	200	150	1	1	5035048055366	6.02
DT95620Z	13	260	200	1	1	5035048055373	7.65
DT95630Z	13	300	250	1	1	5035048055380	8.57
DT95650Z	13	450	400	1	1	5035048055403	11.97
DT95660Z	14	160	100	1	1	5035048055410	7.02
DT95670Z	14	200	150	1	1	5035048055427	7.13
DT95680Z	14	260	200	1	1	5035048055434	7.82
DT95690Z	14	300	250	1	1	5035048055441	9.05
DT95700Z	14	450	400	1	1	5035048055458	13.43
DT95710Z	14	600	550	1	1	5035048055465	19.10
DT95720Z	14	1000	950	1	1	5035048055472	49.08
DT95730Z	15	160	100	1	1	5035048055489	6.69
DT95740Z	15	200	150	1	1	5035048055496	7.65
DT95750Z	15	260	200	1	1	5035048055502	9.00
DT95760Z	15	300	250	1	1	5035048055519	10.02
DT95770Z	15	450	400	1	1	5035048055526	13.49
DT95780Z	16	160	100	1	1	5035048055533	7.31
DT95790Z	16	200	150	1	1	5035048055540	8.64
DT95800Z	16	260	200	1	1	5035048055557	9.34
DT95810Z	16	300	250	1	1	5035048055564	11.01
DT95820Z	16	450	400	1	1	5035048055571	15.24
DT95830Z	16	600	550	1	1	5035048055588	23.14
DT95840Z	16	800	750	1	1	5035048055595	34.30
DT95850Z	16	1000	950	1	1	5035048055601	51.19
DT95860Z	17	200	150	1	1	5035048055618	16.18
DT95870Z	18	200	150	1	1	5035048055625	10.66
DT95880Z	18	250	200	1	1	5035048055632	11.81
DT95890Z	18	300	250	1	1	5035048055649	14.84
DT95900Z	18	450	400	1	1	5035048055656	21.37
DT95910Z	18	600	550	1	1	5035048055663	29.01
DT95920Z	18	800	750	1	1	5035048055670	47.48
DT95930Z	18	1000	950	1	1	5035048055687	68.14
DT95960Z	19	450	400	1	1	5035048055717	24.12
DT95970Z	20	200	150	1	1	5035048055724	12.12
DT95980Z	20	300	250	1	1	5035048055731	16.79
DT95990Z	20	450	400	1	1	5035048055748	24.32
DT96000Z	20	600	550	1	1	5035048055755	33.59
DT96010Z	20	1000	950	1	1	5035048055762	76.69
DT96020Z	22	250	200	1	1	5035048055779	18.70
DT96030Z	22	300	250	1	1	5035048055786	20.24
DT96040Z	22	450	400	1	1	5035048055793	26.64
DT96050Z	22	600	550	1	1	5035048055809	33.74
DT96060Z	22	800	750	1	1	5035048055816	52.63
DT96070Z	22	1000	950	1	1	5035048055823	84.12
DT96080Z	23	250	200	1	1	5035048055830	27.56
DT96090Z	24	250	200	1	1	5035048055847	21.17
DT96100Z	24	450	400	1	1	5035048055854	28.91
DT96110Z	25	250	200	1	1	5035048055861	23.22
DT96120Z	25	300	250	1	1	5035048055878	24.41
DT96130Z	25	450	400	1	1	5035048055885	30.12
DT96140Z	25	1000	950	1	1	5035048055892	89.34
DT96150Z	26	250	200	1	1	5035048055908	26.75
DT96160Z	26	450	400	1	1	5035048055915	31.85
DT96170Z	26	800	750	1	1	5035048055922	70.33
DT96180Z	30	250	200	1	1	5035048055939	40.54
DT96190Z	30	450	400	1	1	5035048055946	48.07

DRILLING

SDS-PLUS EXTREME DeWALT® 2 DRILL BITS BULK PACKS




Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT98000Z	5	110	50	10	1	5035048055953	27.21
DT98010Z	5	110	50	50	1	5035048055960	127.42
DT98030Z	5	160	100	10	1	5035048055984	33.01
DT98060Z	5.5	110	50	10	1	5035048056011	28.37
DT98090Z	5.5	160	100	10	1	5035048056042	30.36
DT98100Z	5.5	160	100	50	1	5035048056059	146.19
DT98120Z	6	110	50	10	1	5035048056073	27.80
DT98130Z	6	110	50	50	1	5035048056080	133.20
DT98140Z	6	110	50	100	1	5035048056097	241.84
DT98150Z	6	160	100	10	1	5035048056103	31.49
DT98160Z	6	160	100	50	1	5035048056110	155.19
DT98170Z	6	160	100	100	1	5035048056127	295.36
DT98180Z	6	210	150	10	1	5035048056134	46.33
DT98480Z	6	210	150	50	1	5035048013977	203.49
DT98190Z	6.5	110	50	10	1	5035048056141	28.96
DT98200Z	6.5	160	100	10	1	5035048056158	34.45
DT98210Z	6.5	160	100	50	1	5035048056165	165.05
DT98460Z	6.5	210	150	10	1	5035048013953	42.84
DT98470Z	6.5	210	150	50	1	5035048013960	214.20
DT98230Z	7	160	100	10	1	5035048056189	33.7
DT98240Z	7	160	100	50	1	5035048056196	165.63
DT98260Z	8	110	50	10	1	5035048056219	31.48
DT98270Z	8	160	100	10	1	5035048056226	36.48
DT98280Z	8	160	100	50	1	5035048056233	169.11
DT98290Z	8	160	100	100	1	5035048056240	315.06
DT98300Z	8	210	150	10	1	5035048056257	40.48
DT98310Z	8	260	200	10	1	5035048056264	72.39
DT98330Z	10	110	50	10	1	5035048056288	33.78
DT98340Z	10	160	100	10	1	5035048056295	40.54
DT98350Z	10	160	100	50	1	5035048056301	191.12
DT98370Z	10	210	150	10	1	5035048056325	46.27
DT98380Z	10	260	200	10	1	5035048056332	65.79
DT98390Z	12	160	100	10	1	5035048056349	49.22
DT98400Z	12	160	100	50	1	5035048056356	237.40
DT98410Z	12	200	150	10	1	5035048056363	52.99
DT98420Z	12	260	200	10	1	5035048056370	56.43
DT98430Z	14	160	100	10	1	5035048056387	55.60
DT98440Z	14	200	150	10	1	5035048056394	64.86

SDS-PLUS EXTREME DeWALT® 2 DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT97000Z	4 piece set in plastic cassette.	5,6,8,10	4	1	5035048056400	20.24
DT97010Z	7 piece set in metal cassette.	5,6x2,8x2,10,12	7	1	5035048056417	16.87
DT97020Z	4 piece set in plastic cassette.	5.5,7,8,10	4	1	5035048056424	16.87



FOR USE WITH
SDS-PLUS
HAMMER DRILLS



APPLICATIONS

- Suitable for fast drilling of plug, anchor or clearance holes in masonry, stone, concrete and brick/block work.


FEATURES

- The innovative EXTREME DeWALT® 2 SDS+ drill bit is amongst the very best in terms of its durability drilling life and speed.
- The Superior carbide grade ensures a tip with outstanding durability which gives consistent drilling life.
- The NEW 4 FLUTE SPIRAL incorporates a maximized central core for increased durability and energy transmission.
- The 140° tip design ensures better bit penetration and longer life.
- Hardened Steel body for extra strength and reduced breakage.





**FOR USE WITH
SDS-PLUS
HAMMER DRILLS**



APPLICATIONS

- Suitable for drilling plug & anchor holes in masonry, all types of stone and concrete.


FEATURES

- New solid carbide drill tip with optimised 4 cutter geometry offers the highest levels of drill bit life and durability from DeWALT to date.
- 4 cutter geometry drills a more concentric hole to offer the best fixing retention.
- 4 flute spiral aids consistent drilling speed and efficient debris removal.
- Unique bonding system joins the solid carbide head to the 4 flute spiral as one to ensure the highest standards available in DeWALT® SDS+ drilling to date.



DRILLING

EXTREME DeWALT® XLR FULL HEAD CARBIDE DRILL BITS SINGLE PACKS



**COMING
IN
2009**

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT89070Z	5	110	50	1	1	5035048077689	TBC
DT89080Z	5	160	100	1	1	5035048077696	TBC
DT89090Z	5	210	150	1	1	5035048077702	TBC
DT89100Z	5.5	110	50	1	1	5035048077719	TBC
DT89110Z	5.5	160	100	1	1	5035048077726	TBC
DT89120Z	6	110	50	1	1	5035048077733	TBC
DT89130Z	6	160	100	1	1	5035048077740	TBC
DT89140Z	6	210	150	1	1	5035048077757	TBC
DT89150Z	6	260	200	1	1	5035048077764	TBC
DT89160Z	6.5	160	100	1	1	5035048077771	TBC
DT89170Z	6.5	210	150	1	1	5035048077788	TBC
DT89180Z	6.5	260	200	1	1	5035048077795	TBC
DT89190Z	6.5	310	250	1	1	5035048077801	TBC
DT89200Z	7	160	100	1	1	5035048077818	TBC
DT89210Z	7	210	150	1	1	5035048077825	TBC
DT89220Z	8	110	50	1	1	5035048077832	TBC
DT89230Z	8	160	100	1	1	5035048077849	TBC
DT89240Z	8	210	150	1	1	5035048077856	TBC
DT89250Z	8	260	200	1	1	5035048077863	TBC
DT89260Z	8	310	250	1	1	5035048077870	TBC
DT89270Z	8	460	400	1	1	5035048077887	TBC
DT89280Z	10	160	100	1	1	5035048077894	TBC
DT89290Z	10	210	150	1	1	5035048077900	TBC
DT89300Z	10	260	200	1	1	5035048077917	TBC
DT89310Z	10	310	250	1	1	5035048077924	TBC
DT89320Z	10	460	400	1	1	5035048077931	TBC
DT89330Z	12	160	100	1	1	5035048077948	TBC
DT89340Z	12	200	150	1	1	5035048077955	TBC
DT89350Z	12	260	200	1	1	5035048077962	TBC
DT89360Z	12	310	260	1	1	5035048077979	TBC
DT89370Z	12	460	410	1	1	5035048077986	TBC

EXTREME DeWALT® XLR FULL HEAD CARBIDE DRILL BITS BULK PACKS

**COMING
IN
2009**


Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT89500Z	5	110	50	10	1	5035048078105	TBC
DT89510Z	5	160	100	10	1	5035048078112	TBC
DT89520Z	5	210	150	10	1	5035048078129	TBC
DT89530Z	5.5	110	50	10	1	5035048078136	TBC
DT89540Z	5.5	160	100	10	1	5035048078143	TBC
DT89550Z	6	110	50	10	1	5035048078150	TBC
DT89560Z	6	160	100	10	1	5035048078167	TBC
DT89570Z	6	210	150	10	1	5035048078174	TBC
DT89580Z	6	260	200	10	1	5035048078181	TBC
DT89590Z	6.5	160	100	10	1	5035048078198	TBC
DT89600Z	6.5	210	150	10	1	5035048078204	TBC
DT89610Z	6.5	260	200	10	1	5035048078211	TBC
DT89620Z	7	160	100	10	1	5035048078228	TBC
DT89630Z	7	260	150	10	1	5035048078235	TBC
DT89640Z	8	110	50	10	1	5035048078242	TBC
DT89650Z	8	160	100	10	1	5035048078259	TBC
DT89660Z	8	210	150	10	1	5035048078266	TBC
DT89670Z	10	160	100	10	1	5035048078273	TBC
DT89680Z	10	210	150	10	1	5035048078280	TBC
DT89690Z	10	260	200	10	1	5035048078297	TBC
DT89700Z	10	310	260	10	1	5035048078303	TBC
DT89710Z	12	160	100	10	1	5035048078310	TBC
DT89720Z	12	200	150	10	1	5035048078327	TBC

EXTREME DeWALT® FULL HEAD CARBIDE DRILL BIT SETS

**COMING
IN
2009**

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT89760Z	7 piece set in metal cassette	5, 6x2, 8x2, 10, 12	7	1	5035048078341	TBC
DT89770Z	Medium Tough Case with SDS+ XLR Full Head Carbide drill bits	5 x 110, 6 x 110 (x2), 6 x 160 (x2), 6.5 x 160, 8 x 160 (x2), 10 x 160, 12 x 160	10	1	5035048078358	TBC


SDS-PLUS 4-CUTTER DRILL BITS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT96800Z	16	250	200	1	1	5035048066133	30.52
DT96810Z	16	450	400	1	1	5035048066140	35.93
DT96820Z	18	250	200	1	1	5035048066157	32.76
DT96830Z	18	450	400	1	1	5035048066164	37.98
DT96840Z	20	250	200	1	1	5035048066171	34.90
DT96850Z	20	450	400	1	1	5035048066188	43.99
DT96860Z	22	250	200	1	1	5035048066195	45.25
DT96870Z	22	450	400	1	1	5035048066201	50.45
DT96880Z	24	250	200	1	1	5035048066218	51.57
DT96890Z	24	450	400	1	1	5035048066225	54.42
DT96900Z	25	250	200	1	1	5035048066232	55.26
DT96910Z	25	450	400	1	1	5035048066249	56.35
DT96920Z	26	450	400	1	1	5035048066256	61.30
DT96930Z	28	250	200	1	1	5035048066263	69.08
DT96940Z	28	450	400	1	1	5035048066270	72.21
DT96950Z	30	250	200	1	1	5035048066287	77.27
DT96960Z	30	450	400	1	1	5035048066294	82.64



**FOR USE WITH
SDS-PLUS
HAMMER DRILLS**



APPLICATIONS

- For fixing holes and through holes 16mm - 30mm.

FEATURES

- 4 flute spiral with maximum flute entry enables faster debris removal.
- Maximised central core enables more efficient energy transmission to the drill bit head.
- Fully supported carbide head gives longer life and cleaner, more concentric holes for better fixing retention.
- Open head design ensures faster drilling.



**FOR USE WITH
SDS-MAX
HAMMER DRILLS**



APPLICATIONS


- For use with SDS-Max drive hammer drills (Hilti type F6 or Y) for anchor, fixing or clearance holes in masonry concrete, brick or block work.

FEATURES

- 4 flute spiral with maximum flute entry enables faster debris removal.
- Maximised central core enables more efficient energy transmission to the drill bit head.
- Fully supported carbide head gives longer life and cleaner, more concentric holes for better fixing retention.
- Open head design ensures faster drilling.



SDS-MAX HAMMER DRILL BITS



Cat. No.	Diameter mm	Length mm	Working Length mm	Cutters	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT94000Z	12	340	200	2	1	1	5035048059678	27.56
DT94010Z	12	540	400	2	1	1	5035048059685	34.41
DT94020Z	12	670	550	2	1	1	5035048059692	45.88
DT94030Z	13	340	200	2	1	1	5035048059708	32.16
DT94040Z	13	540	400	2	1	1	5035048059715	36.66
DT94050Z	14	340	200	2	1	1	5035048059722	34.41
DT94060Z	14	540	400	2	1	1	5035048059739	39.03
DT94070Z	15	340	200	2	1	1	5035048059746	38.80
DT94080Z	15	540	400	2	1	1	5035048059753	40.03
DT94090Z	16	340	200	4	1	1	5035048059760	46.05
DT94100Z	16	540	400	4	1	1	5035048059777	42.56
DT94110Z	18	340	200	4	1	1	5035048059784	41.28
DT94120Z	18	540	400	4	1	1	5035048059791	42.56
DT94130Z	19	340	200	4	1	1	5035048059807	43.41
DT94140Z	19	540	400	4	1	1	5035048059814	44.53
DT94150Z	19	670	550	4	1	1	5035048059821	55.78
DT94160Z	20	340	200	4	1	1	5035048059838	45.88
DT94170Z	20	540	400	4	1	1	5035048059845	50.05
DT94180Z	20	920	800	4	1	1	5035048059852	95.42
DT94190Z	22	340	200	4	1	1	5035048059869	48.13
DT94200Z	22	540	400	4	1	1	5035048059876	50.05
DT94210Z	22	920	800	4	1	1	5035048059883	97.11
DT94220Z	24	340	200	4	1	1	5035048059890	50.38
DT94230Z	24	540	400	4	1	1	5035048059906	55.31
DT94240Z	25	340	200	4	1	1	5035048059913	54.65
DT94250Z	25	540	400	4	1	1	5035048059920	59.55
DT94260Z	25	920	800	4	1	1	5035048059937	143.39
DT94270Z	26	340	200	4	1	1	5035048059944	66.12
DT94280Z	26	540	400	4	1	1	5035048059951	68.37
DT94290Z	28	380	250	4	1	1	5035048059968	70.62
DT94300Z	28	570	450	4	1	1	5035048059975	70.85
DT94310Z	28	670	550	4	1	1	5035048059982	81.64
DT94320Z	30	380	250	4	1	1	5035048059999	67.47
DT94330Z	30	570	450	4	1	1	5035048060001	67.53
DT94340Z	32	380	250	4	1	1	5035048060018	69.27
DT94350Z	32	570	450	4	1	1	5035048060025	70.23
DT94360Z	32	920	800	4	1	1	5035048060032	147.88
DT94370Z	35	380	250	4	1	1	5035048060049	72.87
DT94380Z	35	570	450	4	1	1	5035048060056	86.03
DT94390Z	35	670	550	4	1	1	5035048060063	101.55
DT94400Z	36	570	450	4	1	1	5035048060070	103.80
DT94410Z	38	380	250	4	1	1	5035048060087	77.37
DT94420Z	38	570	450	4	1	1	5035048060094	106.05
DT94430Z	38	670	550	4	1	1	5035048060100	122.40
DT94440Z	40	380	250	4	1	1	5035048060117	80.97
DT94450Z	40	570	450	4	1	1	5035048060124	122.47
DT94460Z	40	920	800	4	1	1	5035048060131	190.95
DT94470Z	42	570	450	4	1	1	5035048060148	124.60
DT94480Z	45	570	450	4	1	1	5035048060155	202.99
DT94490Z	50	570	450	4	1	1	5035048060162	214.34
DT94500Z	52	570	450	4	1	1	5035048060179	222.89

CHISELS

DeWALT offers you a wide range of chisels and chisel fitments to cover every application you may encounter. A variety of working lengths, widths and working end types are available to suit any machine type and user preference.

All DeWALT chisels are manufactured to the highest standards using only top quality raw materials and processes to deliver long life, durability and consistently high performance.



EXTREME DeWALT® SDS-MAX CHISELS



Cat. No. Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6813QZ Pointed 300mm	-	300	1	1	5035048080436	34.34
DT6814QZ Pointed 400mm	-	400	1	1	5035048080443	42.40
DT6815QZ Flat 25 x 300mm	25	300	1	1	5035048080450	34.34
DT6816QZ Flat 25 x 400mm	25	400	1	1	5035048080467	42.40
DT6817QZ Pointed 560mm	-	560	1	1	5035048080474	NOT UK

**FOR USE WITH
SDS-MAX COMBI
HAMMERS AND
BREAKERS**




FEATURES

- New working end design with more material in the wear area for longer chisel life.
- Larger working end breaks more concrete in a single impact leading to greater productivity.
- Wider working end design lessens jamming issues.




FOR USE WITH SDS-PLUS HAMMER DRILLS



APPLICATIONS


- For light chipping and chiselling of tile, mortar, glazing compounds and other masonry products with hammers with a rotation stop feature.

SDS CHISELS SDS-PLUS CHISELS



Cat. No. Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6801QZ Pointed	-	250	1	1	5011402371426	15.19
DT6802QZ Flat	20	250	1	1	5011402371433	15.19
DT6803QZ Flat	40	200	1	1	5011402371440	19.31
DT6804QZ Sliding Chasing	22	250	1	1	5011402371457	34.45
DT6805QZ Hollow/Gouge	22	240	1	1	5011402371464	23.11
DT6806QZ Tile Chisel	40	200	1	1	5011402371471	24.03
DT6807QZ TCT Comb	32	130	1	1	5011402371488	79.90
DT6810QZ TCT Comb	32	200	1	1	5035048014301	NOT UK

SDS-MAX CHISELS



Cat. No. Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6820QZ Pointed	-	300	1	1	5011402378067	23.96
DT6821QZ Pointed	-	400	1	1	5011402378104	23.96
DT8087QZ Pointed	-	600	1	1	5035048061411	30.68
DT6822QZ Flat	25	300	1	1	5011402378074	23.96
DT6823QZ Flat	25	400	1	1	5011402378111	23.96
DT6824QZ Flat	50	360	1	1	5011402378128	41.78
DT6825QZ Flat	80	300	1	1	5011402378081	47.73
DT8088QZ Flat	25	600	1	1	5035048061428	56.74
DT6826QZ Hollow/Gouge	26	300	1	1	5011402378098	41.78
DT6832QZ Sliding Chasing	32	300	1	1	5035048034217	52.07

FOR USE WITH SDS-MAX HAMMER DRILLS

FEATURES


- DeWALT has a wide range of chisels covering most common applications. Specially toughened steel and micro-processor controlled heat treatment ensures consistent tough bits with long life.



DRILLING

DRILLING

SDS CHISELS SDS-MAX CHISELS




Cat. No. Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6833QZ Sliding Chasing	35	380	1	1	5035048034224	88.73
DT6834QZ Tile Chisel	80	300	1	1	5035048034231	46.78
DT6837QZ TCT Comb Chisel	38	280	1	1	5035048034248	111.90
DT6838QZ Bush Hammer	45	240	1	1	5035048034255	122.24
DT8090QZ Clay Spade	110	400	1	1	5035048034514	85.16
DT8091QZ Asphalt Cutter	90	400	1	1	5035048034521	75.47
DT8092QZ Earth Rod Driver	13	260	1	1	5035048034538	67.34
DT8093QZ Earth Rod Driver	16.5	260	1	1	5035048034545	71.36
DT8094QZ Tamping Plate	150	150	1	1	5035048034552	134.66
DT8095QZ Shank End for Tamping Plate	-	300	1	1	5035048034569	41.18

19MM HEXAGON CHISELS



Cat. No. Description	Width mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6940QZ Pointed	-	400	1	1	5035048025031	17.60
DT6941QZ Pointed	-	600	1	1	5035048025048	22.27
DT6942QZ Flat	25	400	1	1	5035048025055	17.60
DT6943QZ Flat	25	600	1	1	5035048025062	22.27
DT6944QZ Flat	60	300	1	1	5035048025079	38.63
DT6945QZ Flat	60	450	1	1	5035048025086	40.90
DT6946QZ Flat wide	140	350	1	1	5035048025093	40.99
DT6939QZ Earth Rod Driver	16	260	1	1	5035048058886	78.24
DT6947QZ Clay Spade	115	400	1	1	5035048058893	100.67
DT6948QZ Asphalt Cutter	90	400	1	1	5035048058909	74.13
DT6949QZ Shank End for Tamping Plate	-	300	1	1	5035048058916	31.26

FOR USE WITH SDS-MAX HAMMER DRILLS



APPLICATIONS

- For heavy duty chiselling, channelling, and demolition tasks in concrete, stone (medium hardness), floor and wall tiles, general masonry and mortar.



FOR USE WITH LARGE DEMOLITION HAMMERS 19MM HEX

APPLICATIONS

- For heavy duty chiselling, channelling, and demolition tasks in concrete, stone (medium hardness), floor and wall tiles, general masonry and mortar.



FOR USE WITH HAMMER DRILLS



APPLICATIONS

- Heavy duty breaking of concrete, asphalt & stone. Heavy duty tamping tasks and earth rod driving.

FOR USE WITH SDS-PLUS HAMMER DRILLS



APPLICATIONS

- For fitting drainage and water pipes, heating pipes, switches, junction & distribution boxes.

FOR USE WITH SDS-MAX HAMMER DRILLS



APPLICATIONS

- For clean round holes in blocks, bricks and light concrete.

DRILLING

PAVEMENT BREAKER CHISELS



Cat. No.	Description	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6927QZ	Bull Point 28mm	1	1	5035048070505	31.06
DT6928QZ	Clay Spade 28mm	1	1	5035048070512	110.67
DT6929QZ	Cold Chisel 28mm	1	1	5035048070529	31.06
DT6932QZ	Scaling Tool 28mm	1	1	5035048070536	42.49
DT6933QZ	Ground Rod Driver 28mm	1	1	5035048070543	110.67
DT6934QZ	Asphalt Cutter 28mm	1	1	5035048070550	96.39
DT6935QZ	Tamper Shank 28mm	1	1	5035048070567	74.97
DT6936QZ	Tamping Plate	1	1	5035048070574	138.88

LIGHT DUTY SDS-PLUS CORE DRILLS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6740QZ	30	72	1	1	5035048013595	46.64
DT6741QZ	35	72	1	1	5035048013601	48.41
DT6742QZ	40	72	1	1	5035048013618	48.94
DT6743QZ	45	72	1	1	5035048013625	53.55
DT6744QZ	50	72	1	1	5035048013632	61.53
DT6745QZ	68	72	1	1	5035048013649	85.25
DT6746QZ	72	72	1	1	5035048013656	99.50
DT6747QZ	80	72	1	1	5035048013663	112.99
DT6748QZ	90	72	1	1	5035048013670	125.57

HEAVY DUTY SDS-MAX CORE DRILLS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6760QZ	40	107	1	1	5035048013724	90.93
DT6761QZ	50	107	1	1	5035048013731	102.33
DT6762QZ	68	107	1	1	5035048013748	113.69
DT6763QZ	80	107	1	1	5035048013755	136.39
DT6764QZ	90	107	1	1	5035048013762	159.15
DT6765QZ	100	107	1	1	5035048013779	170.50
DT6766QZ	125	107	1	1	5035048013786	204.61

DRILLING

ADAPTERS



LIGHT DUTY CORE ADAPTERS

Cat. No.	Description	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6750QZ	SDS-Plus adapter	110	1	1	5035048013687	15.08
DT6751QZ	SDS-Plus adapter	300	1	1	5035048013694	30.15
DT6752QZ	Hex adapter	110	1	1	5035048013700	26.61
DT6753QZ	Pilot drill	120	1	1	5035048013717	10.28

HEAVY DUTY CORE ADAPTERS



Cat. No.	Description	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6770QZ	SDS-Max Adapter	180	1	1	5035048013793	45.46
DT6771QZ	SDS-Max Adapter	400	1	1	5035048013809	70.47
DT6772QZ	Pilot bit	155	1	1	5035048013816	10.76
DT6773QZ	Extension Piece	280	1	1	5035048013823	74.22

SINGLE PIECE CORES



Cat. No.	Description	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6780QZ	SDS-Max core	50	300	1	1	5035048013830	74.22
DT6783QZ	SDS-Max core	68	300	1	1	5035048013847	87.04
DT6784QZ	SDS-Max core	80	300	1	1	5035048013854	93.28
DT6785QZ	Pilot bit	-	185	1	1	5035048013908	90.18

THROUGH DRILLING BITS



Cat. No.	Description	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6790QZ	SDS-Max through drilling bit	55	550	1	1	5035048013861	466.53
DT6791QZ	SDS-Max through drilling bit	65	550	1	1	5035048013878	548.71
DT6792QZ	SDS-Max through drilling bit	80	550	1	1	5035048013885	636.17
DT6793QZ	Pilot bit	-	88	1	1	5035048013892	31.81

DRIVE ADAPTERS



Cat. No.	Description	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT6830QZ	SDS-Max to SDS-Plus	1	1	5011402378135	90.60
DT6831QZ	SDS-Max to Large Spline	1	1	5011402378671	103.23

ADAPTER - SDS-PLUS



Cat. No.	Description	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT7030QZ	SDS-Plus – 1/2" x 20 UNF (Chuck adapter)	1	1	5011402371419	90.64
DT6829QZ	SDS-Plus – 1/2" x 20 UNF chuck adapter / screwdriver bit holder	1	1	5035048034170	17.54

FOR USE WITH LIGHT AND HEAVY DUTY CORE DRILL BITS

- To be used with light duty SDS+ core drills - must be used with a pilot bit.

- To be used with Heavy duty SDS Max Core drills in conjunction with a pilot bit.

- For SDS Max hammer drills - for drilling holes in concrete or masonry from 50 to 80mm diameter.

- For drilling through holes (55 to 80mm diameter) up to 550mm depth in concrete and masonry.

- Allows interchangeability between tool & hammer bit fitments.

- Allows use of round shank drill bits in SDS+ fitment hammers. USE IN ROTARY MODE ONLY.

METAL DRILLING

MANUFACTURING

DeWALT drill bit factory in Buchelberg, Germany produces high performance products that respond to the needs of the professional user. Only the highest quality High Speed Steel is used to guarantee the best heat resistance and durability whilst state of the art grinding technology is used to ensure that every drill bit delivers maximum precision.

QUALITY CONTROL

DeWALT's engineers ensure every drill bit produced by its production processes complies with strict internal tolerances as well as exacting European manufacturing standards and norms (eg German Manufacturing standard DIN 338).

LEADERSHIP PRODUCT

The standard DeWALT range satisfies the application needs of the professional end user but EXTREME 2 METAL drill bits offer outstanding drilling speed as well as a hole quality that is second to none plus excellent durability. EXTREME COBALT bits are also available in order to offer users drilling into stainless steel the same performance advantages.



STATIONARY HARD MATERIALS DRILL BITS

For exceptionally long life in stationary applications in the hardest materials.

EXTREME DeWALT® COBALT DRILL BITS

For EXCEPTIONAL PERFORMANCE in Portable or Stationary drilling applications - hard materials alloyed or non alloyed steels, non ferrous metals, stainless steels up to 1100N/mm². FASTER DRILLING - CLEANER HOLES - INCREASED DURABILITY.

EXTREME DeWALT® 2 METAL DRILL BITS

For EXCEPTIONAL PERFORMANCE in Portable or Stationary drilling applications - alloyed or non alloyed steel, non ferrous metals up to 900N/mm², sheet metal, thin plate, wood and plastics. FASTER DRILLING - CLEANER HOLES - INCREASED DURABILITY.

HSS-G DRILL BITS

For portable or stationary drilling in vast iron, alloyed and non-alloyed steel, non-ferrous metals up to 900N/mm² wood and plastic.

STEP DRILL BITS

For drilling holes and enlarging existing holes in metal from 14mm up to 34mm.

IMPACT DRIVER DRILL BITS

Designed specifically for use with impact drivers in alloyed / non-alloyed steel, non-ferrous metals, sheet metal, thin plate wood and plastics. FASTER DRILLING, CLEANER HOLES - INCREASED DURABILITY

SUITABLE FOR THE FOLLOWING MATERIALS



Stainless Steel



Steel



Iron



Nickel



Brass




Wood



Plastic


STATIONARY HARD MATERIAL DRILL BITS SINGLE PACKS

COMING
IN
2009



Cat. No.	Diameter	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT504000Z	1.0mm	34	12	2	1	5035048081310	TBC
DT504010Z	1.5mm	40	14	2	1	5035048081327	TBC
DT504020Z	1.6mm	43	20	2	1	5035048081334	TBC
DT504030Z	2.0mm	49	24	2	1	5035048081341	TBC
DT504040Z	2.5mm	57	30	2	1	5035048081358	TBC
DT504050Z	3.0mm	61	33	2	1	5035048081365	TBC
DT504060Z	3.1mm	65	36	2	1	5035048081375	TBC
DT504070Z	3.2mm	65	36	2	1	5035048081389	TBC
DT504080Z	3.3mm	65	36	2	1	5035048081396	TBC
DT504090Z	3.5mm	70	39	2	1	5035048081402	TBC
DT504100Z	3.7mm	70	39	2	1	5035048081419	TBC
DT504110Z	4.0mm	75	43	2	1	5035048081426	TBC
DT504120Z	4.1mm	75	43	1	1	5035048081433	TBC
DT504130Z	4.2mm	75	43	1	1	5035048081440	TBC
DT504140Z	4.5mm	80	47	1	1	5035048081457	TBC
DT504150Z	4.8mm	86	52	1	1	5035048081464	TBC
DT504160Z	4.9mm	86	52	1	1	5035048081471	TBC
DT504170Z	5.0mm	86	52	1	1	5035048081488	TBC
DT504180Z	5.1mm	86	52	1	1	5035048081495	TBC
DT504190Z	5.2mm	86	52	1	1	5035048081501	TBC
DT504200Z	5.5mm	93	57	1	1	5035048081518	TBC
DT504210Z	6.0mm	101	63	1	1	5035048081525	TBC
DT504220Z	6.1mm	101	63	1	1	5035048081532	TBC
DT504230Z	6.5mm	101	63	1	1	5035048081549	TBC
DT504240Z	6.8mm	109	69	1	1	5035048081556	TBC
DT504250Z	7.0mm	109	69	1	1	5035048081563	TBC
DT504260Z	7.5mm	109	69	1	1	5035048081570	TBC
DT504270Z	7.8mm	117	75	1	1	5035048081587	TBC
DT504280Z	7.9mm	117	75	1	1	5035048081594	TBC
DT504290Z	8.0mm	117	75	1	1	5035048081600	TBC
DT504300Z	8.5mm	117	75	1	1	5035048081617	TBC
DT504310Z	9.0mm	125	81	1	1	5035048081624	TBC
DT504320Z	9.5mm	125	81	1	1	5035048081631	TBC
DT504330Z	10.0mm	133	87	1	1	5035048081648	TBC
DT504340Z	10.2mm	133	87	1	1	5035048081655	TBC
DT504350Z	10.5mm	133	87	1	1	5035048081662	TBC
DT504360Z	11.0mm	142	94	1	1	5035048081679	TBC
DT504370Z	11.5mm	142	94	1	1	5035048081686	TBC
DT504380Z	12.0mm	151	101	1	1	5035048081693	TBC
DT504390Z	12.5mm	151	101	1	1	5035048081709	TBC
DT504400Z	13.0mm	151	101	1	1	5035048081716	TBC

FOR USE IN
DRILL PRESS OR
CNC MACHINE



Steel Iron Graphite



Nickel Brass Stainless Steel

APPLICATIONS


- Designed for stationary drilling of high alloy content steels and metals with a tensile strength up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels.

FEATURES

- Designed to return maximum life in hard materials (e.g. stainless steel or cast iron) when used in CNC or drill press applications.
- Each drill bit is coated to aid heat dissipation and vastly extend drill bit life.
- Full range of diameters to cover all major applications.



**FOR USE WITH
CORDLESS AND
CORDED DRILLS**



APPLICATIONS

- Suitable for portable or stationary drilling of high alloy content steels and metals with a tensile strength up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels.


FEATURES

- Faster drilling - up to 4x faster than standard HSS-R drill bits.
- Increased durability - up to 50% stronger than standard HSS-R drill bits.
- Cleaner, more accurate, burr-free holes due to recessed cutting wings.
- Innovative tapered web greatly reduces breakage.
- No-Slip shank with 3 flats eliminates slipping in the chuck (diameters 5.0mm and above only).
- Gold Ferrous Oxide coating prevents overheating for longer bit life.
- 5% cobalt alloyed High Speed Steel for stability at high temperatures when drilling tough materials.

DRILLING

HSS-CO EXTREME DeWALT® COBALT DRILL BITS


SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5630QZ	1.0	34	12	2	1	5035048076958	NOT UK
DT5631QZ	1.5	40	18	2	1	5035048076965	NOT UK
DT5632QZ	1.6	43	20	2	1	5035048076972	NOT UK
DT5403QZ	2	49	24	2	1	5011402375912	3.65
DT5404QZ	2.5	57	30	2	1	5011402375936	3.92
DT5405QZ	3	61	33	2	1	5011402375950	4.21
DT5633QZ	3.1	65	36	2	1	5035048076989	NOT UK
DT5634QZ	3.3	65	36	2	1	5035048076996	NOT UK
DT5408QZ	3.5	70	39	2	1	5011402375974	4.98
DT5409QZ	4	75	43	2	1	5011402375998	5.44
DT5635QZ	4.1	75	43	1	1	5035048077009	NOT UK
DT5636QZ	4.2	75	43	1	1	5035048077016	NOT UK
DT5412QZ	4.5	80	47	1	1	5011402376018	3.16
DT5637QZ	4.9	86	46	1	1	5035048077023	NOT UK
DT5414QZ	5	86	52	1	1	5011402376032	3.45
DT5638QZ	5.1	86	46	1	1	5035048077030	NOT UK
DT5415QZ	5.5	93	57	1	1	5011402376056	4.12
DT5416QZ	6	93	57	1	1	5011402376070	4.12
DT5639QZ	6.1	101	58	1	1	5035048077047	NOT UK
DT5417QZ	6.5	101	63	1	1	5011402376094	4.80
DT5640QZ	6.8	109	66	1	1	5035048077054	NOT UK
DT5418QZ	7	109	69	1	1	5011402376117	5.37
DT5641QZ	7.5	109	66	1	1	5035048077061	NOT UK
DT5642QZ	7.8	117	75	1	1	5035048077078	NOT UK
DT5643QZ	7.9	117	75	1	1	5035048077085	NOT UK
DT5419QZ	8	117	75	1	1	5011402376131	5.98
DT5644QZ	8.5	117	72	1	1	5035048077092	NOT UK
DT5421QZ	9	125	81	1	1	5011402376155	7.64
DT5645QZ	9.5	125	78	1	1	5035048077108	NOT UK
DT5422QZ	10	133	87	1	1	5011402376179	8.72
DT5646QZ	10.2	133	84	1	1	5035048077115	NOT UK
DT5647QZ	10.5	133	84	1	1	5035048077122	10.51
DT5424QZ	11	142	94	1	1	5011402376193	NOT UK
DT5648QZ	11.5	142	91	1	1	5035048077139	NOT UK
DT5426QZ	12	151	101	1	1	5011402376216	13.90
DT5649QZ	12.2	151	98	1	1	5035048077146	NOT UK
DT5650QZ	12.5	151	98	1	1	5035048077153	NOT UK
DT5427QZ	13	151	101	1	1	5011402376230	16.68

HSS-CO EXTREME DeWALT® COBALT DRILL BITS

BULK PACKS





Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5660QZ	1.5	40	18	10	1	5035048077160	NOT UK
DT5661QZ	1.6	43	20	10	1	5035048077177	NOT UK
DT5442QZ	2	49	24	10	1	5011402384518	15.34
DT5443QZ	2.5	57	30	10	1	5011402384525	17.19
DT5444QZ	3	61	33	10	1	5011402384532	18.92
DT5662QZ	3.1	65	36	10	1	5035048077184	NOT UK
DT5446QZ	3.2	65	36	10	1	5011402384549	19.66
DT5447QZ	3.3	65	36	10	1	5011402386208	21.77
DT5448QZ	3.5	70	39	10	1	5011402384563	22.64
DT5449QZ	4	75	43	10	1	5011402384570	24.49
DT5450QZ	4.1	75	43	10	1	5011402384587	NOT UK
DT5451QZ	4.2	75	43	10	1	5011402384594	26.35
DT5452QZ	4.5	80	47	10	1	5011402384600	28.46
DT5453QZ	4.8	86	52	10	1	5011402384617	30.43
DT5663QZ	4.9	86	46	10	1	5035048077191	NOT UK
DT5454QZ	5	86	52	10	1	5011402384624	31.05
DT5455QZ	5.1	86	52	10	1	5011402384631	NOT UK
DT5456QZ	5.2	86	52	10	1	5011402384648	37.11
DT5457QZ	5.5	93	57	10	1	5011402384655	37.11
DT5458QZ	6	93	57	10	1	5011402384662	37.11
DT5664QZ	6.1	101	58	10	1	5035048077207	NOT UK
DT5459QZ	6.5	101	63	10	1	5011402384679	43.30
DT5460QZ	6.8	109	69	10	1	5011402384686	NOT UK
DT5461QZ	7	109	69	10	1	5011402384693	48.38
DT5462QZ	7.5	109	69	10	1	5011402384709	51.95
DT5665QZ	7.8	117	75	10	1	5035048077214	NOT UK
DT5666QZ	7.9	117	75	10	1	5035048077221	NOT UK
DT5463QZ	8	117	75	10	1	5011402384716	56.29
DT5464QZ	8.5	117	75	10	1	5011402384723	66.31
DT5465QZ	9	125	81	10	1	5011402384730	68.04
DT5466QZ	9.5	125	81	10	1	5011402384747	77.32
DT5467QZ	10	133	87	10	1	5011402384754	83.51
DT5468QZ	10.2	133	87	10	1	5011402384761	91.78
DT5667QZ	10.5	133	84	5	1	5035048077238	NOT UK
DT5469QZ	11	142	94	5	1	5011402384778	51.02
DT5668QZ	11.5	142	91	5	1	5035048077245	NOT UK
DT5470QZ	12	151	101	5	1	5011402384785	62.59
DT5669QZ	12.2	151	98	5	1	5035048077252	NOT UK
DT5670QZ	12.5	151	98	5	1	5035048077269	75.02
DT5471QZ	13	151	101	5	1	5011402384792	NOT UK

HSS-CO EXTREME DeWALT® COBALT DRILL BITS SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT5940QZ	6 piece set in plastic cassette	2, 3, 4, 5, 6, 8	6	1	5011402376254	26.11
DT7942QZ	Small tough case with EXTREME DeWALT® Cobalt bits	1.5, 2, 2.5, 3, 3.2, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7	13	1	5035048066003	50.60
DT5928QZ	29 piece Cobalt set in plastic case	1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.2, 4.5, 4.8, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13 mm.	29	1	5035048077412	192.30

**FOR USE WITH
CORDLESS AND
CORDED DRILLS**



APPLICATIONS



- Suitable for portable or stationary drilling of high alloy content steels and metals with a tensile strength up to 1100N/mm² e.g. heat and acid proof steel, cast iron, bronze, welded seams, stainless and chrome nickel steels.

FEATURES

- Faster drilling - up to 4x faster than standard HSS-R drill bits.
- Increased durability - up to 50% stronger than standard HSS-R drill bits.
- Cleaner, more accurate, burr-free holes due to recessed cutting wings.
- Innovative tapered web greatly reduces breakage.
- No-Slip shank with 3 flats eliminates slipping in the chuck (diameters 5.0mm and above only).
- Gold Ferrous Oxide coating prevents overheating for longer bit life.
- 5% cobalt alloyed High Speed Steel for stability at high temperatures when drilling tough materials.



**FOR USE WITH
CORDLESS AND
CORDED DRILLS**




APPLICATIONS

- Suitable for portable drilling of steel, alloyed and non-alloyed up to 900 N/mm².
- For drilling sheet or thin materials (suitable for use in wood and plastics).

FEATURES


- Faster drilling - up to 4x faster than standard HSS-R drill bits.
- Increased durability - up to 50% stronger than standard HSS-R drill bits.
- Cleaner, more accurate, burr-free holes due to recessed cutting wings.
- Innovative tapered web greatly reduces breakage.
- No-Slip shank with 3 flats eliminates slipping in the chuck (diameters 5.0mm and above only).
- Gold Ferrous Oxide coating prevents overheating for longer bit life.

EXTREME DeWALT® 2 METAL DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT50340Z	1	34	12	2	1	5035048034767	2.69
DT50350Z	1.5	40	18	2	1	5035048034774	2.83
DT56000Z	1.6	43	20	2	1	5035048076811	NOT UK
DT50360Z	2	49	24	2	1	5035048034781	2.96
DT50370Z	2.5	57	30	2	1	5035048034798	3.20
DT50380Z	3	61	33	2	1	5035048034804	3.79
DT56010Z	3.1	65	36	2	1	5035048076828	NOT UK
DT50390Z	3.2	65	36	2	1	5035048034811	4.18
DT50400Z	3.3	65	36	2	1	5035048034828	4.10
DT50410Z	3.5	70	39	2	1	5035048034835	4.42
DT50420Z	4	75	43	2	1	5035048034842	4.70
DT50630Z	4.1	75	43	1	1	5035048052648	2.43
DT50430Z	4.2	75	43	1	1	5035048034859	2.47
DT50440Z	4.5	80	46	1	1	5035048034866	2.48
DT50450Z	4.8	86	46	1	1	5035048034873	2.60
DT56020Z	4.9	86	46	1	1	5035048076835	NOT UK
DT50460Z	5	86	46	1	1	5035048034880	2.69
DT50640Z	5.1	86	46	1	1	5035048052655	2.82
DT50650Z	5.2	86	46	1	1	5035048052662	2.90
DT50660Z	5.4	93	52	1	1	5035048052679	2.90
DT50470Z	5.5	93	57	1	1	5035048034897	2.92
DT50480Z	6	93	57	1	1	5035048034903	2.92
DT56030Z	6.1	101	58	1	1	5035048076842	NOT UK
DT50490Z	6.5	101	58	1	1	5035048034910	3.32
DT50670Z	6.8	109	66	1	1	5035048052686	NOT UK
DT50500Z	7	109	66	1	1	5035048034927	3.79
DT50510Z	7.5	109	66	1	1	5035048034934	4.28
DT56040Z	7.8	117	75	1	1	5035048076859	NOT UK
DT56050Z	7.9	117	75	1	1	5035048076866	NOT UK
DT50520Z	8	117	72	1	1	5035048034941	4.40
DT50530Z	8.5	117	72	1	1	5035048034958	5.18
DT50540Z	9	125	78	1	1	5035048034965	5.69
DT50550Z	9.5	125	78	1	1	5035048034972	6.30
DT50560Z	10	133	84	1	1	5035048034989	6.95
DT56060Z	10.2	133	84	1	1	5035048076873	NOT UK
DT50570Z	10.5	133	84	1	1	5035048034996	7.25
DT50580Z	11	142	91	1	1	5035048052006	8.33
DT50590Z	11.5	142	91	1	1	5035048052013	8.81
DT50680Z	11.8	151	98	1	1	5035048052693	9.44
DT50600Z	12	151	98	1	1	5035048052020	10.17
DT50610Z	12.5	151	98	1	1	5035048052037	10.27
DT50620Z	13	151	98	1	1	5035048052044	10.52

EXTREME DeWALT® 2 METAL DRILL BITS BULK PACKS




Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT55350Z	1	34	12	10	1	5035048052051	8.84
DT55360Z	1.5	40	18	10	1	5035048052068	9.09
DT56150Z	1.6	43	20	10	1	5035048076880	NOT UK
DT55370Z	2	49	24	10	1	5035048052075	9.09
DT55380Z	2.5	57	30	10	1	5035048052082	9.75
DT55390Z	3	61	33	10	1	5035048052099	10.67
DT56160Z	3.1	65	36	10	1	5035048076897	NOT UK
DT55400Z	3.2	65	36	10	1	5035048052105	16.21
DT55410Z	3.3	65	36	10	1	5035048052112	16.21
DT55420Z	3.5	70	39	10	1	5035048052129	16.84
DT55430Z	4	75	43	10	1	5035048052136	17.34
DT55660Z	4.1	75	43	10	1	5035048052709	17.63
DT55440Z	4.2	75	43	10	1	5035048052143	17.86
DT55450Z	4.5	80	46	10	1	5035048052150	18.57
DT55460Z	4.8	86	46	10	1	5035048052167	22.00
DT56170Z	4.9	86	46	10	1	5035048076903	NOT UK
DT55470Z	5	86	46	10	1	5035048052174	22.39
DT55670Z	5.1	86	46	10	1	5035048052716	22.62
DT55680Z	5.2	86	46	10	1	5035048052723	23.01
DT55690Z	5.4	93	52	10	1	5035048052730	23.30
DT55480Z	5.5	93	57	10	1	5035048052181	23.55
DT55490Z	6	93	57	10	1	5035048052198	24.57
DT56180Z	6.1	101	58	10	1	5035048076910	NOT UK
DT55500Z	6.5	101	58	10	1	5035048052204	26.72
DT55700Z	6.8	109	66	10	1	5035048052747	29.71
DT55510Z	7	109	66	10	1	5035048052211	31.36
DT55520Z	7.5	109	66	10	1	5035048052228	33.48
DT56190Z	7.8	117	75	10	1	5035048076927	NOT UK
DT56200Z	7.9	117	75	10	1	5035048076934	NOT UK
DT55530Z	8	117	72	10	1	5035048052235	36.47
DT55540Z	8.5	117	72	10	1	5035048052242	41.20
DT55550Z	9	125	78	10	1	5035048052259	44.93
DT55560Z	9.5	125	78	10	1	5035048052266	49.16
DT55570Z	10	133	84	10	1	5035048052273	57.45
DT56210Z	10.2	133	84	10	1	5035048076941	NOT UK
DT55580Z	10.5	133	84	10	1	5035048052280	63.24
DT55590Z	11	142	91	10	1	5035048052297	68.22
DT55600Z	11.5	142	91	10	1	5035048052303	72.22
DT55710Z	11.8	151	98	10	1	5035048052754	76.62
DT55610Z	12	151	98	10	1	5035048052310	78.65
DT55620Z	12.5	151	98	10	1	5035048052327	83.85
DT55630Z	13	151	98	10	1	5035048052334	89.05

EXTREME DeWALT® 2 METAL DRILL BIT SETS

See page 55 for details.



**FOR USE WITH
CORDLESS AND
CORDED DRILLS**




APPLICATIONS

- Suitable for portable drilling of steel, alloyed and non-alloyed up to 900 N/mm².
- For drilling sheet or thin materials (suitable for use in wood and plastics).



FOR USE WITH
CORDLESS AND
CORDED DRILLS



Steel Iron Graphite



Nickel Brass Wood


APPLICATIONS

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

FEATURES


- Precision ground twist drill bit for rapid drilling, long life and excellent concentricity.
- Ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle.
- Diameter tolerance to h8.
- Drills above 13mm (1/2") have a shank reduced to 12.7mm.

HSS-G DIN 338 JOBBER METAL DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT52010Z	1	34	12	2	1	5011402373437	2.15
DT52000Z	1.1	36	14	2	1	5035048080481	NOT UK
DT52070Z	1.2	38	16	2	1	5035048080498	NOT UK
DT52100Z	1.3	38	16	2	1	5035048080504	NOT UK
DT52230Z	1.4	40	18	2	1	5035048080511	NOT UK
DT52020Z	1.5	40	18	2	1	5011402373451	2.27
DT52250Z	1.6	43	20	2	1	5035048080528	NOT UK
DT52310Z	1.7	43	20	2	1	5035048080535	NOT UK
DT52360Z	1.8	46	22	2	1	5035048080542	NOT UK
DT52370Z	1.9	46	22	2	1	5035048080559	NOT UK
DT52030Z	2	49	24	2	1	5011402373475	2.27
DT52380Z	2.1	49	24	2	1	5035048080566	NOT UK
DT52390Z	2.2	53	27	2	1	5035048080573	NOT UK
DT52400Z	2.3	53	27	2	1	5035048080580	NOT UK
DT52410Z	2.4	57	30	2	1	5035048080597	NOT UK
DT52040Z	2.5	57	30	2	1	5011402373499	2.27
DT52420Z	2.6	57	30	2	1	5035048080603	NOT UK
DT52430Z	2.7	61	33	2	1	5035048080610	NOT UK
DT52440Z	2.8	61	33	2	1	5035048080627	NOT UK
DT52450Z	2.9	61	33	2	1	5035048080634	NOT UK
DT52050Z	3	61	33	2	1	5011402373512	2.51
DT52460Z	3.1	65	36	2	1	5035048080641	NOT UK
DT52060Z	3.2	65	36	2	1	5011402373536	NOT UK
DT52470Z	3.3	65	36	2	1	5035048080658	NOT UK
DT52480Z	3.4	70	39	2	1	5035048080665	NOT UK
DT52080Z	3.5	70	39	2	1	5011402373574	2.98
DT52490Z	3.6	70	39	2	1	5035048080672	NOT UK
DT52500Z	3.7	70	39	2	1	5035048080689	NOT UK
DT52510Z	3.8	75	43	2	1	5035048080696	NOT UK
DT52520Z	3.9	75	43	2	1	5035048080702	NOT UK
DT52090Z	4	75	43	2	1	5011402373598	3.11
DT52530Z	4.1	75	43	1	1	5035048080719	NOT UK
DT52110Z	4.2	75	43	1	1	5011402373635	1.81
DT52540Z	4.3	80	47	1	1	5035048080726	NOT UK
DT52690Z	4.4	80	47	1	1	5035048076477	NOT UK
DT52120Z	4.5	80	47	1	1	5011402373659	1.83
DT52700Z	4.6	80	47	1	1	5035048076484	NOT UK
DT52710Z	4.7	80	47	1	1	5035048076491	NOT UK
DT52130Z	4.8	86	52	1	1	5011402373673	1.83
DT52720Z	4.9	86	52	1	1	5035048076507	NOT UK
DT52140Z	5	86	52	1	1	5011402373697	1.83
DT52730Z	5.1	86	52	1	1	5035048076514	NOT UK
DT52740Z	5.2	86	52	1	1	5035048076521	NOT UK
DT52750Z	5.3	86	52	1	1	5035048076538	NOT UK
DT52760Z	5.4	93	57	1	1	5035048076545	NOT UK
DT52150Z	5.5	93	57	1	1	5011402373710	2.33
DT52770Z	5.6	93	57	1	1	5035048076552	NOT UK
DT52780Z	5.7	93	57	1	1	5035048076569	NOT UK
DT52790Z	5.8	93	57	1	1	5035048076576	NOT UK
DT52800Z	5.9	93	57	1	1	5035048076583	NOT UK
DT52160Z	6	101	63	1	1	5011402373734	2.51
DT52810Z	6.1	101	63	1	1	5035048076590	NOT UK
DT52820Z	6.2	101	63	1	1	5035048076606	NOT UK
DT52830Z	6.3	101	63	1	1	5035048076613	NOT UK
DT52840Z	6.4	101	63	1	1	5035048076620	NOT UK
DT52170Z	6.5	101	63	1	1	5011402373758	2.85
DT52850Z	6.6	101	63	1	1	5035048076637	NOT UK
DT52550Z	6.7	101	63	1	1	5035048080733	NOT UK
DT52560Z	6.8	109	69	1	1	5035048080740	NOT UK
DT52570Z	6.9	109	69	1	1	5035048080757	NOT UK
DT52180Z	7	109	69	1	1	5011402373772	NOT UK
DT52580Z	7.1	109	69	1	1	5035048080764	NOT UK
DT52590Z	7.2	109	69	1	1	5035048080771	NOT UK
DT52860Z	7.3	109	69	1	1	5035048080788	NOT UK
DT52870Z	7.4	109	69	1	1	5035048080795	NOT UK
DT52320Z	7.5	109	69	1	1	5011402384488	4.18

HSS-G DIN 338 JOBBER METAL DRILL BITS SINGLE PACKS




Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT52880Z	7.6	117	75	1	1	5035048080801	NOT UK
DT52890Z	7.7	117	75	1	1	5035048080818	NOT UK
DT52900Z	7.8	117	75	1	1	5035048080825	NOT UK
DT52910Z	7.9	117	75	1	1	5035048080832	NOT UK
DT52190Z	8	117	75	1	1	5011402373796	3.58
DT52920Z	8.1	117	75	1	1	5035048080849	NOT UK
DT52930Z	8.2	117	75	1	1	5035048080856	NOT UK
DT52940Z	8.3	117	75	1	1	5035048080863	NOT UK
DT52950Z	8.4	117	75	1	1	5035048080870	NOT UK
DT52200Z	8.5	117	75	1	1	5011402373819	4.48
DT52960Z	8.6	125	81	1	1	5035048080887	NOT UK
DT52970Z	8.7	125	81	1	1	5035048080894	NOT UK
DT52980Z	8.8	125	81	1	1	5035048080900	NOT UK
DT52990Z	8.9	125	81	1	1	5035048080917	NOT UK
DT52210Z	9	125	81	1	1	5011402373833	4.53
DT54000Z	9.1	125	81	1	1	5035048080924	NOT UK
DT54010Z	9.2	125	81	1	1	5035048080931	NOT UK
DT54020Z	9.3	125	81	1	1	5035048080948	NOT UK
DT54060Z	9.4	125	81	1	1	5035048080955	NOT UK
DT54070Z	9.5	125	81	1	1	5035048080962	NOT UK
DT54100Z	9.6	133	87	1	1	5035048080979	NOT UK
DT54110Z	9.7	133	87	1	1	5035048080986	NOT UK
DT54130Z	9.8	133	87	1	1	5035048080993	NOT UK
DT54200Z	9.9	133	87	1	1	5035048081006	NOT UK
DT52220Z	10	133	87	1	1	5011402373857	5.13
DT54230Z	10.2	133	87	1	1	5035048081013	NOT UK
DT54250Z	10.5	133	87	1	1	5035048081020	NOT UK
DT52240Z	11	142	94	1	1	5011402373895	NOT UK
DT54280Z	11.5	142	94	1	1	5035048081037	NOT UK
DT52260Z	12	151	101	1	1	5011402373932	9.04
DT54290Z	12.5	151	101	1	1	5035048081044	NOT UK
DT52270Z	13	151	101	1	1	5011402373956	10.17
DT54300Z	13.5	151	101	1	1	5035048081051	NOT UK
DT52280Z	14	160	108	1	1	5011402373970	13.12
DT54310Z	14.5	160	108	1	1	5035048081068	NOT UK
DT52290Z	15	169	114	1	1	5011402373994	14.92
DT54320Z	15.5	169	114	1	1	5035048081075	NOT UK
DT52300Z	16	178	120	1	1	5011402374014	16.12
DT54330Z	16.5	178	120	1	1	5035048081082	NOT UK
DT54340Z	17	178	120	1	1	5035048081099	NOT UK
DT54350Z	17.5	178	120	1	1	5035048081105	NOT UK
DT54360Z	18	191	130	1	1	5035048081112	NOT UK
DT54370Z	18.5	191	130	1	1	5035048081129	NOT UK
DT54380Z	19	198	135	1	1	5035048081136	NOT UK
DT54390Z	19.5	198	135	1	1	5035048081143	NOT UK
DT54720Z	20	205	140	1	1	5035048081150	NOT UK


HSS-G DIN 338 JOBBER METAL DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT59210Z	10 piece set in plastic cassette.	1, 2, 3, 4, 5, 6, 7, 8, 9, 10	10	1	5011402374137	23.01
DT59220Z	13 piece set in plastic cassette.	1.5, 2, 2.5, 3.2, 3, 3.5, 4, 4.5, 5 (x2), 5.5, 6, 6.5	13	1	5011402374151	18.17
DT59230Z	19 piece set in metal cassette.	1, 1.5, 2, 2.5, 3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10	19	1	5011402374175	57.29
DT59290Z	29 piece set in metal case	1, 1.5, 2, 2.5, 3, 3.2, 3.3, 3.5, 4, 4.5, 5, 5.5, 6, 6.5, 7, 7.5, 8, 8.5, 9, 9.5, 10, 10.5, 11, 11.5, 12, 12.5, 13	29	1	5035048077429	101.92

FOR USE WITH
CORDLESS AND
CORDED DRILLS



Steel Iron Graphite




Nickel Brass Wood

APPLICATIONS

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².


FEATURES

- Precision ground twist drill bit for rapid drilling, long life and excellent concentricity.
- Ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle.
- Diameter tolerance to h8.
- Drills above 13mm (1/2") have a shank reduced to 12.7mm.



Steel Iron

FOR USE WITH
CORDLESS AND
CORDED DRILLS




APPLICATIONS

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

FEATURES


- Precision ground twist drill bit for rapid drilling, long life and excellent concentricity.
- Ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle.
- Diameter tolerance to h8.
- Drills above 13mm (1/2") have a shank reduced to 12.7mm.

HSS-G DIN 338 JOBBER METAL DRILL BITS BULK PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT53010Z	1	34	12	10	1	5011402383504	11.36
DT53020Z	1.1	36	14	10	1	5011402383511	11.36
DT53030Z	1.2	38	16	10	1	5011402383528	11.36
DT53040Z	1.3	38	16	10	1	5011402383535	11.36
DT53050Z	1.4	40	18	10	1	5011402383542	11.36
DT53060Z	1.5	40	18	10	1	5011402383559	10.01
DT53070Z	1.6	43	20	10	1	5011402383566	10.01
DT53080Z	1.7	43	20	10	1	5011402383573	10.01
DT53090Z	1.8	46	22	10	1	5011402383580	10.01
DT53100Z	1.9	46	22	10	1	5011402383597	10.01
DT53110Z	2	49	24	10	1	5011402383603	9.00
DT53120Z	2.1	49	24	10	1	5011402383610	9.00
DT53130Z	2.2	53	27	10	1	5011402383627	9.00
DT53140Z	2.3	53	27	10	1	5011402383634	9.00
DT53150Z	2.4	57	30	10	1	5011402383641	9.00
DT53160Z	2.5	57	30	10	1	5011402383658	9.00
DT53170Z	2.6	57	30	10	1	5011402383665	9.00
DT53180Z	2.7	61	33	10	1	5011402383672	9.00
DT53190Z	2.8	61	33	10	1	5011402383689	9.34
DT53200Z	2.9	61	33	10	1	5011402383696	9.34
DT53210Z	3	61	33	10	1	5011402383702	9.34
DT53220Z	3.1	65	36	10	1	5011402383719	9.34
DT53230Z	3.2	65	36	10	1	5011402383726	9.34
DT53250Z	3.3	65	36	10	1	5011402383740	9.34
DT53260Z	3.4	70	39	10	1	5011402383757	9.34
DT53270Z	3.5	70	39	10	1	5011402383764	10.01
DT53280Z	3.6	70	39	10	1	5011402383771	10.01
DT53290Z	3.7	70	39	10	1	5011402383788	10.01
DT53300Z	3.8	75	43	10	1	5011402383795	11.25
DT53310Z	3.9	75	43	10	1	5011402383801	11.25
DT53320Z	4	75	43	10	1	5011402383818	11.25
DT53330Z	4.1	75	43	10	1	5011402383825	11.25
DT53340Z	4.2	75	43	10	1	5011402383832	12.49
DT53350Z	4.3	80	47	10	1	5011402383849	12.49
DT53360Z	4.4	80	47	10	1	5011402383856	12.49
DT53370Z	4.5	80	47	10	1	5011402383863	12.49
DT53380Z	4.6	80	47	10	1	5011402383870	12.49
DT53390Z	4.7	80	47	10	1	5011402383887	13.27
DT53400Z	4.8	86	52	10	1	5011402383894	13.27
DT53410Z	4.9	86	52	10	1	5011402383900	13.27
DT53420Z	5	86	52	10	1	5011402383917	14.17
DT53430Z	5.1	86	52	10	1	5011402383924	14.17
DT53440Z	5.2	86	52	10	1	5011402383931	14.17
DT53450Z	5.3	86	52	10	1	5011402383948	16.54
DT53460Z	5.4	93	57	10	1	5011402383955	16.54
DT53470Z	5.5	93	57	10	1	5011402383962	16.54
DT53480Z	5.6	93	57	10	1	5011402383979	18.67
DT53490Z	5.7	93	57	10	1	5011402383986	18.67
DT53500Z	5.8	93	57	10	1	5011402383993	18.67
DT53510Z	5.9	93	57	10	1	5011402384006	18.67
DT53520Z	6	93	57	10	1	5011402384013	18.67
DT53530Z	6.1	101	63	10	1	5011402384020	21.37
DT53540Z	6.2	101	63	10	1	5011402384037	21.37
DT53550Z	6.3	101	63	10	1	5011402384044	21.37
DT53560Z	6.4	101	63	10	1	5011402384051	21.37
DT53570Z	6.5	101	63	10	1	5011402384068	21.37
DT53580Z	6.6	101	63	10	1	5011402384075	21.37
DT53590Z	6.7	101	63	10	1	5011402384082	24.52
DT53600Z	6.8	109	69	10	1	5011402384099	24.52
DT53610Z	6.9	109	69	10	1	5011402384105	24.52
DT53620Z	7	109	69	10	1	5011402384112	24.52
DT53630Z	7.100	109	69	10	1	5011402384129	27.80


HSS-G DIN 338 JOBBER METAL DRILL BITS BULK PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT53640Z	7.2	109	69	10	1	5011402384136	27.89
DT53650Z	7.3	109	69	10	1	5011402384143	27.89
DT53660Z	7.4	109	69	10	1	5011402384150	27.89
DT53670Z	7.5	109	69	10	1	5011402384167	27.89
DT53680Z	7.6	117	75	10	1	5011402384174	31.38
DT53690Z	7.7	117	75	10	1	5011402384181	31.38
DT53700Z	7.8	117	75	10	1	5011402384198	31.38
DT53710Z	7.9	117	75	10	1	5011402384204	31.38
DT53720Z	8	117	75	10	1	5011402384211	31.38
DT53730Z	8.1	117	75	10	1	5011402384228	35.65
DT53740Z	8.2	117	75	10	1	5011402384235	35.65
DT53750Z	8.3	117	75	10	1	5011402384242	35.65
DT53760Z	8.4	117	75	10	1	5011402384259	35.65
DT53770Z	8.5	117	75	10	1	5011402384266	35.65
DT53780Z	8.6	125	81	10	1	5011402384273	40.26
DT53790Z	8.7	125	81	10	1	5011402384280	40.26
DT53800Z	8.8	125	81	10	1	5011402384297	40.26
DT53810Z	8.9	125	81	10	1	5011402384303	40.26
DT53820Z	9	125	81	10	1	5011402384310	40.26
DT53830Z	9.1	125	81	10	1	5011402384327	44.98
DT53840Z	9.2	125	81	10	1	5011402384334	44.98
DT53850Z	9.3	125	81	10	1	5011402384341	44.98
DT53860Z	9.4	125	81	10	1	5011402384358	44.98
DT53870Z	9.5	125	81	10	1	5011402384365	44.98
DT53880Z	9.6	133	87	10	1	5011402384372	50.50
DT53890Z	9.7	133	87	10	1	5011402384389	50.50
DT53900Z	9.8	133	87	10	1	5011402384396	50.50
DT53910Z	9.9	133	87	10	1	5011402384402	50.50
DT53920Z	10	133	87	10	1	5011402384419	50.50
DT54730Z	10.2	133	87	5	1	5035048081167	28.11
DT53930Z	10.5	133	87	5	1	5011402384426	28.11
DT53940Z	11	142	94	5	1	5011402384433	31.21
DT53950Z	11.5	142	94	5	1	5011402384440	34.86
DT53960Z	12	151	101	5	1	5011402384457	38.41
DT53970Z	12.5	151	101	5	1	5011402384464	42.56
DT53980Z	13	151	101	5	1	5011402384471	46.95


HSS-G DIN 340 LONG SERIES METAL DRILL BITS

BULK PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT57760Z	1.56	85	55	10	1	5035048081174	NOT UK
DT57010Z	2	85	55	10	1	5011402385317	19.30
DT57020Z	2.5	95	66	10	1	5011402385324	20.91
DT57070Z	3	100	66	10	1	5011402385331	20.04
DT57770Z	3.1	100	66	10	1	5035048081181	NOT UK
DT57090Z	3.2	106	69	10	1	5011402385348	23.75
DT57780Z	3.3	106	69	10	1	5035048081198	NOT UK
DT57120Z	3.5	112	73	10	1	5011402385355	22.64
DT57150Z	3.8	119	78	10	1	5011402385362	24.37
DT57170Z	4	119	78	10	1	5011402385379	24.87
DT57180Z	4.1	119	78	10	1	5011402385386	25.61
DT57190Z	4.2	119	78	10	1	5011402385393	25.73

FOR USE WITH
CORDLESS AND
CORDED DRILLS



APPLICATIONS

- Suitable for portable or stationary drilling in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².



FEATURES

- Precision ground twist drill bit for rapid drilling, long life and excellent concentricity.
- Ground from solid stock right hand cutting, type N flute, precision ground at 118° point angle.
- Diameter tolerance to h8.
- Drills above 13mm (1/2") have a shank reduced to 12.7mm.

APPLICATIONS

- Used either portable or stationary for drilling of deep holes in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

**FOR USE WITH
CORDLESS AND
CORDED DRILLS**



APPLICATIONS

- Used either portable or stationary for drilling of deep holes in steel cast steel, alloyed and non-alloyed material, grey cast-iron, spherical-graphite cast iron, sintered iron, nickel, brass, etc up to 900N/mm².

FEATURES

- For drilling and enlarging existing holes from 14mm up to 34mm

FEATURES

- Full range of metal drill bits designed and optimised for use in an impact driver.
- Unique tip design eliminates walking and increases drilling speed.
- Single piece design, optimised flute angle and hardening process deliver extreme life in impact driver applications.

DRILLING

HSS-G DIN 340 LONG SERIES METAL DRILL BITS

BULK PACKS

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT57220Z	4.5	126	82	10	1	5011402385409	29.44
DT57250Z	4.8	132	87	10	1	5011402385416	31.05
DT57790Z	4.9	132	87	10	1	5035048081204	NOT UK
DT57260Z	5	132	87	10	1	5011402385423	31.05
DT57270Z	5.1	132	87	10	1	5011402385430	33.52
DT57310Z	5.5	139	91	10	1	5011402385447	36.98
DT57360Z	6	139	91	10	1	5011402385454	37.36
DT57800Z	6.1	139	91	10	1	5035048081211	NOT UK
DT57410Z	6.5	148	97	10	1	5011402385461	48.37
DT57810Z	6.8	148	97	10	1	5035048081228	NOT UK
DT57460Z	7	156	102	10	1	5011402385478	55.17
DT57480Z	7.5	156	102	10	1	5011402385485	64.70
DT57820Z	7.8	156	102	10	1	5035048081235	NOT UK
DT57830Z	7.9	156	102	10	1	5035048081242	NOT UK
DT57490Z	8	165	109	10	1	5011402385492	58.82
DT57840Z	8.5	165	109	10	1	5035048081259	NOT UK
DT57510Z	9	175	115	10	1	5011402385508	78.43
DT57850Z	9.5	175	115	10	1	5035048081266	NOT UK
DT57530Z	10	184	121	10	1	5011402385515	103.66
DT57860Z	10.2	184	121	5	1	5035048081273	NOT UK
DT57870Z	10.5	184	121	5	1	5035048081280	NOT UK
DT57550Z	11	195	128	5	1	5011402385522	60.19
DT57880Z	11.5	195	128	5	1	5035048081297	NOT UK
DT57570Z	12	200	134	5	1	5011402385539	69.89
DT57890Z	12.5	200	134	5	1	5035048081303	NOT UK
DT57590Z	13	205	134	5	1	5011402385546	76.87



STEP DRILLS

Cat. No.	Description	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT50260Z	4-12mm Step Drill	1	1	5035048077276	TBC
DT50270Z	6-18mm Step Drill	1	1	5035048077283	TBC
DT50300Z	14-25mm Step Drill	1	1	5035048077290	TBC
DT50310Z	20-34mm Step Drill	1	1	5035048077306	TBC

IMPACT DRIVER DRILL BITS

SINGLE PACKS

Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT506000Z	3	64	26	1	1	5035048081723	TBC
DT506010Z	3.2	67	29	1	1	5035048081730	TBC
DT506020Z	3.5	70	29	1	1	5035048081747	TBC
DT506030Z	4	71	30	1	1	5035048081754	TBC
DT506040Z	4.2	71	31	1	1	5035048081761	TBC
DT506050Z	4.5	75	31	1	1	5035048081778	TBC
DT506060Z	4.8	76	32	1	1	5035048081785	TBC
DT506070Z	5	78	33	1	1	5035048081792	TBC
DT506080Z	5.5	78	35	1	1	5035048081808	TBC
DT506090Z	6	80	37	1	1	5035048081815	TBC
DT506100Z	6.5	81	38	1	1	5035048081822	TBC
DT506110Z	7	89	45	1	1	5035048081839	TBC
DT506120Z	7.5	95	50	1	1	5035048081846	TBC
DT506130Z	8	102	50	1	1	5035048081853	TBC
DT506140Z	8.5	102	50	1	1	5035048081860	TBC
DT506150Z	9	102	50	1	1	5035048081877	TBC
DT506160Z	10	102	50	1	1	5035048081884	TBC
DT506170Z	11	102	50	1	1	5035048081891	TBC
DT506180Z	12	102	50	1	1	5035048081897	TBC
DT506190Z	13	102	50	1	1	5035048081914	TBC



DRILLING

WOOD DRILLING

HIGH PERFORMANCE RANGE

The DeWALT range of wood drilling bits is designed to include a wide range of hole diameters as well as drilling depths to cover the maximum of application requirements for the professional user. Whether hole quality, drilling speed or durability are required the DeWALT range has the solution.



DRILLING

SELECTING THE RIGHT DRILL BIT

BRAD POINT BITS

For drilling in hardboard, plywood, chipboard and natural hard and softwoods. Applications include dowelling and wood screw clearance holes.

TCT HINGE BORING BITS

For drilling flat bottom recess holes in hardboard, plywood, chipboard, and hard and softwoods. Applications include fitting cantilever hinges.

WOOD AUGER BITS

For rapid drilling of deep holes in plywood, chipboard, hard and softwoods. Applications include boring through beams, joists, doors etc.

EXTREME DeWALT® FLATWOOD BITS

For faster drilling and extended life in soft and hard woods, chipboard and other man-made materials. Applications include pipe / electrical clearance holes.

FLAT WOOD BITS

For fast, relatively clean drilling in hard and softwoods, chipboard and other man-made materials. Applications include pipe/electric clearance holes.

SELF-FEED BIT

EXTRA SHARP bits for very fast drilling of clean large diameter holes in hard/softwoods, and laminates.

FRAME BITS

For concrete framing applications.



SUITABLE FOR THE FOLLOWING MATERIALS



Wood



MDF



Hardboard



Chipboard



Laminates

**FOR USE WITH
CORDLESS AND
CORDED DRILLS**



Wood MDF Hardboard



Chipboard

APPLICATIONS

- Suitable for drilling hardboard, plywood, chipboard and all natural hard and softwood.
- Typically used for doweling applications or wood screw clearance holes.

FEATURES

- Manufactured from chrome vanadium alloyed steel.
- Centre location point and outer cutting spurs for clean accurate holes.

APPLICATIONS

- For very rapid and accurate drilling of clean holes in hard/softwoods and laminates.

APPLICATIONS

- Typically used to fit cantilever hinges.

FEATURES

- Tungsten carbide tipped wood boring tool for clean accurate flat bottom recess holes.
- Hexagonal shank facilitates a firm chuck grip.

DRILLING

BRAD POINT WOOD DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT45030Z	3	70	46	1	1	5011402385553	1.24
DT45040Z	4	80	52	1	1	5011402385560	1.36
DT45050Z	5	90	60	1	1	5011402385577	1.49
DT45060Z	6	100	66	1	1	5011402385584	1.60
DT45070Z	7	110	72	1	1	5011402385591	1.71
DT45080Z	8	120	80	1	1	5011402385607	2.15
DT45090Z	9	130	84	1	1	5011402385614	2.28
DT45100Z	10	133	90	1	1	5011402385621	2.62
DT45110Z	11*	150	100	1	1	5011402385638	3.76
DT45120Z	12*	155	102	1	1	5011402385645	3.87
DT45130Z	13*	155	102	1	1	5011402385652	4.33
DT45140Z	14*	160	107	1	1	5011402385669	5.30
DT45160Z	16*	165	112	1	1	5011402385683	7.52
DT45180Z	18*	200	130	1	1	5011402385690	9.54
DT45200Z	20*	200	130	1	1	5011402385706	10.72

* For diameters 11mm and above the shank is reduced to 9.5 mm.

BRAD POINT WOOD DRILL BIT SETS

Cat. No.	Description	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT45350Z	5 piece set in plastic cassette	4, 5, 6, 8, 10	5	1	5011402385713	9.42

FRAME DRILL BITS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT48700Z	7	600	1	1	5035048014035	NOT UK
DT48710Z	8	600	1	1	5035048014042	NOT UK
DT48720Z	10	600	1	1	5035048014059	NOT UK
DT48730Z	12	600	1	1	5035048014066	NOT UK
DT48740Z	16	600	1	1	5035048014073	NOT UK
DT48750Z	18	600	1	1	5035048014080	NOT UK
DT48760Z	20	600	1	1	5035048014097	NOT UK
DT48770Z	22	600	1	1	5035048014103	NOT UK


TCT HINGE BORING BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT45410Z	26	65	1	1	5011402386161	13.88
DT45420Z	30	65	1	1	5011402386178	14.45
DT45430Z	35	65	1	1	5011402386185	15.44

DRILLING

WOOD AUGER DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Working Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT46000Z	6 *	200	100	1	1	5011402385720	9.74
DT46020Z	8 *	200	100	1	1	5011402385737	9.81
DT46040Z	10 *	200	100	1	1	5011402385744	10.10
DT46060Z	12	200	100	1	1	5011402385751	10.22
DT46080Z	14	200	100	1	1	5011402385768	11.06
DT46100Z	16	200	100	1	1	5011402385775	12.63
DT46120Z	18	200	100	1	1	5011402385782	13.59
DT46140Z	20	200	100	1	1	5011402385799	15.96
DT46150Z	22	200	100	1	1	5011402385805	17.29
DT46160Z	24	200	100	1	1	5011402385812	19.06
DT46180Z	26	200	100	1	1	5011402385829	22.35
DT46190Z	28	200	100	1	1	5011402385836	25.60
DT46200Z	30	200	100	1	1	5011402385843	30.34
DT46210Z	32	200	100	1	1	5011402385850	35.40
DT46320Z	8 *	380	280	1	1	5011402385867	18.12
DT46340Z	10 *	380	280	1	1	5011402385874	18.34
DT46360Z	12	380	280	1	1	5011402385881	19.06
DT46380Z	14	380	280	1	1	5011402385898	20.09
DT46400Z	16	380	280	1	1	5011402385904	21.49
DT46420Z	18	380	280	1	1	5011402385911	26.24
DT46440Z	20	380	280	1	1	5011402385928	27.14
DT46450Z	22	380	280	1	1	5011402385935	30.34
DT46460Z	24	380	280	1	1	5011402385942	40.57
DT46480Z	26	380	280	1	1	5011402385959	42.83
DT46490Z	28	380	280	1	1	5011402385966	51.31
DT46500Z	30	380	280	1	1	5011402385973	57.52
DT46510Z	32	380	280	1	1	5011402385980	63.79


* Cylindrical shank, all other sizes hexagonal shank

SELF FEED DRILL BITS



Cat. No.	Diameter mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT45750Z	25	1	1	5035048072004	17.22
DT45760Z	28	1	1	5035048072011	21.00
DT45770Z	32	1	1	5035048072028	23.10
DT45780Z	35	1	1	5035048072035	26.88
DT45790Z	38	1	1	5035048072042	28.98
DT45800Z	41	1	1	5035048072059	29.82
DT45810Z	45	1	1	5035048072066	33.60
DT45820Z	51	1	1	5035048072073	36.96
DT45830Z	54	1	1	5035048072080	37.80
DT45840Z	57	1	1	5035048072097	41.58
DT45850Z	65	1	1	5035048072103	45.36
DT45860Z	68	1	1	5035048072110	47.46
DT45870Z	74	1	1	5035048072127	51.66
DT45880Z	76	1	1	5035048072134	55.86
DT45890Z	92	1	1	5035048072141	63.84
DT45900Z	117	1	1	5035048072158	71.40
DT45910Z	Self Feed Set - 5 pce (35mm, 38mm, 54mm, 65mm plus extension bar 140mm)	1	1	5035048072165	147.00
DT45920Z	Self Feed Extension piece 140mm	1	1	5035048072172	19.32

**FOR USE WITH
CORDLESS AND
CORDED DRILLS**



Wood MDF Hardboard



Chipboard

APPLICATIONS

- Typically used for boring clean precise holes through beams, joists, doors etc.

FEATURES

- Threaded centre point to aid accurate drilling.
- Outer cutting spur provides clean holes with less splintering.
- Special "Lewis" spiral flute allows for fast removal of debris and rapid drilling.

APPLICATIONS

- For rapid drilling of clean large diameter holes in wood.

FEATURES

- 2 x sharp cutting edges for extremely fast drilling in woods with reduced risk of binding.
- Aggressive 'Self feed' spur for rapid penetration into material.
- Non slip shank gives better bit retention in chuck.



FOR USE WITH
CORDLESS AND
CORDED DRILLS



Wood MDF Hardboard



Chipboard

APPLICATIONS

- For the rapid drilling of holes in wood.
- Suitable for natural hard and soft wood, chipboard and other man made materials.
- Ideal for door locks, mortising, electrical and plumbing work.


FEATURES

- High quality chrome vanadium flat drill bit.
- Ground central point and cutting edges for accurate location and clean cutting.
- Ground chip breaker to reduce splintering providing relatively clean holes and improved drilling efficiency.



DRILLING

FLATWOOD DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4810QZ	10	150	1	1	5011402385997	4.59
DT4812QZ	12	150	1	1	5011402386000	4.66
DT4813QZ	13	150	1	1	5011402386017	4.72
DT4814QZ	14	150	1	1	5011402386024	5.19
DT4816QZ	16	150	1	1	5011402386031	5.38
DT4818QZ	18	150	1	1	5011402386048	5.68
DT4820QZ	20	150	1	1	5011402386055	5.77
DT4822QZ	22	150	1	1	5011402386062	5.83
DT4824QZ	24	150	1	1	5011402386079	6.08
DT4825QZ	25	150	1	1	5011402386086	6.50
DT4826QZ	26	150	1	1	5011402386093	6.79
DT4828QZ	28	150	1	1	5011402386109	7.34
DT4830QZ	30	150	1	1	5011402386116	7.73
DT4832QZ	32	150	1	1	5011402386123	8.01
DT4835QZ	35	150	1	1	5011402386130	8.91
DT4838QZ	38	150	1	1	5011402386147	9.24

FLATWOOD DRILL BIT EXTENSION

Cat. No.	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4849QZ	300 x 1/4"	1	1	5035048058923	7.35


DRILLING

EXTREME DeWALT® FLATWOOD DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4760QZ	6	152	1	1	5035048072936	4.20
DT4761QZ	8	152	1	1	5035048072943	4.20
DT4762QZ	10	152	1	1	5035048072950	4.86
DT4763QZ	12	152	1	1	5035048072967	4.86
DT4764QZ	13	152	1	1	5035048072974	4.86
DT4765QZ	14	152	1	1	5035048072981	4.86
DT4766QZ	16	152	1	1	5035048072998	4.92
DT4767QZ	18	152	1	1	5035048073001	5.15
DT4768QZ	20	152	1	1	5035048073018	5.36
DT4769QZ	22	152	1	1	5035048073025	5.57
DT4770QZ	24	152	1	1	5035048073032	5.79
DT4771QZ	25	152	1	1	5035048073049	6.00
DT4772QZ	26	152	1	1	5035048073056	6.22
DT4773QZ	28	152	1	1	5035048073063	6.43
DT4774QZ	30	152	1	1	5035048073070	6.64
DT4775QZ	32	152	1	1	5035048073087	6.86
DT4776QZ	35	152	1	1	5035048073094	7.60
DT4777QZ	38	152	1	1	5035048073100	7.90
DT4778QZ	40	152	1	1	5035048073117	7.93
DT7943BQZ	8 piece set (12, 16, 18, 20, 22, 25, 28, 32)	152	1	1	5035048073292	42.84

EXTREME DeWALT® 406mm FLATWOOD DRILL BITS SINGLE PACKS



Cat. No.	Diameter mm	Length mm	Pack Qty.	M.O.Q.	Barcode	List Price Ex. VAT (£)
DT4780QZ	10	406	1	1	5035048073124	NOT UK
DT4781QZ	12	406	1	1	5035048073131	NOT UK
DT4782QZ	13	406	1	1	5035048073148	NOT UK
DT4783QZ	14	406	1	1	5035048073155	NOT UK
DT4784QZ	16	406	1	1	5035048073162	NOT UK
DT4785QZ	20	406	1	1	5035048073179	NOT UK
DT4786QZ	22	406	1	1	5035048073186	NOT UK
DT4787QZ	24	406	1	1	5035048073193	NOT UK
DT4788QZ	25	406	1	1	5035048073209	NOT UK
DT4789QZ	26	406	1	1	5035048073216	NOT UK
DT4790QZ	28	406	1	1	5035048073223	NOT UK
DT4791QZ	30	406	1	1	5035048073230	NOT UK
DT4792QZ	32	406	1	1	5035048073247	NOT UK
DT4793QZ	35	406	1	1	5035048073254	NOT UK
DT4794QZ	38	406	1	1	5035048073261	NOT UK

FOR USE WITH
CORDLESS AND
CORDED DRILLS



Wood MDF Hardboard



Chipboard

APPLICATIONS

- For the rapid drilling of holes in wood.
- Suitable for natural hard and soft wood, chipboard and other man made materials.
- Ideal for door locks, mortising, electrical and plumbing work.

FEATURES

- Extra thick robust steel shank for outstanding durability and bit life.
- Chamfered outer cutting spurs for clean, very fast drilling and extended drilling life.
- Precision ground central point with optimised design for faster material penetration and increased drilling speed.

