

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300390114](#)
Status: **Active**
Overview: [minichange_products](#)
Description: DeviceNet* Standard Cable Plus Drain, Micro-Change® to Mini-Change® Double Ended Cordset, 5 Poles, 90° Male-External Thread to 90° Female-Internal Thread, Length 6.0m (19.68')

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
UL E152210

General

Product Family Industrial Cordsets
Series [130039](#)
Connector End A Micro-Change® (M12)
Connector End B Mini-Change®
IP Rating IP67
Overview [minichange_products](#)
Product Name Micro-Change® (M12), Mini-Change®
Type Double Ended

Physical

Cable Diameter 6.86mm (.270")
Cable Length 6.0m (19.68')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Male-Female
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Contact Copper
Material - Coupling Nut Die-Cast Zinc
Material - Plating Mating Gold
Orientation 90° to 90°
Poles 5
Temperature Range - Operating -20°C to +80°C
Wire Size AWG 22
Wire/Cable Type Shielded-Twisted Pair

Electrical


Current - Maximum per Contact 4A
Voltage - Maximum 250V AC/DC

Material Info

Old Part Number DND93A-M060

Reference - Drawing Numbers

Sales Drawing SD-130039-025



EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[130039Series](#)