


REV.	DATE	ECR NO.	DESCRIPTION
NC	08/25/09	XXXXXX	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex						
7	CONTACT BODY	BRASS	NICKEL	1		DRAWN	CW						08/25/09	
6	SHELL	BRASS	NICKEL	1		CHECKED			PART DESCRIPTION N MALE TO SMA FEMALE ADAPTOR					
5	RETAINER RING	SUS 304	NATURAL	1		ISSUED								
4	GASKET	SILICONE	RED	1		SHEET	1 OF 1		PART NO. 242113					
3	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1										
2	INSULATOR	PTFE	NATURAL	1					DWG. NO. 242113.DWG REV. NC SIZE A SCALE NA					
1	BODY	BRASS	NICKEL	1										
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/CONNEX/242113.DWG							