


General characteristics

- Self-Healing
- Low losses
- High ripple current
- High contact reliability
- Suitable for high frequency applications



TECHNICAL DATA

General technical data	VDE 0560 - IEC61071 - EN61071
Application class (DIN 40040)	GPD / LS
Temperature range (Case)	-40 to + 85 °C
Max permissible ambient temperature	+70 °C
Capacitance tolerance code (15 th digit)	J = ± 5 % ; K = ± 10%
Peak non-repetitive max current	$I_{PKR} \times 1.5$
Test voltage terminal to terminal U_{TT}	2 U_n for 10 seconds
Test voltage terminal to case U_{TC}	3kV - 50Hz for 60 seconds
Dissipation factor (tgδ)	$\leq 5 \times 10^{-4}$ at 1 kHz and 20 °C
Permissible relative humidity	Annual average $\leq 95\%$ on 30 days / year, continuously 100% on other days occasionally 100%. Dewing not admissible
IEC climatic category	40 / 85 / 56 according to IEC 68-1
Capacitance deviation in the operating temperature range of -40 to +85 °C	±1.5% max on capacitance value measured at +20 °C
Change of capacitance versus operating time	-3% after 30.000 hours at U_{RMS} or after 100.000 hours at U_n
Case components	Solvent resistant plastic case with epoxy resin sealing. Flame retardant execution (UL class 94 V0).
Terminals	Tinned brass lugs
Installation	Whatever Position
Life Expectancy	≥ 30.000 hours at U_{RMS} ; ≥ 100.000 hours at U_n
Failure quota	300 / 10 ⁹ components hour

PEAK VOLTAGE TABLE

Un	850 V	1000 V	1200 V	2000 V	3000 V
Ū _{MAX}	1200 V	1300 V	1600 V	2400 V	3500 V

GENERAL CHARACTERISTICS


Code	C	Un	U _{RMS}	dV/dt	I _{PKR}	ESR max @ 100 kHz	ESL	I _{RMS} 100 kHz @ 70°C	DIMENSIONS mm		
	μF	Vdc	Vac	V/μs	A	mΩ	nH	A	B	H	L
C4BSMBX3470ZEE	0.47	850	550	1232	579	4.2	36	20	18	33	32
C4BSMBX3470Z_F	0.47	850	550	758	356	8.2	41	16	20	40	41.5
C4BSMBX3680Z_F	0.68	850	550	758	516	5.7	41	19	20	40	41.5
C4BSMBX4100Z_F	1	850	550	758	758	4.0	41	22	20	40	41.5
C4BSMBX4150Z_J	1.5	850	550	758	1138	2.7	36	29	28	37	42.5
C4BSMBX4200Z_L	2	850	550	758	1517	2.1	43	36	30	45	42
C4BSMBX4220Z_L	2.2	850	550	758	1668	1.9	43	37	30	45	42
C4BSMBX4250Z_M	2.5	850	550	469	1174	1.7	45	39	30	45	57.5
C4BSMBX4300Z_M	3	850	550	469	1408	3.0	45	32	30	45	57.5
C4BSMBX4330Z_M	3.3	850	550	469	1549	2.8	45	33	30	45	57.5
C4BSMBX4400Z_N	4	850	550	469	1878	2.3	48	36	35	50	57.5
C4BSMBX4500Z_N	5	850	550	469	2347	1.9	48	42	35	50	57.5
C4BSNBX3470ZEE	0.47	1000	600	1344	632	3.9	36	20	18	33	32
C4BSNBX3470Z_F	0.47	1000	600	827	389	7.6	41	16	20	40	41.5
C4BSNBX3680Z_F	0.68	1000	600	827	563	5.3	41	20	20	40	41.5
C4BSNBX4100Z_F	1	1000	600	827	827	3.7	41	23	20	40	41.5
C4BSNBX4150Z_J	1.5	1000	600	827	1241	2.5	36	30	28	37	42.5
C4BSNBX4200Z_L	2	1000	600	827	1655	2.0	43	36	30	45	42
C4BSNBX4220Z_M	2.2	1000	600	512	1127	3.8	45	29	30	45	57.5
C4BSNBX4250Z_M	2.5	1000	600	512	1280	3.3	45	30	30	45	57.5
C4BSNBX4300Z_M	3	1000	600	512	1536	2.8	45	33	30	45	57.5
C4BSNBX4330Z_M	3.3	1000	600	512	1690	2.6	45	34	30	45	57.5
C4BSNBX4400Z_N	4	1000	600	512	2049	2.2	48	40	35	50	57.5
C4BSPBX3330ZEE	0.33	1200	630	1568	518	5.0	36	19	18	33	32
C4BSPBX3330Z_F	0.33	1200	630	965	319	9.5	41	15	20	40	41.5
C4BSPBX3470Z_F	0.47	1200	630	965	454	6.7	41	18	20	40	41.5
C4BSPBX3680Z_F	0.68	1200	630	965	656	4.7	41	21	20	40	41.5
C4BSPBX4100Z_J	1	1200	630	965	965	3.3	36	27	28	37	42.5
C4BSPBX4120Z_J	1.2	1200	630	965	1158	2.8	36	29	28	37	42.5
C4BSPBX4150Z_L	1.5	1200	630	965	1448	2.3	43	34	30	45	42
C4BSPBX4200Z_M	2	1200	630	598	1195	3.6	45	29	30	45	57.5
C4BSPBX4220Z_M	2.2	1200	630	598	1315	3.3	45	30	30	45	57.5
C4BSPBX4250Z_M	2.5	1200	630	598	1494	2.9	45	32	30	45	57.5
C4BSPBX4300Z_N	3	1200	630	598	1793	2.5	48	37	35	50	57.5
C4BSPBX4330Z_N	3.3	1200	630	598	1972	2.3	48	39	35	50	57.5
C4BSWBX3100ZEE	0.1	2000	700	2241	224	12.9	36	12	18	33	32
C4BSWBX3100Z_F	0.1	2000	700	1379	138	23.3	41	10	20	40	41.5
C4BSWBX3150ZEE	0.15	2000	700	2241	336	8.6	36	15	18	33	32
C4BSWBX3150Z_F	0.15	2000	700	1379	207	15.6	41	12	20	40	41.5
C4BSWBX3220Z_F	0.22	2000	700	1379	303	10.7	41	14	20	40	41.5
C4BSWBX3330Z_F	0.33	2000	700	1379	455	7.2	41	17	20	40	41.5
C4BSWBX3470Z_F	0.47	2000	700	1379	648	5.1	41	20	20	40	41.5
C4BSWBX3680Z_H	0.68	2000	700	1379	938	3.6	43	26	24	44	41.5
C4BSWBX3820Z_L	0.82	2000	700	1379	1131	3.0	43	30	30	45	42
C4BSWBX4100Z_M	1	2000	700	854	854	5.1	45	24	30	45	57.5
C4BSWBX4120Z_M	1.2	2000	700	854	1024	4.3	45	26	30	45	57.5
C4BSWBX4150Z_N	1.5	2000	700	854	1280	3.5	48	31	35	50	57.5
C4BSYBX2470ZEE	0.047	3000	750	3361	158	21.9	36	10	18	33	32
C4BSYBX2470Z_F	0.047	3000	750	2068	97	36.6	41	8	20	40	41.5
C4BSYBX2680ZEE	0.068	3000	750	3361	229	15.2	36	12	18	33	32
C4BSYBX2680Z_F	0.068	3000	750	2068	141	25.4	41	10	20	40	41.5
C4BSYBX3100Z_F	0.1	3000	750	2068	207	17.3	41	12	20	40	41.5
C4BSYBX3220Z_F	0.22	3000	750	2068	455	8.0	41	17	20	40	41.5
C4BSYBX3330Z_L	0.33	3000	750	2068	683	5.4	43	24	30	45	42
C4BSYBX3470Z_M	0.47	3000	750	1280	602	7.5	45	20	30	45	57.5
C4BSYBX3680Z_N	0.68	3000	750	1280	871	5.3	48	23	35	50	57.5
C4BSYBX3820Z_N	0.82	3000	750	1280	1050	4.4	48	28	35	50	57.5

PEAK VOLTAGE TABLE


Un	250 V	400 V	600 V	700 V	850 V
Û _{MAX}	400 V	600 V	800 V	1000 V	1200V

GENERAL CHARACTERISTICS


Code	C	Un	U _{RMS}	dv/dt	I _{PKR}	ESR max @ 100 kHz	ESL	I _{RMS} 100 kHz @ 70°C	DIMENSIONS mm		
	µF	Vdc	Vac	V/µs	A	mΩ	nH	A	B	H	L
C4BTDBX4470ZEE	4.7	250	160	59	279	2.6	36	22	18	33	32
C4BTDBX4680ZEE	6.8	250	160	59	403	1.9	36	26	18	33	32
C4BTDBX5100Z_F	10	250	160	40	402	2.6	41	27	20	40	41.5
C4BTDBX5150Z_F	15	250	160	40	602	1.8	41	32	20	40	41.5
C4BTDBX5200Z_J	20	250	160	40	803	1.4	36	39	28	37	42.5
C4BTDBX5250Z_H	25	250	160	40	1004	1.2	43	43	24	44	42
C4BTDBX5300Z_L	30	250	160	40	1205	1.0	43	50	30	45	42
C4BTDBX5400Z_M	40	250	160	27	1082	1.5	45	46	30	45	57.5
C4BTDBX5500Z_N	50	250	160	27	1353	1.2	48	54	35	50	57.5
C4BTDBX5600Z_N	60	250	160	27	1624	1.1	48	58	35	50	57.5
C4BTFBX4330ZEE	3.3	400	250	74	245	3.0	36	21	18	33	32
C4BTFBX4400ZEE	4	400	250	74	296	2.5	36	23	18	33	32
C4BTFBX4400Z_F	4	400	250	50	201	4.9	41	19	20	40	41.5
C4BTFBX4500ZEE	5	400	250	74	370	2.0	36	25	18	33	32
C4BTFBX4500Z_F	5	400	250	50	251	4.0	41	22	20	40	41.5
C4BTFBX4680Z_F	6.8	400	250	50	341	3.0	41	25	20	40	41.5
C4BTFBX5100Z_F	10	400	250	50	502	2.1	41	30	20	40	41.5
C4BTFBX5125Z_J	12.5	400	250	50	627	1.7	36	35	28	37	42.5
C4BTFBX5150Z_J	15	400	250	50	753	1.5	36	38	28	37	42.5
C4BTFBX5200Z_L	20	400	250	50	1004	1.2	43	46	30	45	42
C4BTFBX5250Z_M	25	400	250	34	846	1.8	45	41	30	45	42
C4BTFBX5300Z_M	30	400	250	34	1015	1.6	45	45	30	45	42
C4BTFBX5350Z_N	35	400	250	34	1184	1.4	48	52	35	50	57.5
C4BTFBX5400Z_N	40	400	250	34	1353	1.2	48	54	35	50	57.5
C4BTHBX4250ZEE	2.5	600	330	104	259	2.9	36	21	18	33	32
C4BTHBX4250Z_F	2.5	600	330	70	176	5.7	41	18	20	40	41.5
C4BTHBX4300Z_F	3	600	330	70	211	4.8	41	20	20	40	41.5
C4BTHBX4400Z_F	4	600	330	70	281	3.6	41	23	20	40	41.5
C4BTHBX4500Z_F	5	600	330	70	351	2.9	41	25	20	40	41.5
C4BTHBX4680Z_J	6.8	600	330	70	478	2.2	41	31	28	37	42.5
C4BTHBX4800Z_H	8	600	330	70	562	1.9	43	34	24	44	42
C4BTHBX5100Z_L	10	600	330	70	703	1.6	43	40	30	45	42
C4BTHBX5125Z_M	12.5	600	330	47	592	2.5	45	35	30	45	57.5
C4BTHBX5150Z_N	15	600	330	47	710	2.1	45	38	30	45	57.5
C4BTHBX5200Z_N	20	600	330	47	947	1.7	48	47	35	50	57.5
C4BTJBX4150ZEE	1.5	700	400	119	178	4.2	36	18	18	33	32
C4BTJBX4150Z_F	1.5	700	400	80	120	8.2	41	15	20	40	41.5
C4BTJBX4200ZEE	2	700	400	119	237	3.2	36	20	18	33	32
C4BTJBX4200Z_F	2	700	400	80	161	6.2	41	17	20	40	41.5
C4BTJBX4220Z_F	2.2	700	400	80	177	5.7	41	18	20	40	41.5
C4BTJBX4300Z_F	3	700	400	80	241	4.2	41	21	20	40	41.5
C4BTJBX4400Z_F	4	700	400	80	321	3.2	41	24	20	40	41.5
C4BTJBX4500Z_J	5	700	400	80	402	2.6	36	29	28	37	42
C4BTJBX4800Z_L	8	700	400	80	642	1.7	43	38	30	45	57.5
C4BTJBX5100Z_M	10	700	400	54	541	2.7	45	34	30	45	57.5
C4BTJBX5150Z_N	15	700	400	54	812	1.9	48	44	35	50	57.5
C4BTMBX4100ZEE	1	850	450	148	148	5.1	36	16	18	33	32
C4BTMBX4100Z_F	1	850	450	100	100	9.9	41	14	20	40	41.5
C4BTMBX4150Z_F	1.5	850	450	100	151	6.7	41	17	20	40	41.5
C4BTMBX4200Z_F	2	850	450	100	201	5.1	41	19	20	40	41.5
C4BTMBX4300Z_F	3	850	450	100	301	3.4	41	23	20	40	41.5
C4BTMBX4400Z_H	4	850	450	100	402	2.6	43	29	24	44	42
C4BTMBX4500Z_L	5	850	450	100	502	2.2	43	34	30	45	42
C4BTMBX4800Z_N	8	850	450	68	541	2.8	48	37	35	50	57.5
C4BTMBX5100Z_N	10	850	450	68	677	2.3	48	40	35	50	57.5






Style	L	P	a	b	P1
A	41.5	25.5	21.5	29.5	10.5
A	42	25.5	21.5	29.5	10.5
A	42.5	25.5	21.5	29.5	10.5
A	57.5	41	37	45	25





Style	L	P	a	b	P1
B	41.5	22	16	28	6
B	42	22	16	28	6
B	42.5	22	16	28	6
B	57.5	37	31	43	21






Style	L	P	a	b	P1
F	41.5	22	16	28	6
F	42	22	16	28	6
F	42.5	22	16	28	6
F	57.5	37	31	43	21



Style	L	P	a	b	P1
G	41.5	22	4	/	10.5
G	42	22	4	/	10.5
G	42.5	22	4	/	10.5
G	57.5	37	4	/	25



Style	L	P	a	b	P1
H	41.5	25.5	21.5	29.5	10.5
H	42	25.5	21.5	29.5	10.5
H	42.5	25.5	21.5	29.5	10.5
H	57.5	41	37	45	25



Style	B	P	P1	a	b
E	18	31	44	29	33
E	20	33	46	31	35
E	22	35	48	33	37
E	24	37	50	35	39
E	28	41	54	39	43
E	30	43	56	41	45

SINGLE PACKAGE UNIT

Box dimensions	N° of pieces	Weight kgr	Box dimensions	N° of pieces	Weight kgr
20x40x41.5	54	3.0	30x45x42	36	3.4
28x37x42.5	36	2.7	30x45x57.5	27	3.2
24x44x41.5	42	3.2	35x50x57.5	23	3.5