




Part Number: BU-1111-A-**- *
Description: Mini-plunger Clip On Both Ends

2607



- Mini-plunger Clip On Both End
- Material: Hook-up wire: #20(41/36) AWG tinned copper with 105° C PVC insulation; Plunger: Nylon housing; Stainless steel spring Beryllium copper contact
- **Length: -12"(.3m), -24"(.6m), -36"(.9m), -48"(1.2m), -60"(1.5m)
- *Std Colors: -0 Black -2 Red
- Rating: Hands free testing at 300V Category II, 5 Amps
- RoHS Compliant

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mueller Electric:

[BU-5331-F-36-0](#) [BU-1420-A-24-2](#) [BU-1420-A-24-0](#) [BU-5330-F-36-0](#) [BU-5030-C-24-0](#) [BU-3070-C-48-0](#) [BU-1420-A-36-2](#) [BU-1420-A-36-0](#) [BU-5331-F-60-0](#) [BU-5330-F-60-0](#) [BU-3070-C-60-0](#) [BU-5330-F-12-0](#) [BU-5331-F-12-0](#) [BU-8080-E-6-0](#) [BU-8080-E-6-2](#) [BU-3030-A-24-5](#) [BU-3030-A-24-9](#) [BU-2031-A-48-0](#) [BU-2031-A-48-2](#) [BU-5030-C-60-0](#) [BU-5030-C-36-0](#) [BU-8080-E-12-2](#) [BU-8080-E-12-0](#) [BU-2031-A-36-0](#) [BU-3056-C-12-0](#) [BU-2031-A-36-2](#) [BU-3056-C-60-0](#) [BU-2031-A-24-0](#) [BU-2031-A-24-2](#) [BU-3056-C-24-0](#) [BU-3070-C-24-0](#) [BU-5330-F-48-0](#) [BU-5331-F-48-0](#) [BU-5030-C-48-0](#) [BU-5031-C-12-0](#) [BU-5030-C-12-0](#) [BU-8080-E-24-2](#) [BU-8080-E-24-0](#) [BU-8080-E-36-2](#) [BU-8080-E-36-0](#) [BU-2031-A-12-0](#) [BU-2031-A-12-2](#) [BU-5331-F-24-0](#) [BU-5330-F-24-0](#) [BU-3070-F-24-0](#) [BU-1420-A-12-2](#) [BU-1420-A-60-2](#) [BU-1420-A-12-0](#) [BU-1420-A-60-0](#) [BU-3070-C-12-0](#) [BU-3070-F-48-0](#) [BU-1420-A-48-2](#) [BU-1420-A-48-0](#) [BU-3070-F-12-0](#) [BU-3070-C-36-0](#) [BU-3056-C-36-0](#) [BU-3056-C-48-0](#) [BU-3070-F-36-0](#) [BU-30503-0](#) [BU-2031-A-60-0](#) [BU-2031-A-60-2](#) [BU-3070-F-60-0](#) [BU-1111-A-12-0](#) [BU-1080-E-24-2](#) [BU-1480-E-24-2](#) [BU-1414-E-48-2](#) [BU-1121-A-36-2](#) [BU-1212-A-60-0](#) [BU-1212-A-60-2](#) [BU-1449-E-36-2](#) [BU-1450-C-36-0](#) [BU-1450-C-24-0](#) [BU-1153-F-36-0](#) [BU-1170-C-24-0](#) [BU-1212-A-12-2](#) [BU-1170-C-48-0](#) [BU-1414-E-36-0](#) [BU-1481-E-24-2](#) [BU-1031-A-48-2](#) [BU-1031-A-12-2](#) [BU-1080-E-36-2](#) [BU-1153-F-24-0](#) [BU-1031-A-36-2](#) [BU-1080-E-24-0](#) [BU-1414-E-48-0](#) [BU-1153-F-12-0](#) [BU-5454-B-12-0](#) [BU-1170-C-36-0](#) [BU-1414-E-12-0](#) [BU-1449-E-36-0](#) [BU-1031-A-24-2](#) [BU-1031-A-24-0](#) [BU-1414-E-12-2](#) [BU-1170-F-48-0](#) [BU-5454-B-36-0](#) [BU-1170-F-60-0](#) [BU-1170-C-60-0](#) [BU-1212-A-36-2](#) [BU-1156-C-48-0](#) [BU-1080-E-12-0](#)