

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301090028](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Pro-Yellow Nylon 26W Fluorescent Hand Lamp with Switch and Grips Molded, Cord Type 18/3 SJTW, Cord Length 7.62m (25.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E59049

General

Product Family Portable Lighting
Series [130109](#)
NEMA Configuration NEMA 5-15
Outlet None
Overview [Hand Lamps](#)
Product Name Pro-Yellow
Type Hand Lamps
UPC 78678851149

Physical

Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary N/A
Depth N/A
Duty Commercial
Guard Included No
Guard Type N/A
Height N/A
Length N/A
Material - Guard Polycarbonate
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 18/3 SJTW
Lamp Type PL-C 26/41/4P
Lamp Wattage - Maximum 26W
Lumens 1800
On/Off Switch Yes
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number WT6F-25



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

[130109](#) Series