



PART NAME	SERIES 60 UPRIGHT ADD-A-RACK	PART No.	60-2500 TD 60-2513	REV. DATE	1-2-02
-----------	------------------------------	----------	--------------------	-----------	--------


FINISH:
 FRAME ASSEMBLY, DOOR, TOP COWLS & TOP COVER _____ GRAY TEXTURE OR ROYAL BLUE TEXTURE
 PANEL MOUNTING RAILS _____ SMOOTH BLACK

MATERIAL:
 PANEL MOUNTING RAILS _____ 12 GA. STEEL
 FRAME TOP, BASE ASSEMBLY, FILLERS & VERTICAL RAILS _____ 14 GA. STEEL
 RAIL SUPPORTS _____ 16 GA. STEEL
 TOP COWLS & TOP COVER _____ 18 GA. STEEL
 DOOR _____ 20 GA. STEEL



TOP VIEW

TOP VIEW
(LESS TOP COVER & TOP COWLS)



REAR VIEW

LEFT SIDE VIEW


FRONT VIEW

SECTION "A-A"

PANEL MOUNTING RAILS (FRONT & REAR) ARE TAPPED #10-32 ON E.I.A. UNIVERSAL SPACING AND ARE FULLY ADJUSTABLE.

BOTTOM PIERCED FOR MOUNTING RC-7758 CASTERS.

LOAD RATING: 1200 LBS. MAX.



BOTTOM VIEW

PART No.	P.S.	A	B	C	D	E	F	G	H	J	K	L	M
60-2500	21.000	29.625	22.000	20.500	17.000	29.000	26.875	18.937	—	—	—	—	—
60-2501	31.500	40.125	—	—	—	39.500	37.375	29.437	—	—	—	—	—
60-2502	42.000	50.625	—	—	—	50.000	47.875	—	19.281	17.906	—	—	—
60-2503	52.500	61.125	—	—	—	60.500	58.375	—	24.531	23.156	—	—	—
60-2504	61.250	69.875	—	—	—	69.250	67.125	—	28.906	27.531	—	—	—
60-2505	70.000	78.625	—	—	—	78.000	75.875	—	33.281	31.906	—	—	—
60-2506	78.750	87.375	22.000	20.500	17.000	86.750	84.625	—	—	—	25.125	22.312	23.750
60-2507	21.000	29.625	25.500	24.000	20.500	29.000	26.875	18.937	—	—	—	—	—
60-2508	31.500	40.125	—	—	—	39.500	37.375	29.437	—	—	—	—	—
60-2509	42.000	50.625	—	—	—	50.000	47.875	—	19.281	17.906	—	—	—
60-2510	52.500	61.125	—	—	—	60.500	58.375	—	24.531	23.156	—	—	—
60-2511	61.250	69.875	—	—	—	69.250	67.125	—	28.906	27.531	—	—	—
60-2512	70.000	78.625	—	—	—	78.000	75.875	—	33.281	31.906	—	—	—
60-2513	78.750	87.375	25.500	24.000	20.500	86.750	84.625	—	—	—	25.125	22.312	23.750