

HC-B 24-AMLD-AL

Order No.: 1645493

Illustration shows a version with plastic cover

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1645493>

HEAVYCON panel mounting base B24, with single locking latch,
height 27 mm, with aluminum cover

Commercial data

GTIN (EAN)	
sales group	D002
Pack	10 pcs.
Customs tariff	85369010
Catalog page information	Page 497 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
03/01/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data


General data

Note	For contact inserts HC-B24, BB46, D64, DD108, M
Design	B24
Height	27 mm
Width	43 mm
Length	140 mm


Housing type	Panel mounting base with cover
Locking type	With single locking latch
Protective cover	Yes
Degree of protection	IP65 protection when the connector is inserted
Ambient temperature (operation)	-40 °C ... 125 °C
Housing material	Aluminum, die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR
Material lock	High-grade steel, handle: PA-GF
Material grip body interlock	PA-GF
Material, protective cover	Al
Length of the assembly cutout	113 mm
Width of the assembly cutout	35 mm

Diagrams/Drawings

Dimensioned drawing



Dimensional drawing



Panel cutout

Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2010 Phoenix Contact
Technical modifications reserved;