

Search Results

- Evaluate
- FAQ's

- Performance Data

- PDF-ETL Channel ..

- PDF-ETL 4 Connec ..

- Product Bulletins

- PDF-TX6A-SD 10Gi ..

- Technology Briefs

- PDF-Panduit, Cis ..

- PDF-Panduit, Cis ..

- Videos

- WMV-Ecosystem Su ..

- WMV-Panduit and ..
- Design a Solution
- Specification Sheets

- PDF-TX6A-SD 10Gi ..
- How to Buy
- Bill of Material

- Favorite Products List

- Locate Distributor
- Install & Maintain
- Installation Instructions

- PDF-Mini-Com TX6 ..

- PDF-TX6A 10Gig C ..

Home > Product On-Line Catalog > Search Results >


Current refinements (click  to remove)

Search Tips 

 **Text Search: 'PUR6ASD04YL-UG'**

Your search criteria matched only one product, shown below

PUR6ASD04YL-UG



- Exceeds electrical and alien crosstalk requirements of ANSI/TIA-568-C.2 Category 6A, IEEE 802.3an-2006, and ISO 11801 Class E_A channel standards up to 70 meters (229 feet)
- Meets IEEE 802.3af and IEEE 802.3af for PoE applications
- Patent-pending cable design suppresses alien crosstalk with enhanced internal electrical performance
- Round cable design with reduced cable diameter enables improved cable bundling and optimizes fill capacity
- Ideal for distances up to 70 meters, offering smaller cable diameter compared to Category 6 cable; cable diameter 0.240 in. (6.1mm) nominal
- Installation temperature range: 32°F to 140°F (0°C to 60°C)
- Operating temperature range: -4°F to 167°F (-20°C to 75°C)
- Descending length cable markings enable easy identification of remaining cable which reduces installation time and cable scrap

▪ Part Number	PUR6ASD04YL-UG
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Category 6A, riser (CMR), 4-pair, UTP copper cable. Copper conductors are 26 AWG with flame-retardant PVC insulation. Conductors are twisted in pairs, separated by an integrated pair divider, surrounded by a patent-pending matrix tape and protected by a flame-retardant PVC jacket. Ideal for installations up to 70 meters.
▪ Product Type	Copper Cable
▪ Color	Yellow
▪ Cable Color	Yellow
▪ Cable Type	UTP
▪ CE Compliant	No
▪ Flammability Rating	CMR
▪ Performance Level	Category 6A/Class EA
▪ Pricing Description	Copper Cable, Cat 6A, 4-Pair, 26 AWG, UTP, CMR, Yellow, 1000 Feet/305m
▪ Min. Order UOM	FT
▪ Min. Order Qty.	9000
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.