

Metallic Liquidtight Fittings

Flexible Metallic Conduit Fittings



Straight Conduit Fitting

Trade Size (metric designator)	Insulated	Non-Insulated
3/8" (12)	H0381	H038
1/2" (16)	H0501A	H050A
3/4" (21)	H0751A	H075A
1" (27)	H1001	H100
1 1/4" (35)	H1251	H125
1 1/2" (41)	H1501	H150
2" (53)	H2001	H200
2 1/2" (63)	H2501	—
3" (78)	H3001	—

Note: See page T-118 for additional technical data.



Straight with Male
Hubbell Conduit
Fitting
H0501A



45° Conduit Fitting

Trade Size (metric designator)	Insulated	Non-Insulated
3/8" (12)	H03841	H0384
1/2" (16)	H05041	H0504
3/4" (21)	H07541	H0754
1" (27)	H10041	H1004
1 1/4" (35)	H12541	H1254
1 1/2" (41)	H15041	H1504
2" (53)	H20041	H2004

Note: See page T-118 for additional technical data.



45° Angle with Male
Hubbell Conduit
Fitting
H05041



90° Conduit Fitting

Trade Size (metric designator)	Insulated	Non-Insulated
3/8" (12)	H03891	H0389
1/2" (16)	H05091	H0509
3/4" (21)	H07591	H0759
1" (27)	H10091	H1009
1 1/4" (35)	H12591	H1259
1 1/2" (41)	H15091	H1509
2" (53)	H20091	H2009

Note: See page T-118 for additional technical data.



90° Angle with Male
Hubbell Conduit
Fitting
H0509