





LOC		DIST		P		F		ZONE		LTR		REVISIONS		DATE		APPD	
CM		53										D	REV PER EC 061B-0103-98	6-11-98	JH	R5	


- 1 0.00076 [.000030] MIN GOLD IN LOCALIZED GOLD PLATE AREA OVER 0.00127 [.000050] MIN NICKEL.
- 2 WIRE RANGE: 0.3 - 0.84mm² (24-18 AWG).
- 3 INSULATION RANGE: 2.79 [.110] MAX. DIA.
- 4 DIMENSIONS IN BRACKETS ARE IN INCHES.




SECTION A-A
SCALE 10:1



SECTION B-B
SCALE 10:1



SECTION C-C
SCALE 10:1



SECTION D-D
SCALE 10:1

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

	1	0.25 [.010] BRASS	770147-5
	PRE-TIN	0.25 [.010] BRASS	770147-1
FINISH		MATERIAL	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± - MATERIAL	DR 11-3-93 R. VESTAL	NAME
	CHK 11-3-93 R. SWING	
	APPD 11-3-93 C. CASH	
	APPD 11-3-93 C. CASH	
SEE TABLE	PRODUCT SPEC -	PIN, .093, LOOSE PIECE, COMMERCIAL PIN AND SOCKET
FINISH	APPLICATION SPEC -	
SEE TABLE	WEIGHT -	

AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME		
PIN, .093, LOOSE PIECE, COMMERCIAL PIN AND SOCKET		
SIZE	CAGE CODE	DRAWING NO
D 00779	C-770147	
SCALE	5:1	SHEET 1 OF 1

CUSTOMER DRAWING