

LABFACILITY

TEMPERATURE & PROCESS TECHNOLOGY


Standard Quick Wire Sockets



'Just push-in wire & tighten screw'

- Standard in-line quick wire socket allowing rapid termination of wires
- Easy 'jab-in' connection, just push-in wire & tighten screw
- Accepts standard round plug pins
- Available in Thermocouple types K, J, T, E, N, R/S, B
- For Types K, J, T, E & N contacts are made from true Thermocouple alloys
- B type has compensating copper/copper contacts
- Contacts are polarised to prevent incorrect connection
- Colour coded in accordance with IEC specification

T/C Type	Colour Code (IEC)	+Positive Contact (alloy type)	-Negative Contact (alloy type)	Product Code	Farnell order Code
K	Green	+Nickel Chromium	-Nickel Alloy	IS-K-FQ	381-0331
J	Black	+Iron	-Copper Nickel	IS-J-FQ	381-0320
B	Grey	+Copper	-Copper	IS-B-FQ	234-7072
E	Violet	+Nickel Chromium	-Copper Nickel	IS-E-FQ	234-7073
N	Pink	+Nickel/Chro/Silicon	-Nickel Silicon	IS-N-FQ	234-7074
R/S	Orange	+Copper	-Copper Alloy	IS-R/S-FQ	234-7075
T	Brown	+Copper	-Copper Nickel	IS-T-FQ	234-7077



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com