



FEATURES

- DVI - analog to 15 pin VGA adapter
- High cycle, dual beam low insertion force contacts
- D- subminiature adapting end is polarized
- Fully shielded to protect against EMI / RFI
- 4-40 threaded insert with thumbscrew
- Available in both long and short versions

SPECIFICATIONS

- Insulator material: UL94V-0 thermoplastic polyester
- Shell material: Nickel or tin plated steel
- Current rating: 1.5 amperes
- Dielectric withstanding voltage: 500V for 10 milliseconds
- Insulator resistance: 1000 Megohms at 100V DC
- Voltage: 40 V
- Impedance: 75 Ohms +/- 10% on co-axial wires

SERIES 628 ADAPTERS / CABLE ASSEMBLIES

ORDERING GUIDE

628 - 000 - 924

SERIES

EDAC INTERNAL

PRODUCT TYPE

SERIES

628 Series

PRODUCT TYPE

921	DVI / HD 15 cable assembly
922	LFH60 / HD 15 cable assembly
923	LFH60 / DVI cable assembly
924	DVI / HD 15 adapter
924S	DVI / HD15 adapter - short black
924W	DVI / HD15 adapter - short white
932	USB A / USB B cable assembly
935	RJ11 cable assembly
936	RJ45 cable assembly
937	SMB / SMB cable assembly
940	USB A / mini USB B cable assembly
944	USB B / USB B cable assembly
945	BNC / SMB cable assembly
953	Serial internal cable assembly
954	Multiple video cable assembly
955	LFH60 / 6XBNC cable assembly
957	LFH60 / 4XSCART cable assembly

*For a more complete listing of products, please contact edac@edac.net

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[EDAC:](#)

[628-000-943](#) [628-000-900](#) [628-000-901](#) [628-000-902](#) [628-000-904](#) [628-000-906-2](#) [628-000-920](#) [628-000-921](#)
[628-000-924](#) [628-000-960A](#) [628-000-969](#) [628-001-021](#)