

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com



Female connectors with clamping yoke screw connection for conductor connection with straight (180°) outlet direction. The female connectors provide space for labelling and can be coded. Can be fastened with flange or release latch. They feature an integrated plus/minus screw, protection against false insertion under clamping yoke. They are delivered with an opened clamping yoke.

- 0.2-2.5 mm² (IEC) / 26-12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	1943810000
Part designation	BLZP 5.08/02/180 SN BK BX
Version	PCB plug-in connector, female plug, 5.08 mm, No. of poles: 2, 180°, Clamping yoke connection, Clamping range, max.: 4 mm ² , Box
GTIN (EAN)	4032248617821
Qty.	100 pc(s).
Packaging	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

System parameters

Conductor connection system	Clamping yoke connection	Outgoing direction of conductor	180°
Pitch in mm	5.08 mm	Pitch in inch	0.2 inch
No. of poles	2	No. of rows	1
Screwdriver blade	0.6 x 3.5	Screwdriver blade standard	DIN 5264
Tightening torque, min.	0.4 Nm	Tightening torque, max.	0.5 Nm
Clamping screw	M 2.5	Stripping length	7 mm
L1 in mm	5.08 mm	L1 in inch	0.2 inch
Electric shock protection to DIN VDE 57 106 Safe from finger touch			

Material data

Insulating material	PBT	Colour	black
colour chart	Similar to RAL 9011	Flammability class UL 94	V-0
CTI	≥ 200	Contact material	Copper alloy
Contact surface	tinned	Contact base material	Copper alloy
Highest continuous operating temperature, min.	-25 °C	Highest continuous operating temperature, max.	100 °C

Connectable conductors

Clamping range, min.	0.13 mm ²	Clamping range, max.	4 mm ²
Conductor connection cross-section AWG, min.	AWG 26	Conductor connection cross-section AWG, max.	AWG 12
Solid, min. H05(07) V-U	0.2 mm ²	Solid, max. H05(07) V-U	4 mm ²
Flexible, min. H05(07) V-K	0.2 mm ²	Flexible, max. H05(07) V-K	4 mm ²
w. wire end ferrule, DIN 46228 pt 1, min.	0.2 mm ²	with wire end ferrule, DIN 46228 pt 1, max.	4 mm ²
w. plastic collar ferrule, DIN 46228 pt 4, min.	0.2 mm ²	with plastic collar ferrule, DIN 46228 pt 4, max.	2.5 mm ²
Gauge to EN 60999 a x b; ø	2.8 mm x 2.4 mm		

DIN IEC rating data

Rated current, min. No. of poles (Tu=20°C)	19 A	Rated current, max. No. of poles (Tu=20°C)	15.5 A
Rated current, no. of poles (Tu=40°C), min.	16 A	Rated current, no. of poles (Tu=40°C), max.	13 A
Rated voltage for overvoltage class/pollution severity II/2	400 V	Rated voltage for overvoltage class/pollution severity III/2	320 V
Rated voltage at overvoltage category/pollution degree III/3	250 V	Rated impulse withstand voltage for overvoltage class/pollution severity II/2	4 kV
Rated impulse withstand voltage for overvoltage class/pollution severity III/2	4 kV	Rated impulse withstand voltage for overvoltage class/pollution severity III/3	4 kV
Short-time withstand current resistance	3 x 1s with 120 A		

CSA rating data

Rated voltage (Use group B)	300 V	Rated current (use group B)	10 A
Rated voltage (Use group C)	50 V	Rated voltage (use group D)	300 V
Rated current (use group D)	10 A	Wire cross-section, AWG, min.	AWG 26
Wire cross-section, AWG, max.	AWG 12		

UL 1059 rating data

Rated voltage (use group B)	300 V	Rated current (use group B)	10 A
Rated voltage (use group C)	50 V	Rated voltage (use group D)	300 V
Rated current (use group D)	10 A	Wire cross-section, AWG, min.	AWG 26
Wire cross-section, AWG, max.	AWG 12		

System pitch 5.08 mm (0.200 inch)
BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Approvals

Approvals institutes	CURUS
----------------------	-------

Classifications

eClass 6.0	27-26-07-08
------------	-------------



Notes

Notes	• Additional colours on request • Rated current related to rated cross-section and min. No. of poles. • Wire end ferrule without plastic collar to DIN 46228 pt 1 • Wire end ferrule with plastic collar to DIN 46228 pt 4 • P on drg. = pitch • Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards.
-------	--

System pitch 5.08 mm (0.200 inch)
BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Drawings



System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SLD 5.08/90G



2-tier male connector with parallel pin arrangement. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 11 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1601790000	SLD 5.08/04/90G 3.2SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 4, 90°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190055752	50 pc(s).	Box

SL-SMT 5.08/180G Box



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1838210000	SL-SMT 5.08/02/180G 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248348275	100 pc(s).	Box
1775922001	SL-SMT 5.08/02/180G 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248158911	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL-SMT 5.08/180 Tape



High-temperature-resistant, straight, open ended male connector. Packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1821100000	SL-SMT 5.08/02/180 1.5 SN BK RL	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248319749	250 pc(s).	Tape

SL 5.08/135



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 17 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1603060000	SL 5.08/02/135 3.2SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 135°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190095512	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL 5.08/180



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1517260000	SL 5.08/02/180 3.2 SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190034795	100 pc(s).	Box

SLD 5.08/180G



2-tier male connector with parallel pin arrangement. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 11 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1602390000	SLD 5.08/04/180G 3.2SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 4, 180°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190180539	50 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL 5.00/90



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1625990000	SL 5.00/02/90 4.5SN BK BX	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 90°, Solder pin length: 4.5 mm, tinned, black, Solder connection, Box	4008190197292	100 pc(s).	Box
1571130000	SL 5.00/02/90 3.2SN OR BX	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190156121	100 pc(s).	Box

SL-SMT 5.08/180G Tape



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1820170000	SL-SMT 5.08/02/180G 1.5 SN BK RL	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248315680	250 pc(s).	Tape

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL 5.08/90




Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1508060000	SL 5.08/02/90 3.2SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190189006	100 pc(s).	Box

SLDF 5.08



Male connector for through-panel mounting with optional locking function. Internal connection as flat-blade or solder connection. These male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1599130000	SLDF 5.08 L/F 2 SN OR	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Clamping range, max.: , Box	4008190175931	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL-SMT 5.08/90 Tape



High-temperature-resistant, 90° angled, open male connector. Packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1821160000	SL-SMT 5.08/02/90 1.5 SN BK RL	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248319800	350 pc(s).	Tape

SL-SMT 5.08/180 Box



High-temperature-resistant, straight, open ended male connector. Packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1837980000	SL-SMT 5.08/02/180 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248348046	100 pc(s).	Box
1775522001	SL-SMT 5.08/02/180 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248157549	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL-SMT 5.08/90G Box



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1780180000	SL-SMT 5.08/02/90G 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248165506	100 pc(s).	Box
1775002001	SL-SMT 5.08/02/90G 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248156023	100 pc(s).	Box

SL-SMT 5.08/90G Tape



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1821140000	SL-SMT 5.08/02/90G 1.5 SN BK RL	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248319787	350 pc(s).	Tape

System pitch 5.08 mm (0.200 inch)
BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

SL-SMT 5.08/90 Box



High-temperature-resistant, 90° angled, open male connector. Packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1779950000	SL-SMT 5.08/02/90 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248165278	100 pc(s).	Box
1774762001	SL-SMT 5.08/02/90 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248155699	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZF 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SLZF 5.08/180FI



Male connector with tension clamp connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1846510000	SLZF 5.08/02/180FI SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Tension clamp connection, Clamping range, max.: 3.31 mm ² , Box	4032248362813	100 pc(s).	Box

SL-SMT 5.08/180LF Box



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1838440000	SL-SMT 5.08/02/180LF 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248348503	100 pc(s).	Box
1776362001	SL-SMT 5.08/02/180LF 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248159147	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZF 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SLZF 5.08/270B




Male connector with tension clamp connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1706140000	SLZF 5.08/02/270B SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 270°, Tension clamp connection, Clamping range, max.: 3.31 mm ² , Box	4032248113996	100 pc(s).	Box

SLZF 5.08/180B



Male connector with tension clamp connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1710210000	SLZF 5.08/02/180B SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Tension clamp connection, Clamping range, max.: 3.31 mm ² , Box	4008190319526	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL 5.08/180B



Male connectors with straight outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1519560000	SL 5.08/02/180B 3.2 SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190083892	100 pc(s).	Box

SLZF 5.08/180F



Male connector with tension clamp connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data


Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1846930000	SLZF 5.08/02/180F SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Tension clamp connection, Clamping range, max.: 3.31 mm ² , Box	4032248363100	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SLS 5.08/180B



Male connector with screw clamping yoke connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21.5 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1627240000	SLS 5.08/02/180B SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Box	4008190199753	100 pc(s).	Box

SLZF 5.08/90B



Male connector with tension clamp connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 23 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1673550000	SLZF 5.08/02/90B SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 90°, Tension clamp connection, Clamping range, max.: 3.31 mm ² , Box	4008190435264	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL-SMT 5.08/90F Box




High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1837630000	SL-SMT 5.08/02/90F 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248347445	100 pc(s).	Box

SL-SMaRT 5.0x/90 Tape



High-temperature-resistant male connector for side-by-side mounting. Packed in tape with 1.5 mm solder pin. Optimised for automatic assembly and suitable for reflow soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 15 A (UL)

General ordering data


Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1812430000	SL-SMaRT 5.0X/02/90 1.5SN BK RL	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248294015	350 pc(s).	Tape

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL-SMaT 5.0x/180 Tape



High-temperature-resistant male connector for side-by-side mounting. Packed in tape with 1.5 mm solder pin. Optimised for automatic assembly and suitable for reflow soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 16.5 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1812450000	SL-SMaT 5.0X/02/180 1.5SN BK RL	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248294039	270 pc(s).	Tape

SL-SMT 5.08/180LF Tape



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1776364001	SL-SMT 5.08/02/180LF 1.5 SN BK RL	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248163472	250 pc(s).	Tape

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL 5.08/135B



Male connectors with 135° outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 17 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1605530000	SL 5.08/02/135B 3.2SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 135°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190104290	100 pc(s).	Box

SL-SMT 5.08/180F Box



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1837320000	SL-SMT 5.08/02/180F 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248345915	100 pc(s).	Box
1837860000	SL-SMT 5.08/02/180F 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 180°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248347674	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SLT 5.08B



Male connectors with screw TOP connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 14 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 16 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1611710000	SLT 5.08/02/180B SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, TOP connection, Clamping range, max.: 2.5 mm ² , Box	4008190192594	100 pc(s).	Box

SL-SMT 5.08/90LF Tape



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1775234001	SL-SMT 5.08/02/90LF 1.5 SN BK RL	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248167784	350 pc(s).	Tape

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL-SMT 5.00/90LF Tape




High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1797750000	SL-SMT 5.00/02/90LF 1.5SN BK RL	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Tape	4032248239757	350 pc(s).	Tape

SL 5.08/90B



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1510360000	SL 5.08/02/90B 3.2SN OR BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190180188	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL-SMT 5.00/90LF Box



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1797230000	SL-SMT 5.00/02/90LF 1.5SN BK BX	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248238019	100 pc(s).	Box
1840350000	SL-SMT 5.00/02/90LF 3.2SN BK BX	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248351091	100 pc(s).	Box

SLDV-THR 5.08/180F



High-temperature-resistant, 2-tier, laterally offset male connector with flange or solder flange. 1.5 mm solder pin suitable for reflow soldering. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1828770000	SLDV-THR 5.08/04/180F 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 4, 180°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248335442	50 pc(s).	Box
1828890000	SLDV-THR 5.08/04/180F 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 4, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248335589	50 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SLDV-THR 5.08/180FLF



High-temperature-resistant, 2-tier, laterally offset male connector with flange or solder flange. 1.5 mm solder pin suitable for reflow soldering. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 15 A (IEC) / 10 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1829130000	SLDV-THR 5.08/04/180FLF 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 4, 180°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248335824	50 pc(s).	Box
1829010000	SLDV-THR 5.08/04/180FLF 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 4, 180°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248335701	50 pc(s).	Box

SL-SMT 5.08/90LF Box



High-temperature-resistant male connector, packed in box or tape. In tape with 1.5 mm solder pin optimised for automatic assembly. 3.2 mm solder pin suitable for reflow and wave soldering. These male connectors can be labelled and coded.

- 400 V (IEC) / 300 V (UL)
- 19 A (IEC) / 15 A (UL)

General ordering data


Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1775232001	SL-SMT 5.08/02/90LF 1.5SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 1.5 mm, tinned, black, Reflow solder connection, Box	4032248157211	100 pc(s).	Box
1780410000	SL-SMT 5.08/02/90LF 3.2SN BK BX	PCB plug-in connector, male header, 5.08 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, black, Reflow solder connection, Box	4032248165735	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch) BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Counterpart

SL 5.00/90B



Male connectors with 90° outlet direction. The solder pin length is optimised for wave flow soldering. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 400 V (IEC) / 300 V (UL)
- 18 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1580860000	SL 5.00/02/90B 3.2SN OR BX	PCB plug-in connector, male header, 5 mm, No. of poles: 2, 90°, Solder pin length: 3.2 mm, tinned, Orange, Solder connection, Box	4008190054489	100 pc(s).	Box

SLS 5.08/180F



Male connector with screw clamping yoke connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21.5 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1846360000	SLS 5.08/02/180F SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Clamping yoke connection, Clamping range, max.: 3.31 mm², Box	4032248362066	100 pc(s).	Box

System pitch 5.08 mm (0.200 inch)
BLZP 5.08/02/180 SN BK BX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Counterpart

SLS 5.08/180FI



Male connector with screw clamping yoke connection for connecting conductors. The male connectors provide space for labelling and can be coded. Packed in cardboard box.

- 0.20 - 2.5 mm² (IEC) / 26 - 12 AWG (UL)
- 400 V (IEC) / 300 V (UL)
- 21.5 A (IEC) / 15 A (UL)

General ordering data

Order No.	Part designation	Version	GTIN (EAN)	Qty.	Packaging
1846210000	SLS 5.08/02/180FI SN OR BX	PCB plug-in connector, male plug, 5.08 mm, No. of poles: 2, 180°, Clamping yoke connection, Clamping range, max.: 3.31 mm ² , Box	4032248362493	100 pc(s).	Box