



Search Results

- Evaluate
- FAQ's
- Design a Solution
- Part Draw ings

- PDF-Single Gang ..

- DWG-Single Gang ..
- How to Buy
- Bill of Material

- Favorite Products List

- Locate Distributor

Home > Products Overview > Search Results >

Current refinements (click to remove) [Search Tips](#) Within Results

Text Search: 'JBP1IW'

Your search criteria matched only one product, shown below

JBP1IW



Pan-Way® Power Rated Surface Mount Outlet Boxes are UL 5A listed to 600V and CSA Certified to 300V. For use with LDP, LDS, and T-45. *Pan-Way*® Low Voltage Surface Mount Outlet Boxes are one and two-gang style boxes for low voltage and or fiber optic applications. JBX3510**, JB1**, and JB1D** are supplied with adhesive backing. All surface mount outlet boxes are available in four colors, IW (Off White) with EI (Electric Ivory), IG (International Gray) or WH (White).

- JBX3510 assembles without the use of screws for faster installation
- JBX3510, JB1, and JB1D are supplied with adhesive backing to speed installation
- JB1 and JB1D are a one-piece design requiring no assembly

Part Number	JBP1IW
RoHS Compliancy Status	Compliant
Part Description	Single gang two-piece screw together outlet box. Box accepts Pan-Way® Screw-On Faceplates or any NEMA standard single gang faceplate. For use with Pan-Way® LD profile raceway. 5.19"L x 3.45"W x 1.75"H (131.9mm x 87.7mm x 44.4mm). Breakouts for 1/2", 3/4", or 1" diameter conduit.
Product Type	Power Rated
Color	Off White
Pricing Description	Single Gang Power Rated 2-piece Outlet Box
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.