

PC SCREW TERMINALS

These easy-to-mount, multipurpose screw type terminals are a practical, low-cost alternative to PC screw type edge connectors, barrier blocks, terminal boards and terminal strips. Steadfast and easy to install, will accommodate solid or stranded wire, crimp type terminals or lugs. Multi-placement of these low-profile terminals make them ideally suited for high density packaging. Supplied unassembled or with screw installed and captivated.

PRINCIPAL FEATURES

- Low profile
- Stable, no-rock design with exclusive anti-rotational feature
- Easily mounts with four legs into pre-drilled or punched holes
- Accepts 14-22 AWG solid or stranded wire, crimp type terminals or lugs
- Ideally suited for high-density packaging
- Available in horizontal or vertical mounting
- Space-saving and time saving
- Easy accessibility for PC board testing
- Binding screw is positioned above board level to avoid wicking during wave soldering
- Terminals are made of Brass with Tin Plate
- Supplied with a combination drive 6-32 binding head screw




**SNAP-IN
PC MOUNT**

- Color coded screws available (add color screw suffix to Cat. No.)

CAT. NO. 7779 (No Screw Supplied)

CAT. NO. 7690 (Screw Supplied Unassembled)

CAT. NO. 7692 (Screw Installed & Captivated)



COLOR SELECTION:
Select desired screw terminal and add color suffix to the screw terminal Cat. No.

HEAD COLOR	SUFFIX
RED	-2
BLACK	-3
WHITE	-4
BLUE	-5
GREEN	-6
YELLOW	-7
NICKEL	none



7693-5


7700

HORIZONTAL TYPE


SPECIFICATIONS

Rated: 15 Amps
Terminal: .032 (.81) Brass, Matte Tin Plate
Binding Head Screw: Brass, Nickel Plate

Mounting Detail



Color coded screws available (add color screw suffix to Cat. No.)



7700-3

PC MOUNT

- Color coded screws available (add color screw suffix to Cat. No.)

CAT. NO. 7781 (No Screw Supplied)


CAT. NO. 8190 (Screw Supplied Unassembled)

CAT. NO. 7700 (Screw Installed & Captivated)



**SNAP-IN
PC MOUNT**


7773



SPECIFICATIONS

Rated: 15 Amps
Terminal: .032 (.81) Brass, Matte Tin Plate
Binding Head Screw: Brass, Nickel Plate

Mounting Detail




CAT. NO. 7774 (No Screw Supplied)

CAT. NO. 7773 (Screw Supplied Unassembled)



**SNAP-IN
PC MOUNT**

7693-4



- Color coded screws available (add color screw suffix to Cat. No.)

CAT. NO. 7780 (No Screw Supplied)

CAT. NO. 7691 (Screw Supplied Unassembled)


CAT. NO. 7693 (Screw Installed & Captivated)

VERTICAL TYPE


SPECIFICATIONS

Rated: 15 Amps
Terminal: .032 (.81) Brass, Matte Tin Plate
Binding Head Screw: Brass, Nickel Plate

Mounting Detail




Color coded screws available (add color screw suffix to Cat. No.)



7702-7

- Color coded screws available (add color screw suffix to Cat. No.)

Mounting Detail



7701

PC MOUNT

- Color coded screws available (add color screw suffix to Cat. No.)

CAT. NO. 7782 (No Screw Supplied)

CAT. NO. 8191 (Screw Supplied Unassembled)

CAT. NO. 7701 (Screw Installed & Captivated)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Keystone Electronics:

[7690-2](#) [7690-3](#) [7690-4](#) [7690-5](#) [7690-6](#) [7690-7](#) [7691-3](#) [7691-4](#) [7691-5](#) [7691-7](#) [7692-2](#) [7692-3](#) [7692-4](#) [7692-5](#)
[7692-6](#) [7692-7](#) [7693-2](#) [7693-4](#) [7693-5](#) [7693-6](#) [7693-7](#) [7700-2](#) [7700-3](#) [7700-4](#) [7700-5](#) [7701-2](#) [7701-3](#) [7701-6](#)
[7701-7](#) [7702-4](#) [7702-6](#) [8189-2](#) [8189-3](#) [8189-4](#) [8189-5](#) [8189-6](#) [8189-7](#) [8190-2](#) [8190-3](#) [8190-4](#) [8190-5](#) [8190-6](#)
[8190-7](#) [8191-2](#) [8191-3](#) [8191-4](#) [8191-6](#)