


## Dimensions: mm (in.)



Mouser Stock No.	Type	Circuit
10TF605	SPST	On-Off
10TF610	SPDT	On-On

## Electrical Specifications:

- Rating: 3A / 125VAC
- Insulation Resistance:  $\geq 100M\Omega$  min. @ 500VDC
- Dielectric Strength: 1000VAC for 1 minute
- Contact Resistance:  $\leq 20m\Omega$  max. @ 2.5VDC

Miniature Toggle Switches  
10TF605, 10TF610

**Mountain**  
**Switch**

Available from Mouser Electronics

[www.mouser.com](http://www.mouser.com)

1-800-346-6873

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[10TF610](#) [10TF605](#)