


PA / PAZ

WIRE MARKING



- Closed, permanent grip and adjustable marking sleeve for as yet unconnected wires.
- For applications including electrical engineering, pneumatics and hydraulics.
- Twist-protection for secure combination marking
- Excellent legibility
- Available in halogen free material (Zerex)

FACTS

Material:

- PA: Cadmium and silicon free, soft PVC according to special Partex formula.
- PAZ: Zerex, thermoplastic polyether based polurethane mixture. The material is free from halogen, cadmium and silicon.

Printing:

- PA: PVC, Hot stamped.
- PAZ: ZEREX, Etching black ink jet with high resolution

Text:

Alphanumeric and special characters.

Resistance:

The product is tested according to Partex Product Test Program by the Swedish Test and Research Institute and has the following test properties:

- Flammability resistance according to UL94-V0.
- Resistant to UV radiation, corresponding to 1 year outdoors in the south of Sweden.
- Resistance to chemicals meets Partex Product Test Program.
- Resistance to temperature and ageing meets norms of Partex Product Test Program.

For application in hostile environments, please contact Partex for information.

Temperature resistance:

- PA: Shape permanence from -30°C to +60°C (-22°F to +140°F).
- PAZ: Shape permanence from -30°C to +90°C (-22°F to +194°F).

GENERAL INFORMATION

Design

Closed combination marker. Unique bellow design enables wide diameter range and permanent grip. A chevron cut prevents twisting between adjacent sleeves. The hot stamp print gives excellent legibility.

Colours

- PA: Standard colours yellow and white and international colour code for 0-9.
- PAZ: Standard colours yellow and white. Other colours, please contact Partex.

Multi character marking

See separate product information.

PRODUCT AND ORDERING INFORMATION


PA02



Diameter: 1.3 - 3.0 mm
Area: ~0.2 - 1.5 mm²
Inch: .051" - .118"
Sleeve length: 3 mm

No# of characters: 1

ZEREX = Halogen free material
= Packaging



	Article number PVC	Article number PVC	Article number Zerex	Article number Zerex	Article number PVC
Character	Yellow	White	Yellow	White	Colour code
0	PA-02003#V40.0	PA-02003#V90.0	PAZ02003SB40.0	PAZ02003SB90.0	PA-02003#V09.0
1	PA-02003#V40.1	PA-02003#V90.1	PAZ02003SB40.1	PAZ02003SB90.1	PA-02003#V19.1
2	PA-02003#V40.2	PA-02003#V90.2	PAZ02003SB40.2	PAZ02003SB90.2	PA-02003#V29.2
3	PA-02003#V40.3	PA-02003#V90.3	PAZ02003SB40.3	PAZ02003SB90.3	PA-02003#V30.3
4	PA-02003#V40.4	PA-02003#V90.4	PAZ02003SB40.4	PAZ02003SB90.4	PA-02003#V40.4
5	PA-02003#V40.5	PA-02003#V90.5	PAZ02003SB40.5	PAZ02003SB90.5	PA-02003#V59.5
6	PA-02003#V40.6	PA-02003#V90.6	PAZ02003SB40.6	PAZ02003SB90.6	PA-02003#V69.6
7	PA-02003#V40.7	PA-02003#V90.7	PAZ02003SB40.7	PAZ02003SB90.7	PA-02003#V79.7
8	PA-02003#V40.8	PA-02003#V90.8	PAZ02003SB40.8	PAZ02003SB90.8	PA-02003#V80.8
9	PA-02003#V40.9	PA-02003#V90.9	PAZ02003SB40.9	PAZ02003SB90.9	PA-02003#V90.9
A	PA-02003#V40.A	PA-02003#V90.A	PAZ02003SB40.A	PAZ02003SB90.A	-
B	PA-02003#V40.B	PA-02003#V90.B	PAZ02003SB40.B	PAZ02003SB90.B	-
C	PA-02003#V40.C	PA-02003#V90.C	PAZ02003SB40.C	PAZ02003SB90.C	-
D	PA-02003#V40.D	PA-02003#V90.D	PAZ02003SB40.D	PAZ02003SB90.D	-
E	PA-02003#V40.E	PA-02003#V90.E	PAZ02003SB40.E	PAZ02003SB90.E	-
F	PA-02003#V40.F	PA-02003#V90.F	PAZ02003SB40.F	PAZ02003SB90.F	-
G	PA-02003#V40.G	PA-02003#V90.G	PAZ02003SB40.G	PAZ02003SB90.G	-
H	PA-02003#V40.H	PA-02003#V90.H	PAZ02003SB40.H	PAZ02003SB90.H	-
I	PA-02003#V40.I	PA-02003#V90.I	PAZ02003SB40.I	PAZ02003SB90.I	-
J	PA-02003#V40.J	PA-02003#V90.J	PAZ02003SB40.J	PAZ02003SB90.J	-
K	PA-02003#V40.K	PA-02003#V90.K	PAZ02003SB40.K	PAZ02003SB90.K	-
L	PA-02003#V40.L	PA-02003#V90.L	PAZ02003SB40.L	PAZ02003SB90.L	-
M	PA-02003#V40.M	PA-02003#V90.M	PAZ02003SB40.M	PAZ02003SB90.M	-
N	PA-02003#V40.N	PA-02003#V90.N	PAZ02003SB40.N	PAZ02003SB90.N	-
O	PA-02003#V40.O	PA-02003#V90.O	PAZ02003SB40.O	PAZ02003SB90.O	-
P	PA-02003#V40.P	PA-02003#V90.P	PAZ02003SB40.P	PAZ02003SB90.P	-
Q	PA-02003#V40.Q	PA-02003#V90.Q	PAZ02003SB40.Q	PAZ02003SB90.Q	-
R	PA-02003#V40.R	PA-02003#V90.R	PAZ02003SB40.R	PAZ02003SB90.R	-
S	PA-02003#V40.S	PA-02003#V90.S	PAZ02003SB40.S	PAZ02003SB90.S	-
T	PA-02003#V40.T	PA-02003#V90.T	PAZ02003SB40.T	PAZ02003SB90.T	-
U	PA-02003#V40.U	PA-02003#V90.U	PAZ02003SB40.U	PAZ02003SB90.U	-
V	PA-02003#V40.V	PA-02003#V90.V	PAZ02003SB40.V	PAZ02003SB90.V	-
W	PA-02003#V40.W	PA-02003#V90.W	PAZ02003SB40.W	PAZ02003SB90.W	-
X	PA-02003#V40.X	PA-02003#V90.X	PAZ02003SB40.X	PAZ02003SB90.X	-
Y	PA-02003#V40.Y	PA-02003#V90.Y	PAZ02003SB40.Y	PAZ02003SB90.Y	-
Z	PA-02003#V40.Z	PA-02003#V90.Z	PAZ02003SB40.Z	PAZ02003SB90.Z	-
Å	PA-02003#V40.Å	PA-02003#V90.Å	PAZ02003SB40.Å	PAZ02003SB90.Å	-
Ä	PA-02003#V40.Ä	PA-02003#V90.Ä	PAZ02003SB40.Ä	PAZ02003SB90.Ä	-
Ö	PA-02003#V40.Ö	PA-02003#V90.Ö	PAZ02003SB40.Ö	PAZ02003SB90.Ö	-
+	PA-02003#V40.+	PA-02003#V90.+	PAZ02003SB40.+	PAZ02003SB90.+	-
-	PA-02003#V40.-	PA-02003#V90.-	PAZ02003SB40.-	PAZ02003SB90.-	-
.	PA-02003#V40..	PA-02003#V90..	PAZ02003SB40..	PAZ02003SB90..	-
/	PA-02003#V40./	PA-02003#V90./	PAZ02003SB40./	PAZ02003SB90./	-
:	PA-02003#V40.:	PA-02003#V90.:	PAZ02003SB40.:	PAZ02003SB90.:	-
=	PA-02003#V40.EQ	PA-02003#V90.EQ	PAZ02003SB40.EQ	PAZ02003SB90.EQ	-
Earth	PA-02003#V40.GRD	PA-02003#V90.GRD	-	-	-
Earth in a Circle	PA-02003#V40.GRDC	PA-02003#V90.GRDC	-	-	-
"Neutral/Blank"	PA-02003#N4	PA-02003#N9	PAZ02003SN4	PAZ02003SN9	-

PACKAGING



Compact disc

Number of markers: 500 pcs

Packaging: S

Example: PA-02003SV40.0



Reel

Number of markers: 1000 pcs

Packaging: B

Example: PA-02003BV40.0



Single bag

Number of markers: 10x25 pcs

Packaging: P

Example: PA-02003PV40.0



Strip pack

Number of markers: 5x200 pcs

Packaging: A

Example: PA-02003AV40.0

PRODUCT AND ORDERING INFORMATION


PA 1



Diameter: 2.5 - 5.0 mm
Area: ~1.5 - 4.0 mm²
Inch: .059" - .197"
Sleeve length: 3 mm

No# of characters: 1

ZEREX = Halogen free material
= Packaging



	Article number PVC	Article number PVC	Article number Zerex	Article number Zerex	Article number PVC
Character	Yellow	White	Yellow	White	Colour code
0	PA-10003#V40.0	PA-10003#V90.0	PAZ10003SB40.0	PAZ10003SB90.0	PA-10003#V09.0
1	PA-10003#V40.1	PA-10003#V90.1	PAZ10003SB40.1	PAZ10003SB90.1	PA-10003#V19.1
2	PA-10003#V40.2	PA-10003#V90.2	PAZ10003SB40.2	PAZ10003SB90.2	PA-10003#V29.2
3	PA-10003#V40.3	PA-10003#V90.3	PAZ10003SB40.3	PAZ10003SB90.3	PA-10003#V30.3
4	PA-10003#V40.4	PA-10003#V90.4	PAZ10003SB40.4	PAZ10003SB90.4	PA-10003#V40.4
5	PA-10003#V40.5	PA-10003#V90.5	PAZ10003SB40.5	PAZ10003SB90.5	PA-10003#V59.5
6	PA-10003#V40.6	PA-10003#V90.6	PAZ10003SB40.6	PAZ10003SB90.6	PA-10003#V69.6
7	PA-10003#V40.7	PA-10003#V90.7	PAZ10003SB40.7	PAZ10003SB90.7	PA-10003#V79.7
8	PA-10003#V40.8	PA-10003#V90.8	PAZ10003SB40.8	PAZ10003SB90.8	PA-10003#V80.8
9	PA-10003#V40.9	PA-10003#V90.9	PAZ10003SB40.9	PAZ10003SB90.9	PA-10003#V90.9
A	PA-10003#V40.A	PA-10003#V90.A	PAZ10003SB40.A	PAZ10003SB90.A	-
B	PA-10003#V40.B	PA-10003#V90.B	PAZ10003SB40.B	PAZ10003SB90.B	-
C	PA-10003#V40.C	PA-10003#V90.C	PAZ10003SB40.C	PAZ10003SB90.C	-
D	PA-10003#V40.D	PA-10003#V90.D	PAZ10003SB40.D	PAZ10003SB90.D	-
E	PA-10003#V40.E	PA-10003#V90.E	PAZ10003SB40.E	PAZ10003SB90.E	-
F	PA-10003#V40.F	PA-10003#V90.F	PAZ10003SB40.F	PAZ10003SB90.F	-
G	PA-10003#V40.G	PA-10003#V90.G	PAZ10003SB40.G	PAZ10003SB90.G	-
H	PA-10003#V40.H	PA-10003#V90.H	PAZ10003SB40.H	PAZ10003SB90.H	-
I	PA-10003#V40.I	PA-10003#V90.I	PAZ10003SB40.I	PAZ10003SB90.I	-
J	PA-10003#V40.J	PA-10003#V90.J	PAZ10003SB40.J	PAZ10003SB90.J	-
K	PA-10003#V40.K	PA-10003#V90.K	PAZ10003SB40.K	PAZ10003SB90.K	-
L	PA-10003#V40.L	PA-10003#V90.L	PAZ10003SB40.L	PAZ10003SB90.L	-
M	PA-10003#V40.M	PA-10003#V90.M	PAZ10003SB40.M	PAZ10003SB90.M	-
N	PA-10003#V40.N	PA-10003#V90.N	PAZ10003SB40.N	PAZ10003SB90.N	-
O	PA-10003#V40.O	PA-10003#V90.O	PAZ10003SB40.O	PAZ10003SB90.O	-
P	PA-10003#V40.P	PA-10003#V90.P	PAZ10003SB40.P	PAZ10003SB90.P	-
Q	PA-10003#V40.Q	PA-10003#V90.Q	PAZ10003SB40.Q	PAZ10003SB90.Q	-
R	PA-10003#V40.R	PA-10003#V90.R	PAZ10003SB40.R	PAZ10003SB90.R	-
S	PA-10003#V40.S	PA-10003#V90.S	PAZ10003SB40.S	PAZ10003SB90.S	-
T	PA-10003#V40.T	PA-10003#V90.T	PAZ10003SB40.T	PAZ10003SB90.T	-
U	PA-10003#V40.U	PA-10003#V90.U	PAZ10003SB40.U	PAZ10003SB90.U	-
V	PA-10003#V40.V	PA-10003#V90.V	PAZ10003SB40.V	PAZ10003SB90.V	-
W	PA-10003#V40.W	PA-10003#V90.W	PAZ10003SB40.W	PAZ10003SB90.W	-
X	PA-10003#V40.X	PA-10003#V90.X	PAZ10003SB40.X	PAZ10003SB90.X	-
Y	PA-10003#V40.Y	PA-10003#V90.Y	PAZ10003SB40.Y	PAZ10003SB90.Y	-
Z	PA-10003#V40.Z	PA-10003#V90.Z	PAZ10003SB40.Z	PAZ10003SB90.Z	-
Ä	PA-10003#V40.Ä	PA-10003#V90.Ä	PAZ10003SB40.Ä	PAZ10003SB90.Ä	-
Å	PA-10003#V40.Å	PA-10003#V90.Å	PAZ10003SB40.Å	PAZ10003SB90.Å	-
Ö	PA-10003#V40.Ö	PA-10003#V90.Ö	PAZ10003SB40.Ö	PAZ10003SB90.Ö	-
+	PA-10003#V40.+	PA-10003#V90.+	PAZ10003SB40.+	PAZ10003SB90.+	-
-	PA-10003#V40.-	PA-10003#V90.-	PAZ10003SB40.-	PAZ10003SB90.-	-
.	PA-10003#V40..	PA-10003#V90..	PAZ10003SB40..	PAZ10003SB90..	-
/	PA-10003#V40./	PA-10003#V90./	PAZ10003SB40./	PAZ10003SB90./	-
:	PA-10003#V40.:	PA-10003#V90.:	PAZ10003SB40.:	PAZ10003SB90.:	-
=	PA-10003#V40.EQ	PA-10003#V90.EQ	PAZ10003SB40.EQ	PAZ10003SB90.EQ	-
Earth	PA-10003#V40.GRD	PA-10003#V90.GRD	-	-	-
Earth in a Circle	PA-10003#V40.GRDC	PA-10003#V90.GRDC	-	-	-
"Neutral/Blank"	PA-10003#N4	PA-10003#N9	PAZ10003SN4	PAZ10003SN9	-

PACKAGING



Compact disc
Number of markers: 500 pcs
Packaging: S
Example: PA-10003SV40.0



Reel
Number of markers: 1000 pcs
Packaging: B
Example: PA-10003BV40.0



Single bag
Number of markers: 10x25 pcs
Packaging: P
Example: PA-10003PV40.0



Strip pack
Number of markers: 5x200 pcs
Packaging: A
Example: PA-10003AV40.0

PRODUCT AND ORDERING INFORMATION


PA2



Diameter: 4.0 - 10.0 mm
 Area: ~2.5 - 16.0 mm²
 Inch: .157" - .394"
 Sleeve length: 4 mm

No# of characters: 1

ZEREX = Halogen free material
 # = Packaging



	Article number PVC	Article number PVC	Article number Zerex	Article number Zerex	Article number PVC
Character	Yellow	White	Yellow	White	Colour code
0	PA-20004#V40.0	PA-20004#V90.0	PAZ20004SB40.0	PAZ20004SB90.0	PA-20004#V09.0
1	PA-20004#V40.1	PA-20004#V90.1	PAZ20004SB40.1	PAZ20004SB90.1	PA-20004#V19.1
2	PA-20004#V40.2	PA-20004#V90.2	PAZ20004SB40.2	PAZ20004SB90.2	PA-20004#V29.2
3	PA-20004#V40.3	PA-20004#V90.3	PAZ20004SB40.3	PAZ20004SB90.3	PA-20004#V30.3
4	PA-20004#V40.4	PA-20004#V90.4	PAZ20004SB40.4	PAZ20004SB90.4	PA-20004#V40.4
5	PA-20004#V40.5	PA-20004#V90.5	PAZ20004SB40.5	PAZ20004SB90.5	PA-20004#V59.5
6	PA-20004#V40.6	PA-20004#V90.6	PAZ20004SB40.6	PAZ20004SB90.6	PA-20004#V69.6
7	PA-20004#V40.7	PA-20004#V90.7	PAZ20004SB40.7	PAZ20004SB90.7	PA-20004#V79.7
8	PA-20004#V40.8	PA-20004#V90.8	PAZ20004SB40.8	PAZ20004SB90.8	PA-20004#V80.8
9	PA-20004#V40.9	PA-20004#V90.9	PAZ20004SB40.9	PAZ20004SB90.9	PA-20004#V90.9
A	PA-20004#V40.A	PA-20004#V90.A	PAZ20004SB40.A	PAZ20004SB90.A	-
B	PA-20004#V40.B	PA-20004#V90.B	PAZ20004SB40.B	PAZ20004SB90.B	-
C	PA-20004#V40.C	PA-20004#V90.C	PAZ20004SB40.C	PAZ20004SB90.C	-
D	PA-20004#V40.D	PA-20004#V90.D	PAZ20004SB40.D	PAZ20004SB90.D	-
E	PA-20004#V40.E	PA-20004#V90.E	PAZ20004SB40.E	PAZ20004SB90.E	-
F	PA-20004#V40.F	PA-20004#V90.F	PAZ20004SB40.F	PAZ20004SB90.F	-
G	PA-20004#V40.G	PA-20004#V90.G	PAZ20004SB40.G	PAZ20004SB90.G	-
H	PA-20004#V40.H	PA-20004#V90.H	PAZ20004SB40.H	PAZ20004SB90.H	-
I	PA-20004#V40.I	PA-20004#V90.I	PAZ20004SB40.I	PAZ20004SB90.I	-
J	PA-20004#V40.J	PA-20004#V90.J	PAZ20004SB40.J	PAZ20004SB90.J	-
K	PA-20004#V40.K	PA-20004#V90.K	PAZ20004SB40.K	PAZ20004SB90.K	-
L	PA-20004#V40.L	PA-20004#V90.L	PAZ20004SB40.L	PAZ20004SB90.L	-
M	PA-20004#V40.M	PA-20004#V90.M	PAZ20004SB40.M	PAZ20004SB90.M	-
N	PA-20004#V40.N	PA-20004#V90.N	PAZ20004SB40.N	PAZ20004SB90.N	-
O	PA-20004#V40.O	PA-20004#V90.O	PAZ20004SB40.O	PAZ20004SB90.O	-
P	PA-20004#V40.P	PA-20004#V90.P	PAZ20004SB40.P	PAZ20004SB90.P	-
Q	PA-20004#V40.Q	PA-20004#V90.Q	PAZ20004SB40.Q	PAZ20004SB90.Q	-
R	PA-20004#V40.R	PA-20004#V90.R	PAZ20004SB40.R	PAZ20004SB90.R	-
S	PA-20004#V40.S	PA-20004#V90.S	PAZ20004SB40.S	PAZ20004SB90.S	-
T	PA-20004#V40.T	PA-20004#V90.T	PAZ20004SB40.T	PAZ20004SB90.T	-
U	PA-20004#V40.U	PA-20004#V90.U	PAZ20004SB40.U	PAZ20004SB90.U	-
V	PA-20004#V40.V	PA-20004#V90.V	PAZ20004SB40.V	PAZ20004SB90.V	-
W	PA-20004#V40.W	PA-20004#V90.W	PAZ20004SB40.W	PAZ20004SB90.W	-
X	PA-20004#V40.X	PA-20004#V90.X	PAZ20004SB40.X	PAZ20004SB90.X	-
Y	PA-20004#V40.Y	PA-20004#V90.Y	PAZ20004SB40.Y	PAZ20004SB90.Y	-
Z	PA-20004#V40.Z	PA-20004#V90.Z	PAZ20004SB40.Z	PAZ20004SB90.Z	-
Å	PA-20004#V40.Å	PA-20004#V90.Å	PAZ20004SB40.Å	PAZ20004SB90.Å	-
Ä	PA-20004#V40.Ä	PA-20004#V90.Ä	PAZ20004SB40.Ä	PAZ20004SB90.Ä	-
Ö	PA-20004#V40.Ö	PA-20004#V90.Ö	PAZ20004SB40.Ö	PAZ20004SB90.Ö	-
+	PA-20004#V40.+	PA-20004#V90.+	PAZ20004SB40.+	PAZ20004SB90.+	-
-	PA-20004#V40.-	PA-20004#V90.-	PAZ20004SB40.-	PAZ20004SB90.-	-
.	PA-20004#V40..	PA-20004#V90..	PAZ20004SB40..	PAZ20004SB90..	-
/	PA-20004#V40./	PA-20004#V90./	PAZ20004SB40./	PAZ20004SB90./	-
:	PA-20004#V40.:	PA-20004#V90.:	PAZ20004SB40.:	PAZ20004SB90.;	-
=	PA-20004#V40.EQ	PA-20004#V90.EQ	PAZ20004SB40.EQ	PAZ20004SB90.EQ	-
Earth	PA-20004#V40.GRD	PA-20004#V90.GRD	-	-	-
Earth in a Circle	PA-20004#V40.GRDC	PA-20004#V90.GRDC	-	-	-
"Neutral/Blank"	PA-20004#N4	PA-20004#N9	PAZ20004SN4	PAZ20004SN9	-

PACKAGING



Compact disc
 Number of markers: 250 pcs
 Packaging: S
 Example: PA-20004SV40.0




Strip pack
 Number of markers: 5x100 pcs
 Packaging: A
 Example: PA-20004AV40.0

PRODUCT AND ORDERING INFORMATION

PA3



Diameter: 8.0 - 16.0 mm
 Area: ~16.0 - 70.0 mm²
 Inch: .315" - .630"
 Sleeve length: 6 mm
 No# of characters: 1



	Article number PVC	Article number PVC	Article number Zerex	Article number Zerex	Article number PVC
Character	Yellow	White	Yellow	White	Yellow
0	PA-30006AV40.0	PA-30006AV90.0	-	-	-
1	PA-30006AV40.1	PA-30006AV90.1	-	-	-
2	PA-30006AV40.2	PA-30006AV90.2	-	-	-
3	PA-30006AV40.3	PA-30006AV90.3	-	-	-
4	PA-30006AV40.4	PA-30006AV90.4	-	-	-
5	PA-30006AV40.5	PA-30006AV90.5	-	-	-
6	PA-30006AV40.6	PA-30006AV90.6	-	-	-
7	PA-30006AV40.7	PA-30006AV90.7	-	-	-
8	PA-30006AV40.8	PA-30006AV90.8	-	-	-
9	PA-30006AV40.9	PA-30006AV90.9	-	-	-
A	PA-30006AV40.A	PA-30006AV90.A	-	-	-
B	PA-30006AV40.B	PA-30006AV90.B	-	-	-
C	PA-30006AV40.C	PA-30006AV90.C	-	-	-
D	PA-30006AV40.D	PA-30006AV90.D	-	-	-
E	PA-30006AV40.E	PA-30006AV90.E	-	-	-
F	PA-30006AV40.F	PA-30006AV90.F	-	-	-
G	PA-30006AV40.G	PA-30006AV90.G	-	-	-
H	PA-30006AV40.H	PA-30006AV90.H	-	-	-
I	PA-30006AV40.I	PA-30006AV90.I	-	-	-
J	PA-30006AV40.J	PA-30006AV90.J	-	-	-
K	PA-30006AV40.K	PA-30006AV90.K	-	-	-
L	PA-30006AV40.L	PA-30006AV90.L	-	-	-
M	PA-30006AV40.M	PA-30006AV90.M	-	-	-
N	PA-30006AV40.N	PA-30006AV90.N	-	-	-
O	PA-30006AV40.O	PA-30006AV90.O	-	-	-
P	PA-30006AV40.P	PA-30006AV90.P	-	-	-
Q	PA-30006AV40.Q	PA-30006AV90.Q	-	-	-
R	PA-30006AV40.R	PA-30006AV90.R	-	-	-
S	PA-30006AV40.S	PA-30006AV90.S	-	-	-
T	PA-30006AV40.T	PA-30006AV90.T	-	-	-
U	PA-30006AV40.U	PA-30006AV90.U	-	-	-
V	PA-30006AV40.V	PA-30006AV90.V	-	-	-
W	PA-30006AV40.W	PA-30006AV90.W	-	-	-
X	PA-30006AV40.X	PA-30006AV90.X	-	-	-
Y	PA-30006AV40.Y	PA-30006AV90.Y	-	-	-
Z	PA-30006AV40.Z	PA-30006AV90.Z	-	-	-
Å	PA-30006AV40.Å	PA-30006AV90.Å	-	-	-
Ä	PA-30006AV40.Ä	PA-30006AV90.Ä	-	-	-
Ö	PA-30006AV40.Ö	PA-30006AV90.Ö	-	-	-
+	PA-30006AV40.+	PA-30006AV90.+	-	-	-
-	PA-30006AV40.-	PA-30006AV90.-	-	-	-
.	PA-30006AV40..	PA-30006AV90..	-	-	-
/	PA-30006AV40./	PA-30006AV90./	-	-	-
:	PA-30006AV40.:	PA-30006AV90.:	-	-	-
=	PA-30006AV40.EQ	PA-30006AV90.EQ	-	-	-
Earth	PA-30006AV40.GRD	PA-30006AV90.GRD	-	-	-
Earth in a Circle	PA-30006AV40.GRDC	PA-30006AV90.GRDC	-	-	-
"Neutral/Blank"	PA-30004AN4	PA-30006AN9	-	-	-


PACKAGING



Strip pack
 Number of markers: 5x20 pcs
 Packaging: A
 Example: PA-30006AV40.0


ACCESSORIES

PAD AND PAV INSTALLATION TOOLS




PAD
Teflon coated stainless steel alt. stainless steel conical installation tool with axial hole at the fat end for wire. For use with striped wires an Partex wire marking PA02 and PA1.


PAV
U-shaped installation tool in stainless steel for both left and right mounting. Depending on how the U-shaped part of PAV is turned in, the marker can be expanded over the whole diameter range.



Tool	Designed for	Length mm	Diameter		Inner diameter		Number /Pack.	Article number	
			mm	Inch	mm	Inch		Metal	Teflon coatad
PAD-3	PA02	100	3,1	.122	1,8	.70	1 pce	PAD-3M	PAD-3T
PAD-4	PA1	100	4,2	.165	2.5	.98	1 pce	PAD-4M	PAD-4T
PAD-5	PA1	100	5,0	.197	2,5	.98	1 pce	PAD-5M	PAD-5T
PAV02	PA02	124	3,8	.150	-	-	1 pce	PAV02M	
PAV10	PA1	130	5,0	.197	-	-	1 pce	PAV03M	



MD - MDH



CAS - PAM



SRP



PSK