

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191150048

Status:

Active

Description:

Avikrimp™ Snap Spade Terminal for 10-12 AWG Wire

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Ring and Spade Terminals

Series

19115

Mil-Spec

N/A

Product Name

Avikrimp™

Type

Spade Snap

Physical

Barrel Type

Closed

Flammability

94V-0

Insulation

Nylon (PA)

Material - Plating Mating

Tin

Packaging Type

Bag

Plating min: Mating (µin)

160

Plating min: Mating (µm)

4

Plating min: Termination (µin)

160

Plating min: Termination (µm)

4

Stud Size

10 (M5)

Wire Insulation Diameter

5.70mm (.225") max.

Wire Size AWG

10, 12

Electrical

CSA

LR18689

UL

E32244

Material Info


Old Part Number

C-8719-10

Reference - Drawing Numbers

Sales Drawing

CCD80503



Series
image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19115Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	0640010100
Crimp Head for the AT-200™ Pneumatic Hand Tool	0640050100
Hand Crimp Tool	0640011500

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION