

Housing - HC-B 16-TFL-76/O1STM25G - 1645024

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



HEAVYCON sleeve housing B16, for single locking latch, height 76 mm, without support 1x M25, straight conductor exit

The illustration shows the version
HC-B 16-TFL-76/O1STM40G

Key commercial data

package_quantity	10
GTIN	4017918912888

Technical data

Dimensions

Height	76 mm
Width	43 mm
Length	94 mm

Ambient conditions

Degree of protection for housing	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B16, BB32, D40, DD72, HS6, M, K
Design	B16
Housing type	Sleeve housings
Locking type	for single locking latch
No. of cable exits	1
Cable exit	Straight
Screw connection	None
Type of the screw connection	1x M25
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray

classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816

Housing - HC-B 16-TFL-76/O1STM25G - 1645024

classifications

eCl@ss

eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440209

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

accessories

Full screw connection

HC-K-KV-M25(11-17) - 1690639



HC-M-KV-M25(11-16) - 1690574



HC-M-KV-M25(14-21) - 1646007



Housing - HC-B 16-TFL-76/O1STM25G - 1645024

accessories

HC-M-KV-M25(1ASI) - 1584020




Multiple screw connection

HC-M-KV-M25(1X10/1X11) - 1580228



Drawings

Dimensioned drawing



Dimensional drawing

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>