


Mini USB B Type Receptacle

154-4100



Mini USB B Type Receptacle



Dimensions: mm (In.)

Tolerance Range MM	
0 - 1	±0.1
1 - 4	±0.3
4 - 16	±0.5
16 - 63	±0.8
63 - 250	±1.0

SPECIFICATIONS

Voltage rating:	30VAC (rms)
Current rating:	1 Amp
Contact resistance:	50mΩ Max.
Insulation resistance:	100MΩ Min.
Dielectric strength:	100VAC Min.
Contacts:	phosphor bronze
Shell:	copper alloy
Receptacle housing:	LCP black
Durability:	1500 cycles
Mating force:	35N Max.
Unmating force:	2.9N Min.
Nickel:	in all area
Contact area:	gold 5u" over nickel
Solder area:	tin-lead over nickel
Shell:	tin-lead over nickel
Fully compliant with current USB1.0 specifications.	

Date Last Revised: 6-22-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC- 300638

154-4100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[154-4100](#)