


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200805083](#)
Status: **Active**
Overview: [Brad Ultra-Lock Connection System](#)
Description: Ultra-Lock (M12) Double-Ended Cordset, 8 Poles, Female (Straight) to Male (Straight), PUR/PVC Cable, 1.0m (3.28') Length

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Industrial Cordsets
Series	120080
Connector End A	Ultra-Lock (M12)
Connector End B	Ultra-Lock (M12)
IP Rating	IP69K
Material - Contact	Copper Alloy
Overview	Brad Ultra-Lock Connection System
Product Name	Ultra-Lock (M12)
Protocol	N/A
Region	Europe
Type	Double Ended
UPC	884982235458
Physical	
Cable Diameter	6.70mm (.264")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Push to Lock
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	104.977/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-30°C TO +80°C
Wire Size AWG	N/A
Wire/Cable Type	EU Cable
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	30V AC / 36V DC
Material Info	
Engineering Number	WW8030P02M010
Reference - Drawing Numbers	
Sales Drawing	1200805076-00P, SD-120080-055



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Reviewed Halogen-Free Status Not Low-Halogen	China RoHS
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[120080](#) Series

Mates With
[1202440002](#) MicroChange (M12) Circular Hybrid Technology (CHT) Female Receptacle