

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

GP

00

P

LTR

DESCRIPTION

DATE

DWN

APVD

Tooling Drawing NO.

USB A: TR00662

USB B: TR00664


E

PER ECR-06-020659

04SEP06

WW

WW



PIN ASSIGNMENT :

USB A	2	3	1	4	Shell
	White(D-)	Green(D+)	Red(Vbus)	Black(Gnd)	Drain Braid
USB B	2	3	1	4	Shell

TYCO P/N
T/D YYWW
MADE IN CHINA

LABEL

PART NO.	1487594-1	1487594-2	1487594-3	1487594-4	1487594-5
LENGTH(L)	500	250	162	310	750

NOTES:

1. TESTED FOR CONTINUITY, SHORTS AND OPENS, HI-POT 630V FOR 10MS.
2. CABLE ASSEMBLY MEETS USB 2.0 STANDARDS.
3. EXPOSED CABLE BRAID IS NOT PERMISSIBLE BEYOND OVERMOLD.
4. THE FINAL CABLE ASSEMBLY MAXIMUM LENGTH NOT TO EXCEED 1000MM PER USB SPECIFICATIONS.
5. MEETS REQUIREMENTS OF EU DIRECTIVE 2002/95/EC

AR	AR	AR	AR	AR	MR	COPPER FOIL, W: 5MM	6
1	1	1	1	1	PC	LABEL 25*35MM, WHITE: 25*13	5
AR	AR	AR	AR	AR	KG	Overmold PVC, 40P, Color: Black(BK01)	4
AR	AR	AR	AR	AR	M1	USB 2.0 Cable 28AWG*1P+28AWG*2C+Al/Mylar +Drain+Braid, Color: Black(BK01), OD: 4.20±0.15mm	3
1	1	1	1	1	PC	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 B Type.	2
1	1	1	1	1	PC	USB 4Pin Connector Contacts: Gold 30U Plated, Shell: Nickel Plated, Housing UL94V-0 A Type.	1
-5	-4	-3	-2	-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN BOVEY LIU 25FEB02

CHK J.HUNT 25FEB02

APVD J.HUNT 25FEB02

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608NAME
CABLE ASSEMBLY, USB A TYPE TO USB B TYPE

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 00779 C-1487594

SCALE - SHEET 1 OF 1 REV E