

Twist drill sets in steel case

1.1

Description	Article no.	Price set €
Consisting of 19 twist drills DIN 338 TL 3000 HSS Co 5 ground Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	229 214	
Consisting of 25 twist drills DIN 338 TL 3000 HSS Co 5 ground Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	229 215	
Consisting of 19 twist drills DIN 338 type N HSS Co 5 ground Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	215 214	
Consisting of 25 twist drills DIN 338 type N HSS Co 5 ground Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	215 215	
Consisting of 50 twist drills DIN 338 type N HSS Co 5 ground Ø 1,0 mm up to 5,9 mm x in increments of 0,1 mm	215 217	
Consisting of 41 twist drills DIN 338 type N HSS Co 5 ground Ø 6,0 mm up to 10,0 mm in increments of 0,1 mm	215 218	
Consisting of 19 twist drills DIN 338 TL 3000 HSS ground Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	258 214	
Consisting of 25 twist drills DIN 338 TL 3000 HSS ground Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	258 215	
Consisting of 19 twist drills DIN 338 type N HSS ground Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	214 214	
Consisting of 25 twist drills DIN 338 type N HSS ground Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	214 215	
Consisting of 50 twist drills DIN 338 type N HSS ground Ø 1,0 mm up to 5,9 mm in increments of 0,1 mm	214 217	
Consisting of 41 twist drills DIN 338 type N HSS ground Ø 6,0 mm up to 10,0 mm in increments of 0,1 mm	214 218	
Consisting of 19 twist drills DIN 338 TL 3000 HSS-TiAlN ground Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	258 214 F	
Consisting of 19 twist drills DIN 338 TL 3000 HSS-TiAlN ground Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	258 215 F	
Consisting of 19 twist drills DIN 338 type N HSS-TiN ground Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	250 214 T	
Consisting of 25 twist drills DIN 338 type N HSS-TiN ground Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	250 215 T	
Consisting of 13 twist drills DIN 338 type N HSS rolled Ø 1,5 mm up to 6,5 mm in increments of 0,5 mm + Ø 3,3 and 4,2 mm	205 207	
Consisting of 19 twist drills DIN 338 type N HSS rolled Ø 1,0 mm up to 10,0 mm in increments of 0,5 mm	205 212	
Consisting of 25 twist drills DIN 338 type N HSS rolled Ø 1,0 mm up to 13,0 mm in increments of 0,5 mm	205 213	
Consisting of 50 twist drills DIN 338 type N HSS rolled Ø 1,0 mm up to 5,9 mm x in increments of 0,1 mm	205 217	
Consisting of 41 twist drills DIN 338 type N HSS rolled Ø 6,0 mm up to 10,0 mm x in increments of 0,1 mm	205 218	



No. 229 214



No. 214 214



No. 250 214 T



No. 205 212