

CK1,6-ERAG-1,50BU

Order No.: 1884115



<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=1884115>

Rolled female contact, single contacts, silver-plated, 0.5 mm² ... 1.5 mm²

Commercial data

EAN	4017918163815
Pack	100 pcs.
Customs tariff	85366990
Weight/Piece	0.00043 KG
Catalog page information	Page 529 (PC-2009)

Product notes

WEEE/RoHS-compliant since:
12/01/2005



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data

Electrical characteristics

Note	For HC-D...R and VC-D...R contact carriers: the quality of a crimp connection is determined by DIN EN 60 352-2
Volume resistance	5 mΩ
Ambient temperature (operation)	-40 °C ... 125 °C

Mechanical characteristics

Conductor cross section	0.5 mm ² ... 1.5 mm ²
Connection cross section AWG	20 ... 16
Stripping length of the individual wire	3.5 mm +1
Insertion/withdrawal cycles	≥ 500

General characteristics

Type	Individual female contact
------	---------------------------

Material data

Contact material	Copper alloy
Contact surface material	hard-silver plated

Certificates / Approvals




Certification GOST

Accessories

Item	Designation	Description
General		
1884869	VC-EW 1,6	Contact removal tool, for turned and rolled CK- 1.6-... contacts

Diagrams/Drawings

Dimensioned drawing



Address

PHOENIX CONTACT Inc., USA
586 Fulling Mill Road
Middletown, PA 17057, USA
Phone (800) 888-7388
Fax (717) 944-1625
<http://www.phoenixcon.com>



© 2010 Phoenix Contact
Technical modifications reserved;