

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

89400-1520

Status:

Active

Description:

2.00mm Pitch Wire-to-Board Header, Vertical, 15 Circuits, with Kinked PC Tail

Documents:

3D Model

Product Specification PS-87369-0002 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

89400

Application

Signal, Wire-to-Board

Product Name

N/A

Physical

Breakaway

No

Circuits (Loaded)

15

Circuits (maximum)

15

Color - Resin

Natural

Durability (mating cycles max)

30

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

Yes

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.40mm

PCB Locator

No

PCB Retention

Yes

PCB Thickness - Recommended

1.20mm

Packaging Type

Bag

Pitch - Mating Interface

2.00mm

Plating min - Mating

1.270µm

Plating min - Termination

1.270µm

Polarized to PCB

No

Shrouded

Partial

Stackable

No

Temperature Range - Operating

-25°C to +85°C

Termination Interface: Style

Through Hole

Electrical

Current - Maximum per Contact

4A

Voltage - Maximum


250V

Material Info

Reference - Drawing Numbers

Product Specification

PS-87369-0002, RPS-87369-001



Series
image - Reference only

EU RoHS

ELV and RoHS
Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

89400Series

Mates With

87369 Crimp Housing

This document was generated on 06/05/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION