

LOC	DIST	REVISIONS				JR/MS		
		P	LTR	DESCRIPTION		DATE	OWN	APVD
G	14		F1	REVISED PER ECO-11-004820		11MAR11	RK	HMR

 WIRE RANGE	 Listed FILE E13288	 LR7189 Certified
12-10 AWG SOLID OR STRANDED	12-10 AWG STRANDED	12-10 AWG SOLID OR STRANDED

- 1

STAMP AMP 12-10* APPROX AS SHOWN
- 2

PRELIMINARY – NOT FOR PRODUCTION
- 3



0.00254 [.000100] MIN TIN PLATE PER
ASTM B-545
- 4

CLEANED, UNPLATED
- 5

0.00254 [.000100] MIN TIN-LEAD (93-7) PLATE
PER ASTM B-545 (3% MIN LEAD CONTENT)
- 6

COPPER PER ASTM B-152, ANNEALED

5	500	LOOSE PIECE	322454-3
4	—	LOOSE PIECE	2 322454-2
3	50	LOOSE PIECE, BOX	8-322454-2
3	2500	ON TAPE, REEL	322454-1
3	----	LOOSE PIECE	322454
FINISH	QTY	PACKAGE TYPE	PART NO.

MAX. RECOMMENDED OPERATING TEMPERATURE: 170°C MAX	THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 3-17-93	 TE Connectivity			
	DIMENSIONS: MM [INCHES]		CHK DA PATTERSON 3-17-93				
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD JL MECKLEY 3-17-93	NAME TERMINAL, RING TONGUE, SOLISTRAND			
			PRODUCT SPEC — APPLICATION SPEC —	SIZE A2	CAGE CODE 00779	DRAWING NO G-322454	RESTRICTED TO —
VOLTAGE RATING: N/A			WEIGHT —	CUSTOMER DRAWING			
CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] SOLID OR STRANDED	MATERIAL 6		FINISH SEE TABLE	SCALE 10:1	SHEET 1 of 1	REV F1	