

ESHF-125-01-L-D-SM-LC

ESHF-105-01-L-D-SM

EHF-125-01-L-D-SM-LC

SHF, ESHF, EHF, ECF SERIES

SHROUDED & EJECTOR IDC HEADER

FFSD*, FFTP

EHF — **1** **NO. PINS PER ROW** — **01** — **PLATING OPTION** — **D** — **TAIL OPTION** — **OTHER OPTION**

04, 05, 08, 10, 13, 17, 20, 25
(Standard sizes)

—F
= Gold flash on post,
Matte Tin on tail

—L
= 10μ" (0.25 μm)
Gold on post,
Matte Tin on tail

Leave blank for Through-Hole version

—SM
= Surface Mount

—RA
= Right Angle

—“XX”
= Polarized Position
(—RA not available)

—LC
= Locking Clip
(—SM only)
(Manual placement required)

—K
= (7,50 mm) .295" DIA
Polyimide Film Pick
& Place Pad

—P
= Pick & Place Pad
(—SM only)

—TR
= Tape & Reel
Packaging
(—LC not available)

Technical drawing of a 10-pin connector showing top, side, and detail views with dimensions.

Top view dimensions: (8,76) .345, (6,5) .380, (1,27) .050, (14,48) .570, (0,21) .021, (0,41) .016 SQ, (1,52) .060, (11,30) .445, (8,26) .325, (6,67) .263, (2,29) .090, (1,27) .050, (1,27) .050.

Side view dimensions: (3,05) .120, (8,51) .335, (7,52) .296.

Detail view dimensions: (0,21) .021, (0,41) .016 SQ, (1,52) .060, (11,30) .445, (8,26) .325, (6,67) .263, (2,29) .090, (1,27) .050.

Labels: —SM, —RA, —TH, —LC, —SM, —RA.

Due to technical progress, all designs, specifications and components are subject to change without notice.