



# SPECIFICATIONS

FREQUENCY RANGE: 7 TO 12.4 GHz  
 NUMBER OF OUTPUT PORTS: 2  
 MINIMUM ISOLATION: 20 dB  
 MAXIMUM VSWR: 1.35  
 MAXIMUM INSERTION LOSS: .40 dB



**PASTERNAK ENTERPRISES, INC.**  
 P.O BOX 16759, IRVINE, CA 92623  
 PHONE (949) 261-1920 FAX (949) 261-7451  
 WEB ADDRESS: [www.pasternack.com](http://www.pasternack.com)  
 E-MAIL ADDRESS: [sales@pasternack.com](mailto:sales@pasternack.com)  
**COAXIAL & FIBER OPTICS**

DWG TITLE <b>PE2020</b>		DES. SMA FEMALE POWER DIVIDER FREQUENCY RANGE: 7-12.4 GHz 2 OUTPUT PORTS			
SIZE A	FSCM NO. 53919	CAD FILE 040302	SCALE N/A		127

**NOTES:**  
 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.  
 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.