





NOTE:

1. MATERIAL:

HOUSING: PA46 GLASS FILLED, UL94V-0, COLOR: NATURAL

TERMINAL: PHOSPHOR BRONZE

2. PLATING: 1) PARTIAL GOLD PLATING OVER NICKEL PLATING OVERALL

CONTACT POINT: 0.10 μm MINIMUM GOLD PLATING



TAIL POINT :GOLD PLATING

2) 1-3 μm TIN-BISMUTH OVER NICKEL PLATING OVERALL

3. PRODUCT SPECIFICATION: PS-78119-001

4. PRODUCT ARE PACKED IN TAPE & REEL.

REVISED EC NO: J2013-1512 DRW: KAWASHI 1.01 CHKD: KATAHASHI APPR: YNOGAWA	DESCRIPTION REV	QUALITY SYMBOLS F_A=0 F_G=0 F_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT			
			4 PLACES	± ---	± ---	CHECKED BY BOKOK	DATE 2006/04/18				
			3 PLACES	± ---	± ---			molex			
			2 PLACES	± 0.15	± ---						
			1 PLACE	± ---	± ---						
			0 PLACE	±	±	APPROVED BY PTL IM	DATE 2006/04/18				
			ANGULAR ± 3 °			MATERIAL NO.		DOCUMENT NO.			SHEET NO.
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-78119-001			1 OF 7
						SIZE A3	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				



N	0.30 ^{+0.05} _{-0.02}	0.30 ^{+0.05} _{-0.02}	0.35 ^{+0.04} _{-0.03}	0.35 ^{+0.05} ₀
P	0.50±0.03	0.50±0.05	0.50±0.02	0.50±0.05
M	0.50±0.10	0.50±0.08	0.50±0.12	0.50±0.10
B	B±0.03	B±0.05	B±0.03	B±0.05
	1	2	1	2
	FFC		FPC	

REVISED EC NO: J2013-1512 DRWN: KAWASHI 101 2013/06/12 CHKD: KATAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/25	DESCRIPTION	QUALITY SYMBOLS ▽_F=0 ▽_G=0 ▽_P=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
				mm	INCH	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT							
			4 PLACES ± --- ± ---		CHECKED BY BOKOK	DATE 2006/04/18									
			3 PLACES ± --- ± ---		APPROVED BY PTLIM	DATE 2006/04/18	molex								
			2 PLACES ± 0.15 ± ---		MATERIAL NO.							DOCUMENT NO.		SHEET NO.	
			1 PLACE ± --- ± ---		SEE TABLE							SD-78119-001		2 OF 7	
0 PLACE ± ±		SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
			ANGULAR ± 3 °												
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS												
A4			REV												

10 9 8 7 6 5 4 3 2 1

ELV & RoHS COMPLIANT

TIN-BISMUTH PLATING TERMINAL ASSEMBLY PART NUMBERS

ASSY P/N W/O PACKAGING	CKT	DIM A	DIM B	DIM C	DIM D	PLATING TYPE
78119-0109	10	7.10	4.50	6.40	5.60	2
78119-0119	11	7.60	5.00	6.90	6.10	
78119-0129	12	8.10	5.50	7.40	6.60	
78119-0139	13	8.60	6.00	7.90	7.10	
78119-0149	14	9.10	6.50	8.40	7.60	
78119-0159	15	9.60	7.00	8.90	8.10	
78119-0169	16	10.10	7.50	9.40	8.60	
78119-0179	17	10.60	8.00	9.90	9.10	
78119-0189	18	11.10	8.50	10.40	9.60	
78119-0199	19	11.60	9.00	10.90	10.10	
78119-0209	20	12.10	9.50	11.40	10.60	
78119-0219	21	12.60	10.00	11.90	11.10	
78119-0229	22	13.10	10.50	12.40	11.60	
78119-0239	23	13.60	11.00	12.90	12.10	
78119-0249	24	14.10	11.50	13.40	12.60	
78119-0259	25	14.60	12.00	13.90	13.10	
78119-0269	26	15.10	12.50	14.40	13.60	
78119-0279	27	15.60	13.00	14.90	14.10	
78119-0289	28	16.10	13.50	15.40	14.60	
78119-0299	29	16.60	14.00	15.90	15.10	
78119-0309	30	17.10	14.50	16.40	15.60	

ASSY P/N W/O PACKAGING	CKT	DIM A	DIM B	DIM C	DIM D	PLATING TYPE
78119-0319	31	17.60	15.00	16.90	16.10	2
78119-0329	32	18.10	15.50	17.40	16.60	
78119-0339	33	18.60	16.00	17.90	17.10	
78119-0349	34	19.10	16.50	18.40	17.60	
78119-0359	35	19.60	17.00	18.90	18.10	
78119-0369	36	20.10	17.50	19.40	18.60	
78119-0379	37	20.60	18.00	19.90	19.10	
78119-0389	38	21.10	18.50	20.40	19.60	
78119-0399	39	21.60	19.00	20.90	20.10	
78119-0409	40	22.10	19.50	21.40	20.60	

REVISED	EC NO: J2013-1512	2013/06/12	QUALITY SYMBOLS
	DRWNA:YOSHI I01	2013/06/12	
	CHKD:K TAKAHASHI	2013/06/12	
	APPR:YNOGAWA	2013/06/12	
A4	DESCRIPTION		REV

$\nabla_A = 0$
 $\nabla_C = 0$
 $\nabla_P = 0$

GENERAL TOLERANCES
(UNLESS SPECIFIED)

	mm	INCH
4 PLACES	$\pm$ ---	$\pm$ ---
3 PLACES	$\pm$ ---	$\pm$ ---
2 PLACES	$\pm$ 0.15	$\pm$ ---
1 PLACE	$\pm$ ---	$\pm$ ---
0 PLACE	$\pm$	$\pm$

ANGULAR $\pm$ 3 °
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
MM ONLY

DRAWN BY	DATE
YLQIAO	2006/04/11
CHECKED BY	DATE
BOKOK	2006/04/18
APPROVED BY	DATE
PTLIM	2006/04/18

MATERIAL NO.
SEE TABLE

SIZE
A3

SCALE
NTS

TITLE

DOCUMENT NO.

DESIGN UNITS
METRIC

0.50MM PITCH, FPC CONN.
NON-ZIF, SMT

molex



SD-78119-001

THIRD ANGLE
PROJECTION

SHEET NO.
4 OF 7

9 8 7 6 5 4 3 2 1



EMBOSSED TYPE A

CUSTOMER
PULL OUT DIRECTION

REEL

NOTES:



1. LEADER AND TRAILER TAPE

2. PEELING OFF FORCE OF THE TOP TAPE: 20-80gf.
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIGURE)

3. PACKAGING STANDARD IS AS PER EIA-481.


4. TAPE & REEL QUANTITY = 1000 PCS/REEL

SECTION Y-Y




DETAIL 1

EMBOSSED TYPE B



DETAIL 1



SECTION Z-Z

REVISED EC NO: J2013-1512 DRAWN: YOSHI 101 CHKD: K TAKAHASHI APPR: YNOGAWA REV A4	DESCRIPTION 2013/06/12 2013/06/12 2013/06/25	QUALITY SYMBOLS 	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		
					DRAWN BY YLOQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT				
					CHECKED BY BOKOK	DATE 2006/04/18					
					APPROVED BY PTL IM	DATE 2006/04/18	molex				
					MATERIAL NO.						
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE TABLE		SD-78119-001			5 OF 7	
			THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								

	10	9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																						
	ELV & RoHS COMPLIANT																																																																																																																																																																																																																																																																															
F											F																																																																																																																																																																																																																																																																					
E	PARTIAL GOLD PLATING TERMINAL ASSEMBLY PART NUMBERS										E																																																																																																																																																																																																																																																																					
D	<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1108</td><td>78119-0108</td><td>10</td><td>24.00</td><td>-</td><td>11.50</td><td>7.40</td><td>5.10</td><td rowspan="10">A</td></tr><tr><td>78119-1118</td><td>78119-0118</td><td>11</td><td>24.00</td><td>-</td><td>11.50</td><td>7.90</td><td>5.60</td></tr><tr><td>78119-1128</td><td>78119-0128</td><td>12</td><td>24.00</td><td>-</td><td>11.50</td><td>8.40</td><td>6.10</td></tr><tr><td>78119-1138</td><td>78119-0138</td><td>13</td><td>24.00</td><td>-</td><td>11.50</td><td>8.90</td><td>6.60</td></tr><tr><td>78119-1148</td><td>78119-0148</td><td>14</td><td>24.00</td><td>-</td><td>11.50</td><td>9.40</td><td>7.10</td></tr><tr><td>78119-1158</td><td>78119-0158</td><td>15</td><td>24.00</td><td>-</td><td>11.50</td><td>9.90</td><td>7.60</td></tr><tr><td>78119-1168</td><td>78119-0168</td><td>16</td><td>24.00</td><td>-</td><td>11.50</td><td>10.40</td><td>8.10</td></tr><tr><td>78119-1178</td><td>78119-0178</td><td>17</td><td>24.00</td><td>-</td><td>11.50</td><td>10.90</td><td>8.60</td></tr><tr><td>78119-1188</td><td>78119-0188</td><td>18</td><td>24.00</td><td>-</td><td>11.50</td><td>11.40</td><td>9.10</td></tr><tr><td>78119-1198</td><td>78119-0198</td><td>19</td><td>24.00</td><td>-</td><td>11.50</td><td>11.90</td><td>9.60</td></tr><tr><td>78119-1208</td><td>78119-0208</td><td>20</td><td>24.00</td><td>-</td><td>11.50</td><td>12.40</td><td>10.10</td><td rowspan="10">B</td></tr><tr><td>78119-1218</td><td>78119-0218</td><td>21</td><td>32.00</td><td>28.40</td><td>14.20</td><td>12.90</td><td>10.60</td></tr><tr><td>78119-1228</td><td>78119-0228</td><td>22</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.40</td><td>11.10</td></tr><tr><td>78119-1238</td><td>78119-0238</td><td>23</td><td>32.00</td><td>28.40</td><td>14.20</td><td>13.90</td><td>11.60</td></tr><tr><td>78119-1248</td><td>78119-0248</td><td>24</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.40</td><td>12.10</td></tr><tr><td>78119-1258</td><td>78119-0258</td><td>25</td><td>32.00</td><td>28.40</td><td>14.20</td><td>14.90</td><td>12.60</td></tr><tr><td>78119-1268</td><td>78119-0268</td><td>26</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.40</td><td>13.10</td></tr><tr><td>78119-1278</td><td>78119-0278</td><td>27</td><td>32.00</td><td>28.40</td><td>14.20</td><td>15.90</td><td>13.60</td></tr><tr><td>78119-1288</td><td>78119-0288</td><td>28</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.40</td><td>14.10</td></tr><tr><td>78119-1298</td><td>78119-0298</td><td>29</td><td>32.00</td><td>28.40</td><td>14.20</td><td>16.90</td><td>14.60</td></tr><tr><td>78119-1308</td><td>78119-0308</td><td>30</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.40</td><td>15.10</td></tr></table>	ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A	78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60	78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10	78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60	78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10	78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60	78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10	78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60	78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10	78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60	78119-1208	78119-0208	20	24.00	-	11.50	12.40	10.10	B	78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60	78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10	78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60	78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10	78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60	78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10	78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60	78119-1288	78119-0288	28	32.00	28.40	14.20	16.40	14.10	78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60	78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10	<table><tr><th>ASSY P/N PACKED IN T&R</th><th>ASSY P/N W/O PACKAGING</th><th>CKT</th><th>W</th><th>So</th><th>F</th><th>Bo</th><th>B</th><th>EMBOSSED TYPE</th></tr><tr><td>78119-1318</td><td>78119-0318</td><td>31</td><td>32.00</td><td>28.40</td><td>14.20</td><td>17.90</td><td>15.60</td><td rowspan="14">B</td></tr><tr><td>78119-1328</td><td>78119-0328</td><td>32</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.40</td><td>16.10</td></tr><tr><td>78119-1338</td><td>78119-0338</td><td>33</td><td>32.00</td><td>28.40</td><td>14.20</td><td>18.90</td><td>16.60</td></tr><tr><td>78119-1348</td><td>78119-0348</td><td>34</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.40</td><td>17.10</td></tr><tr><td>78119-1358</td><td>78119-0358</td><td>35</td><td>32.00</td><td>28.40</td><td>14.20</td><td>19.90</td><td>17.60</td></tr><tr><td>78119-1368</td><td>78119-0368</td><td>36</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.40</td><td>18.10</td></tr><tr><td>78119-1378</td><td>78119-0378</td><td>37</td><td>32.00</td><td>28.40</td><td>14.20</td><td>20.90</td><td>18.60</td></tr><tr><td>78119-1388</td><td>78119-0388</td><td>38</td><td>32.00</td><td>28.40</td><td>14.20</td><td>21.40</td><td>19.10</td></tr><tr><td>78119-1398</td><td>78119-0398</td><td>39</td><td>44.00</td><td>40.40</td><td>20.20</td><td>21.90</td><td>19.60</td></tr><tr><td>78119-1408</td><td>78119-0408</td><td>40</td><td>44.00</td><td>40.40</td><td>20.20</td><td>22.40</td><td>20.10</td></tr></table>	ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE	78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B	78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10	78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60	78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10	78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60	78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10	78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60	78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10	78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60	78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10	D
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																								
78119-1108	78119-0108	10	24.00	-	11.50	7.40	5.10	A																																																																																																																																																																																																																																																																								
78119-1118	78119-0118	11	24.00	-	11.50	7.90	5.60																																																																																																																																																																																																																																																																									
78119-1128	78119-0128	12	24.00	-	11.50	8.40	6.10																																																																																																																																																																																																																																																																									
78119-1138	78119-0138	13	24.00	-	11.50	8.90	6.60																																																																																																																																																																																																																																																																									
78119-1148	78119-0148	14	24.00	-	11.50	9.40	7.10																																																																																																																																																																																																																																																																									
78119-1158	78119-0158	15	24.00	-	11.50	9.90	7.60																																																																																																																																																																																																																																																																									
78119-1168	78119-0168	16	24.00	-	11.50	10.40	8.10																																																																																																																																																																																																																																																																									
78119-1178	78119-0178	17	24.00	-	11.50	10.90	8.60																																																																																																																																																																																																																																																																									
78119-1188	78119-0188	18	24.00	-	11.50	11.40	9.10																																																																																																																																																																																																																																																																									
78119-1198	78119-0198	19	24.00	-	11.50	11.90	9.60																																																																																																																																																																																																																																																																									
78119-1208	78119-0208	20	24.00	-	11.50	12.40	10.10	B																																																																																																																																																																																																																																																																								
78119-1218	78119-0218	21	32.00	28.40	14.20	12.90	10.60																																																																																																																																																																																																																																																																									
78119-1228	78119-0228	22	32.00	28.40	14.20	13.40	11.10																																																																																																																																																																																																																																																																									
78119-1238	78119-0238	23	32.00	28.40	14.20	13.90	11.60																																																																																																																																																																																																																																																																									
78119-1248	78119-0248	24	32.00	28.40	14.20	14.40	12.10																																																																																																																																																																																																																																																																									
78119-1258	78119-0258	25	32.00	28.40	14.20	14.90	12.60																																																																																																																																																																																																																																																																									
78119-1268	78119-0268	26	32.00	28.40	14.20	15.40	13.10																																																																																																																																																																																																																																																																									
78119-1278	78119-0278	27	32.00	28.40	14.20	15.90	13.60																																																																																																																																																																																																																																																																									
78119-1288	78119-0288	28	32.00	28.40	14.20	16.40	14.10																																																																																																																																																																																																																																																																									
78119-1298	78119-0298	29	32.00	28.40	14.20	16.90	14.60																																																																																																																																																																																																																																																																									
78119-1308	78119-0308	30	32.00	28.40	14.20	17.40	15.10																																																																																																																																																																																																																																																																									
ASSY P/N PACKED IN T&R	ASSY P/N W/O PACKAGING	CKT	W	So	F	Bo	B	EMBOSSED TYPE																																																																																																																																																																																																																																																																								
78119-1318	78119-0318	31	32.00	28.40	14.20	17.90	15.60	B																																																																																																																																																																																																																																																																								
78119-1328	78119-0328	32	32.00	28.40	14.20	18.40	16.10																																																																																																																																																																																																																																																																									
78119-1338	78119-0338	33	32.00	28.40	14.20	18.90	16.60																																																																																																																																																																																																																																																																									
78119-1348	78119-0348	34	32.00	28.40	14.20	19.40	17.10																																																																																																																																																																																																																																																																									
78119-1358	78119-0358	35	32.00	28.40	14.20	19.90	17.60																																																																																																																																																																																																																																																																									
78119-1368	78119-0368	36	32.00	28.40	14.20	20.40	18.10																																																																																																																																																																																																																																																																									
78119-1378	78119-0378	37	32.00	28.40	14.20	20.90	18.60																																																																																																																																																																																																																																																																									
78119-1388	78119-0388	38	32.00	28.40	14.20	21.40	19.10																																																																																																																																																																																																																																																																									
78119-1398	78119-0398	39	44.00	40.40	20.20	21.90	19.60																																																																																																																																																																																																																																																																									
78119-1408	78119-0408	40	44.00	40.40	20.20	22.40	20.10																																																																																																																																																																																																																																																																									
C											C																																																																																																																																																																																																																																																																					
B											B																																																																																																																																																																																																																																																																					
A	<table><tr><td rowspan="10">REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 2013/06/12 CHKD: KATAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/15 A4</td><td rowspan="10">DESCRIPTION QUALITY SYMBOLS F=0 F=0 F=0</td><td colspan="2">GENERAL TOLERANCES (UNLESS SPECIFIED)</td><td colspan="2">DIMENSION STYLE MM ONLY</td><td>SCALE NTS</td><td>DESIGN UNITS METRIC</td><td colspan="2">THIRD ANGLE PROJECTION</td></tr><tr><td rowspan="5">4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE</td><td rowspan="5">± --- ± --- ± 0.15 ± --- ±</td><td rowspan="5">± --- ± --- ± --- ± --- ±</td><td>DRAWN BY YLQIAO</td><td>DATE 2006/04/11</td><td rowspan="5">TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT</td><td rowspan="5">DOCUMENT NO. SD-78119-001</td><td rowspan="5">SHEET NO. 6 OF 7</td></tr><tr><td>CHECKED BY BOKOK</td><td>DATE 2006/04/18</td></tr><tr><td>APPROVED BY PTL IM</td><td>DATE 2006/04/18</td></tr><tr><td colspan="2">MATERIAL NO. SEE TABLE</td></tr><tr><td colspan="2">SIZE A3</td></tr><tr><td colspan="2">ANGULAR ± 3 °</td><td colspan="2"></td><td colspan="2"></td></tr><tr><td colspan="2">DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS</td><td colspan="2"></td><td colspan="2"></td></tr></table>										REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 2013/06/12 CHKD: KATAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/15 A4	DESCRIPTION QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.15 ± --- ±	± --- ± --- ± --- ± --- ±	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT	DOCUMENT NO. SD-78119-001	SHEET NO. 6 OF 7	CHECKED BY BOKOK	DATE 2006/04/18	APPROVED BY PTL IM	DATE 2006/04/18	MATERIAL NO. SEE TABLE		SIZE A3		ANGULAR ± 3 °						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A																																																																																																																																																																																																																															
REVISED EC NO: J2013-1512 DRW: NAYOSHI I 01 2013/06/12 CHKD: KATAHASHI 2013/06/12 APPR: YNOGAWA 2013/06/15 A4	DESCRIPTION QUALITY SYMBOLS F=0 F=0 F=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC		THIRD ANGLE PROJECTION																																																																																																																																																																																																																																																																							
		4 PLACES 3 PLACES 2 PLACES 1 PLACE 0 PLACE	± --- ± --- ± 0.15 ± --- ±	± --- ± --- ± --- ± --- ±	DRAWN BY YLQIAO	DATE 2006/04/11	TITLE 0.50MM PITCH, FPC CONN. NON-ZIF, SMT	DOCUMENT NO. SD-78119-001	SHEET NO. 6 OF 7																																																																																																																																																																																																																																																																							
					CHECKED BY BOKOK	DATE 2006/04/18																																																																																																																																																																																																																																																																										
					APPROVED BY PTL IM	DATE 2006/04/18																																																																																																																																																																																																																																																																										
					MATERIAL NO. SEE TABLE																																																																																																																																																																																																																																																																											
					SIZE A3																																																																																																																																																																																																																																																																											
		ANGULAR ± 3 °																																																																																																																																																																																																																																																																														
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																																																																																																																																																																																																																																																																														
		ib_frame_A3_P_AM_T Rev. G 2012/01/11																																																																																																																																																																																																																																																																														
			9	8	7	6	5	4	3	2	1																																																																																																																																																																																																																																																																					

