

Article Number: 558-00380

Banded Continuous Colored Signal Panel Roll, 2.0" X 250', UV Stable, Orange/White, 250ft/RL



Base Data

Local Order Number	558-00380
Type	HT2OE50250UV
Color	Orange (OG)
Features and Benefits	• Continuous Colored Signal Panel labels come with yellow or orange stripes for easy printing of caution and warning labels. • Continuous labels allow for designing and cutting labels to any length. • Various widths are available so that a wide variety of sign sizes can be customized and produced on demand.
Product Description	The Pre-printed colored header vinyl rolls can be used to design signs that conform to Occupational Safety and Hazard Association (OSHA) and American National Standards Institute (ANSI) requirements for Warning and Caution Signs and markers. All can be designed, printed and cut to length in Tagprint Pro and any HellermannTyton thermal transfer printing system.
Short Description	Banded Continuous Colored Signal Panel Roll, 2.0" X 250', UV Stable, Orange/White, 250ft/RL

Product Dimensions

Length L (Imperial)	250.0 ft
Length L (Metric)	76.2 m
Width W (Imperial)	2.0 "
Width W (Metric)	50.8 mm
Height H (Imperial)	2.0 "
Height H (Metric)	50.8 mm
Print Method	Thermal Transfer
Vertical Repeat VR (metric)	50.8 mm
Vertical Repeat VR (imperial)	2.0 "
Width of Liner WL (metric)	50.8 mm
Width of Liner WL (imperial)	2.0 "

Logistics and Packaging

Quantity Per	reel
Package Quantity	250
Package Quantity (Metric)	250
Labels per Column	1
Labels per Row	1

Material and Specifications

Material Type 840/926, Polyester (PET), white (WH) UV stable w/ clear Polyester laminate

Material Shortcut 840/926

Adhesive Acrylic

Adhesive Shortcut Acrylic

Adhesive Operating Temperature -40°F to +302°F (-40°C to +150°C)

Operating Temperature -40°F to +302°F (-40°C to +150°C)

ROHS Compliant Yes

Certification/Specification UL969