


CH81 Series Dual Row Board Mount Pin Header



2.54mm(.100") Center spacing

⊙ Mates with CB82, CB83, CB85, CB87, CB91, CB94, CB96 and CB97


RoHS Compliant




RU :E159616





A = 2.54 x No. of Spaces
B = A + 2.36



Recommended P.C. Board Layout





Option Code	Pin Dimension	
	C	D
00	6.00(.236)	3.00(.118)
01	6.26(.246)	3.00(.118)
02	3.50(.138)	3.50(.138)
03	4.20(.165)	4.20(.165)
04	15.50(.610)	3.00(.118)



A = 2.54 x No. of Spaces
B = A + 2.36

Recommended P.C. Board Layout



Option Code	Pin Dimension	
	C	D
00	6.00(.236)	3.00(.118)
01	6.26(.246)	3.00(.118)
02	3.50(.138)	3.50(.138)
03	3.00(.118)	3.00(.118)
04	3.40(.134)	2.80(.110)

Ordering Code

1 **2** **3** **4** **5** **6**
CH 8 1 **8 0** **2** **V** **1** **0 0**

- 1** Series No.
- 2** Circuits:
04 to 80
- 3** Plating code:
2= Gold flash over Nickel plated
*Optional plating available but MOQ requested
- 4** Tail Style:
V= Straight Type
H= Right Angle Type
- 5** Insulator Color:
1= PBT UL 94V-0 , Color Black
2= PBT UL 94V-0 , Color Black (RoHS Compliant)
- 6** Other options:
00= Standard
*Special options Consult manufacturer