




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORPORATION.

PANDUIT PART NUMBER	DIMENSIONS				MAXIMUM CABLE DIA. in. (mm)	ADHESIVE BACKING	WEIGHT lbs/100 pcs (g)/100 pcs
	A	B	C	D			
ACC62-A	1.12 (28.5)	1.24 (31.4)	.73 (18.5)	0.65 (16.5) (REF)	0.62 (15.7)	RUBBER	0.96 (437)
ACC62-AT						ACRYLIC	
ACC62-AV						HIGH BOND ACRYLIC	



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

				CAD FILENAME/LAYERS				G03597BD_DC_GB0239BB/00C			
				PANDUIT CORP.				TINLEY PARK, ILLINOIS			
				ACC62-A, ACC62-AT, ACC62-AV				ADHESIVE CORD CLIP			
00C	11-6-09	TMSA	SMY	ADDED PART NUMBER ACC62-AV	GB0239BB	00C	KLN	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (.5) ANGLES ±5°			
00B	7/9/08	DJSM		REVISED AND RE-RELEASED TO TEAMCENTER REV HISTORY; TABULARIZED DIMS; REMOVED .86 AND .49 DIMS; REVISED .63 DIM TO INCLUDE TAPE; .73 WAS .74; REMOVED TAPE, APPLICATION, AND WARRANTY NOTES	GB0239BB	00B					
3	7/18/00	JAD		DIMENSIONS, .63, .86, & .49 WERE CHANGED TO REF DIMENSIONS	GB0239BB	3		DRAWN BY JRL DATE 9-11-92 CHK'D KLN			
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST				
								MAT'L: NYLON 6/6			
								SCALE FULL			
								DRAWING NO. GB0239BB			
								DWG A SIZE			