



Product: [1505A](#) 

75 Ohm SDI Coax, RG-59, 20 AWG Solid BC, Foil + 95% TC Braid, PVC Jkt, CMR

Product Description

75 Ohm SDI Coax, RG-59, 20 AWG Solid Bare Copper Conductor, PE Insulation, Foil + 95% Tinned Copper Braid Shield, PVC Jacket, CMR

Technical Specifications

Product Overview

Suitable Applications:	Digital Video, 6 Gb/s UHDTV, HD-SDI 1080p
------------------------	---

Construction Details

RG Type:	59
----------	----

Conductor

AWG	Stranding	Nom. Diameter	Material
20	Solid	0.032 in	BC - Bare Copper

Insulation

Material	Nom. Diameter
PE - Polyethylene (Foam)	0.145 in

Outer Shield Material

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
2	Braid	Tinned Copper (TC)		95%

Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.233 in

Electrical Characteristics

Return Loss (RL)

Frequency [MHz]	Min. Return Loss [dB]
5 - 1600 MHz	23 dB
1600 - 4500 MHz	21 dB
4500 - 6000 MHz	15 dB

Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.3 dB/100ft
3.58 MHz	0.6 dB/100ft
5 MHz	0.63 dB/100ft
6 MHz	0.69 dB/100ft
7 MHz	0.74 dB/100ft
10 MHz	0.9 dB/100ft
12 MHz	0.91 dB/100ft
25 MHz	1.3 dB/100ft

67.5 MHz	2.05 dB/100ft
71.5 MHz	2.1 dB/100ft
88.5 MHz	2.2 dB/100ft
100 MHz	2.3 dB/100ft
135 MHz	2.7 dB/100ft
143 MHz	2.8 dB/100ft
180 MHz	3.1 dB/100ft
270 MHz	3.8 dB/100ft
360 MHz	4.4 dB/100ft
540 MHz	5.5 dB/100ft
720 MHz	6.4 dB/100ft
750 MHz	6.5 dB/100ft
1000 MHz	7.6 dB/100ft
1500 MHz	9.5 dB/100ft
2000 MHz	11.2 dB/100ft
2250 MHz	11.9 dB/100ft
3000 MHz	14.0 dB/100ft
4500 MHz	17.5 dB/100ft
6000 MHz	21.1 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedence	Nom. Velocity
10 Ohm/1000ft	3.8 Ohm/1000ft	16.3 pF/ft	75 Ohm	82%

Voltage

UL Voltage Rating
300 V (CMR, CMG)

Mechanical Characteristics

Temperature

UL Rating	Operating
60°C	-20°C to +75°C

Bend Radius

Installation Min.
2.3 in

Bulk Cable Weight:	31 lbs/1000ft
Max. Pull Tension:	52 lbs

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, UV Resistance
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1666 Vertical Shaft, FT4
NEC / UL Compliance:	CMR
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	1506A

Product Notes

Notes:	Also available in multi-coax bundled versions. See 7794A through 7798A. Print legend includes sequential footage marks.
--------	---

History

Update and Revision:	Revision Number: 0.346 Revision Date: 09-30-2020
----------------------	--

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[1505A 010500](#) [1505A 0105000](#) [1505A 0061000](#) [1505A 006500](#) [1505A 0065000](#) [1505A 0011000](#) [1505A 0015000](#)
[1505A N3U1000](#) [1505A N3U5000](#) [1505A 0081000](#) [1505A 0085000](#) [1505A 0031000](#) [1505A 0035000](#) [1505A](#)
[0021000](#) [1505A 002500](#) [1505A 0025000](#) [1505A 0071000](#) [1505A 0075000](#) [1505A 0095000](#) [1505A 0041000](#) [1505A](#)
[0045000](#) [1505A 0091000](#) [1505A 0101000](#)