



.002-.010 FLATS
BOTH CORNERS

HUCK
HG-77-B

NOMINAL
TOUCH-GO

3

90°

A

±.001
-.000

.225

1
8

RELIEF

MIN GRIP
TOUCH-NO GO

4

A

90°

±.001
-.000

.164

.2972 ±.001

3
8

±.0010

.0825

±.000
-.001

.264


1
8

RELIEF

.002-.010 FLATS
BOTH CORNERS

SHARP CORNERS

DC-C6 collar



SECTION A-A

HG77-B	GAGE NUMBER	Huck International, Inc. Installation System Division 1 Corporate Drive - Kingston, NY 12401	
		PIN/COLLAR: NAS1426;NAS1436;NAS1080C06	
		NAME: Alloy stl, shear pin / Alum collar	
		TYPE: Pull (pin postion only)	
	OTHER		PRODUCT REVISION: F REVISED: 2/6/2002