








LOC	DIST	REVISIONS				
DY	-	P	LTR	DESCRIPTION	DATE	APVD
			F2	REVISED PER ECR-13-019056	09DEC13	W.K.



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE	01JUNE2007	TE Connectivity		
		CHK KT GOH	01JUNE2007			
		APVD SF LEONG	01JUNE2007	NAME HPI 2.0 RECEPTACLE HOUSING WITH LATCH		
		PRODUCT SPEC 108-51087				
		APPLICATION SPEC -		SIZE A3		
		WEIGHT -				
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1	OF 2
					REV F2	

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION		DATE	APVD
DY	-			SEE SHEET 1			




NOTES:

- 1


MATERIAL:
THERMOPLASTIC, UL94V-0,
- 2

TE LOGO LOCATED AT APPROXIMATE LOCATION AS SHOWN
- 3

SUITABLE TE CONTACT:1735801-1 APPLICABLE WIRE SIZE #24~#30 ONLY



5~16P



3~4P

BLACK	8.2	10.4±0.2	28.00	32.80	30.00	16P	3-1735447-6
	8.2	10.4±0.2	26.00	30.80	28.00	15P	3-1735447-5
	8.2	10.4±0.2	24.00	28.80	26.00	14P	3-1735447-4
	8.2	10.4±0.2	22.00	26.80	24.00	13P	3-1735447-3
	8.2	10.4±0.2	20.00	24.80	22.00	12P	3-1735447-2
	8.2	10.4±0.2	18.00	22.80	20.00	11P	3-1735447-1
	8.2	10.4±0.2	16.00	20.80	18.00	10P	3-1735447-0
	8.2	10.4±0.2	14.00	18.80	16.00	9P	2-1735447-9
	8.2	10.4±0.2	12.00	16.80	14.00	8P	2-1735447-8
	7.3	9.5±0.2	10.00	14.80	12.00	7P	2-1735447-7
	5.3	7.5±0.2	8.00	12.80	10.00	6P	2-1735447-6
	3.3	5.5±0.2	6.00	10.80	8.00	5P	2-1735447-5
	1.3	3.5±0.2	4.00	8.80	6.00	4P	2-1735447-4
	1.0	1.8 ^{+0.08} _{-0.2}	2.00	6.80	4.00	3P	2-1735447-3
NATURAL	8.2	10.4±0.2	28.00	32.80	30.00	16P	1-1735447-6
	8.2	10.4±0.2	26.00	30.80	28.00	15P	1-1735447-5
	8.2	10.4±0.2	24.00	28.80	26.00	14P	1-1735447-4
	8.2	10.4±0.2	22.00	26.80	24.00	13P	1-1735447-3
	8.2	10.4±0.2	20.00	24.80	22.00	12P	1-1735447-2
	8.2	10.4±0.2	18.00	22.80	20.00	11P	1-1735447-1
	8.2	10.4±0.2	16.00	20.80	18.00	10P	1-1735447-0
	8.2	10.4±0.2	14.00	18.80	16.00	9P	1735447-9
	8.2	10.4±0.2	12.00	16.80	14.00	8P	1735447-8
	7.3	9.5±0.2	10.00	14.80	12.00	7P	1735447-7
	5.3	7.5±0.2	8.00	12.80	10.00	6P	1735447-6
	3.3	5.5±0.2	6.00	10.80	8.00	5P	1735447-5
	1.3	3.5±0.2	4.00	8.80	6.00	4P	1735447-4
	1.0	1.8 ^{+0.08} _{-0.2}	2.00	6.80	4.00	3P	1735447-3
COLOUR	E	D	C	B	A	POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
mm

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±

FINISH -

DWN
WYLEE
01JUNE2007

CHK
KT GOH
01JUNE2007

APVD
SFLEONG
01JUNE2007

PRODUCT SPEC
108-51087

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
HPI 2.0 RECEPTACLE HOUSING
WITH LATCH

SIZE
A3

CAGE CODE
00779

DRAWING NO
1735447

RESTRICTED TO

SCALE
5:1

SHEET
2

OF
2

REV
F2