

Pocket Fold-up Thermometer

✓ **4.5" stainless steel probe adjusts from 0 to 180°**
With detents at 45°, 90°, 135° and 180°

Features:

- Wide °C/°F switchable temperature range
-58 to 572°F (-50 to 300°C)
- Fold up probe 4.5" (114mm) adjusts from 0° to 180° for best measurement and viewing angle
- Large LCD display with 0.1 degree resolution
- Auto power off after 1 hour or when probe is placed in stored position
- Data Hold and Min/Max recordings
- Fast response time — one second under normal conditions
- Complete with wrist strap and one AAA battery



Specifications	
Range	-58 to 572°F (-50 to 300°C)
Accuracy	±1.8°F (-22 to 482°F); ±1°C (-30 to 250°C)
Resolution	0.1°/1° resolution
Dimensions	6.1 x 2.0 x 0.8" (154 x 50 x 20mm)
Weight	2.5oz (71g)

Ordering Information:

39272Pocket Fold-up Thermometer
409992Vinyl Pouch Carrying Case



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Extech:](#)

[39272](#)