




Schematic



Model No.	Switching Position		
	ON	NONE	OFF
DS-40			
Term Comm.	2-3	OPEN	2-1

SPECIFICATIONS:

CONTACT RATING : 3 AMPS @ 120 V AC or 28 V DC.
 1.5 AMPS @250 V AC or 0.4VA AMPS @ 20V AC or DC
 ELECTRICAL LIFE : 6,000 make-and-break cycles at full load.
 CONTACT RESISTANCE : 20 mΩ max. initial @ 2-4 V DC.
 100 mA, for both silver and gold plated contacts.
 INSULATION RESISTANCE : 1,000 MΩ min.
 DIELECTRIC STRENGTH : 1,000 V RMS @ sea level.
 OPERATING TEMPERATURE : -30 °C to 130 °C

MATERIALS:

CASE : Diallyl phthalate (DAP)(UL-94V-0).
 ACTUATOR : ZINC ALLOY.
 BUSHING : ZINC ALLOY.
 HOUSING : Stainless steel.
 TERMINAL/CONTACT : Brass, with silver or gold plated.
 or gold over silver
 SWITCH SUPPORT : Brass, tin plated.

GOLDSUN ELECTRONICS CO., LTD.

JAMECO NO. 72161	GOLDSUN NO. DS-40T1B1A1-ROHS		
Description SUB-MINI TOGGLE SWITCH SPST ON-OFF 2P SOLDER LUG			Rev. 1
UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: