

Feedthrough Capacitor Filters EG Series

[RoHS Compliant]




Model	Rated voltage DC (V)	Rated current (A) max.	Operating temperature range (°C)	Storage temperature range (°C)
EG-□-□□□□	50	5	-25 to +85	-40 to +100


• Withstanding voltage: 125VDC • Insulation resistance: 1000MΩ

Shape and Dimensions

●EG-8 type




●EEG-4 type



[mm]

Circuit Diagram



Numbering System

EG-□-□□□□


①

②

① 3:3 line, 4:4 line, 8:8 line

② 470S : 47pF, 101S : 100pF, 271S : 270pF, 471P : 470pF, 102P : 1,000pF

Attenuation Characteristics



- All specifications in this catalog and production status of products are subject to change without notice. Prior to the purchase, please contact NEC TOKIN for updated product data.
- Please request for a specification sheet for detailed product data prior to the purchase.
- Before using the product in this catalog, please read "Precautions" and other safety precautions listed in the printed version catalog.